


ADVANCED PERFORMANCE Pneumatic Products for Pure Gas Applications



- **Gases:** Pure Air (DEF STAN 58-96), Nitrogen
- **Small Pneumatics Components and Sub-Assemblies** – modular or integral
– for High-Pressure Pneumatic Applications
- **Designed** to Specific Requirements
- **Stainless Steel Cylinders** – Pressures to 500 bar
- **Manifold Assemblies** – options include Charging Valves, Relief Valves or
Burst Discs, Pressure Gauges, Control Valves
- **Pressure** Regulating Valves
- **Solenoid Valves** – manifold or in-line; single or two-stage
- **Pipework Sub-Assemblies** connecting cylinders to manifolds or components;
or manifolds to other sub-assemblies
- **Applications:**
 - Thermal Imaging
 - Pressurisation
 - Blowdown
 - Actuation

Solutions built to exact customer requirements and specifications



Pressure test rig



Gas tube helium leak test equipment



Pure air compatibility test equipment



Brazing control panel