

# D-Subminiature

## 289-064

### Shorting Cap Backshell, HiPer-D

D-SUBMINIATURE ACCESSORIES



#### 289-064

This accessory fits HiPer-D connectors with backshell groove: 280-018P, 280-019S, 280-046P, 280-047S. Not compatible with standard D-Sub connectors.

**HiPer-D Shorting Cap.** Low profile two piece adapter fits HiPer-D® connectors with backshell groove (280-018P, 280-019S, 280-046P, 280-047S). Available in five standard finishes. Optional lanyard for attaching cap. Aluminum with passivated stainless steel screwlocks and clips.

#### ATTACHMENT TYPE

**F**

**Wire Rope, Black Nylon Jacket**  
6/6 nylon over stainless steel rope, fair flexibility, good abrasion resistance, -55 to +100 °C

**H**

**Wire Rope, Black FEP Jacket**  
Black FEP jacket over SST rope, fair flexibility, good abrasion resistance, .100" diameter, -65 to +200 °C

Shell Size	A Max		B Max	
	in	mm	in	mm
1	.894	22.7	.550	14.0
2	1.218	30.9	.550	14.0
3	1.760	44.7	.550	14.0
4	2.408	61.2	.550	14.0
5	2.297	58.3	.654	16.6
6	2.422	61.5	.716	18.2

#### PART NUMBER

Sample PN →		<b>289-064</b>	<b>3</b>	<b>JF</b>	<b>H</b>	<b>4</b>
Base P/N	<b>289-064</b>					
Shell Size	<b>1 2 3 4 5 6</b>					
Finish	<b>TZ</b> Tin-Zinc <b>MN</b> Mega-Nickel <b>JF</b> Cadmium, Yel. Chromate <b>ME</b> Electroless Nickel <b>NF</b> Olive Drab Cadmium <b>MT</b> Nickel-PTFE <b>ZR</b> Black Zinc-Nickel					
Attachment Type	<b>Omit</b> No Attachment <b>F</b> Wire Rope, Black Nylon Jacket <b>H</b> Wire Rope, Black FEP Jacket					
Attachment Length	<b>Omit</b> No Attachment Length in One Inch Increments (Example: "5" for five inch length)					

