

GS22759-33

Silver Coated Wire, High-Strength Copper Conductor with Modified XL-ETFE Insulation

MIL-STAR

NOTES

1. Wire is made in accordance with AS22759/33.
2. Conductor is silver coated high-strength copper per AS29606.
3. Insulation is crosslinked modified ETFE
4. Wire maximum continuous temperature rating is 200°C (392°F).
5. Voltage rating is 600 volts (RMS) at sea level.
6. Color code per MIL-STD-681. See MIL-STD-681 for additional wire color codes. Jacket color code must be white (9) if adding color stripes.
7. Consult factory for custom stripe color order.

HOW TO ORDER						
Sample Part Number	GS22759-33	-24	-9	0	1	2
Basic Part Number	GS22759-33					
Wire Size	See Table I					
Jacket Color Code	See Table II					
First Stripe Color Code	(Omit for none) See Table II					
Second Stripe Color Code	(Omit for none) See Table II					
Third Stripe Color Code	(Omit for none) See Table II					




Table II: Jacket and Stripe Color Codes

Color code	Color
0	Black
1	Brown
2	Red
3	Orange
4	Yellow
5	Green
6	Blue
7	Violet
8	Gray
9	White

Table I: Part Number and Wire Specifications

Part Number	Wire Size	Stranding (Number of strands x AWG of strands)	Diameter of stranded conductor (inches)		Finished Wire		
			min.	max.	Resistance at 20° C (68° F) (Ohms/1000 ft) max.	Diameter (inches)	Weight (lbs/1000 ft) max.
GS22759-33-30*	30	7 X 38	0.0105	0.0124	117.4	.024±.002	0.66
GS22759-33-28*	28	7 X 36	0.0135	0.0164	74.4	.027±.002	0.91
GS22759-33-26*	26	19 X 38	0.0175	0.0204	44.8	.032±.002	1.4
GS22759-33-24*	24	19 X 36	0.0225	0.0254	28.4	.037±.002	2.0
GS22759-33-22*	22	19 X 34	0.0285	0.0314	17.5	.043±.002	2.9
GS22759-33-20*	20	19 X 32	0.0365	0.0394	10.7	.050±.002	4.4