


SPECIAL PURPOSE CONTACTS

Thermocouple Cables



8577-0001 Jumper wire M22759 with M39029/56 and 58 contacts

HOW TO ORDER							
Sample Part No.	8577-0001M	-16	-22	-0	-3	-P20	-S20
Wire Spec	8577-0001M = MIL-SPEC M22759 8577-0001G : Made IAW M22759 (GS22759)						
Wire Slash Sht	16 to 19, 32 to 35, 41 to 46						
Wire Gage (AWG)	-8, -10, -12, -14, -16, -18, -20, -22, -24, -26						
Color Code	0 = Black 1 = Brown 2 = Red 3 = Orange 4 = Yellow 5 = Green 6 = Blue 7 = Violet 8 = Gray 9 = White						
Length in Feet	3 = 3 Feet 1.5 = 1 Foot, 6 Inches						
Contact Type	P20 = Pin Contacts, Size 20 S20 = Socket Contacts, Size 20 See Table I & II						
Contacts	See Table I & II (Omit for None)						



JUMPER WIRE WITH CONTACTS

TABLE I: PIN CONTACT			
	Contact Size	Wire Range (AWG)	Contact P/N
P22	22	22, 24 & 26	M39029/58-360
P20	20	20, 22 & 24	M39029/58-363
P16	16	16, 18 & 20	M39029/58-364
P12	12	12 & 14	M39029/58-365
P10	10	10	M39029/58-528
P8	8	8	850-014
P8B	8	8	850-014F

TABLE II: SOCKET CONTACT			
	Contact Size	Wire Range (AWG)	Contact P/N
S22	22	22, 24 & 26	M39029/56-348
S20	20	20, 22 & 24	M39029/56-351
S16	16	16, 18 & 20	M39029/56-352
S12	12	12, & 14	M39029/56-353
S10	10	10	M39029/56-527
S8	8	8	850-013
S8B	8	8	850-013F