


963-066-24 Cat6a Cable, #24 AWG



963-066-24

- 100 Ohm twisted pair shielded cable.
- -65 to +200 °C rated operating temperature
- FEP jacket, FEP insulation
- Dual shields: Aluminized Polyimide tape and #40 AWG silver-plated copper

NOTES

- Cable identified with manufacturer's name and part number.
- Cable is sold in 1 foot increments. Specify desired length on purchase order.

Cable Construction

A	(4x) Data Pairs	100 Ohm (Nom.), Shielded Twisted Pair
	Conductors	24 AWG (19/36) High Strength Copper Alloy
	Insulation	FEP
	Colors	Blue, White/Blue Orange, White/Orange Green, White/Green Brown, White/Brown
	Binder	PTFE Tape
B	Pair Shield	Aluminum/Polyimide tape
B	Outer Shield	Silver Plated Copper, 90% min. coverage
C	Outer Jacket	FEP (White Laser-Markable)
Minimum bend radius: 1.25		
Weight: 19.0 g/ft		

Electrical Performance

Dielectric Withstanding Voltage (VRMS)	600
Differential Impedance	100 ± 10 Ohms
Insertion Loss (SDD21)	See Table 1

Environmental Properties

Temperature Range	-65°C to 200°C
-------------------	----------------

Table 1: Attenuation

Frequency (MHz)	dB / ft Maximum
100	.081
250	.125
500	.182
1000	.266
2000	.380