



# SERIES 79 Advanced-Performance Rectangular with SpeedMaster™ 10G High-Speed Contacts



## 7925-005 Float Mount Connector Plug

Part Number Development							
<b>Sample Part Number</b>	<b>7925-005</b>	<b>N</b>	<b>C2-23</b>	<b>M</b>	<b>G</b>	<b>S</b>	<b>-A</b>
<b>Series - Basic Part No.</b>	7925-005 Float Mount Connector Plug						
<b>N-Less Contacts</b>	Connectors are supplied less contacts, order separately via these Part Numbers: <b>858-101-X</b> SpeedMaster Pin contacts, individual <b>8585-0001</b> SpeedMaster Contacts, pre-terminated (Use order code "A" for P1) <b>850-095-X</b> 22HD Socket contacts, individual						
<b>Shell Size/Insert Arrangements</b>	See Insert Arrangements table						
<b>Shell Finish</b>	<b>M</b> = Electroless Nickel <b>MT</b> = Nickel Teflon <b>E</b> = Chemfilm <b>Z2</b> = Gold <b>UC</b> = Black Zinc Cobalt <b>J</b> = Yellow Cadmium <b>NF</b> = Olive Drab Cadmium						
<b>Hardware Option</b>	<b>G</b> = Guide Pin <b>S</b> = Single Piece (Screw Mount)						
<b>Backshell Geometry</b>	<b>C</b> = Clam Shell <b>S</b> = Single Piece						
<b>Optional Shell Keying</b>	See Mod Code 1104 Omit for None						



Hardware Options	
<b>N</b> No Hardware	<b>G</b> Guide Pin
Thread Size is #10-32	Connector Supplied with Non-Removable Guide Bushing

### NOTES


1. Refer to drawing 799-008 for complete materials and finishes specifications.
2. Contacts are ordered separately. SpeedMaster contacts may be ordered pre-terminated via 8585-0001, or contact the factory for complete cable contact.

Insert Arrangements		
<b>A1</b> 1X SPEEDMASTER	<b>B2</b> 2X SPEEDMASTER	<b>B1-16</b> 1X SPEEDMASTER 16X #22HD
<b>C3</b> 3X SPEEDMASTER	<b>C2-23</b> 2X SPEEDMASTER 23X #22HD	<b>C1-46</b> 1X SPEEDMASTER 46X #22HD
<b>D4</b> 4X SPEEDMASTER	<b>D2-48</b> 2X SPEEDMASTER 48X #22HD	

# SERIES 79 Advanced-Performance Rectangular with SpeedMaster™ 10G High-Speed Contacts



## 7925-005 Float Mount Connector Plug



### Dimensions

Shell Size	A Max	B	C Max	D
A	2.320 (58.93)	1.075 (27.30)	0.611 (15.52)	1.815 (46.10)
B	2.760 (70.10)	1.515 (38.48)	1.051 (26.70)	2.255 (57.28)
C	3.200 (81.28)	1.955 (49.66)	1.491 (37.87)	2.695 (68.45)
D	3.640 (92.46)	2.395 (60.83)	1.931 (49.05)	3.135 (79.63)

### BUSHING FLOAT DETAILS

