


SERIES 79 Advanced-Performance Rectangular with SpeedMaster™ 10G High-Speed Contacts



7925-006 Float Mount Connector Receptacle

Part Number Development							
Sample Part Number	7925-006	N	C2-23	M	B	S	-A
Series - Basic Part No.	7925-006 Float Mount Connector Receptacle						
N-Less Contacts	Connectors are supplied less contacts, order separately via these Part Numbers: 858-100-X SpeedMaster Socket contacts, individual 8585-0001 SpeedMaster Socket contacts, pre-terminated (Use order code "B" for P1) 850-094-X 22HD Pin contacts, individual						
Shell Size/Insert Arrangements	See Insert Arrangements table						
Shell Finish	M = Electroless Nickel MT = Nickel Teflon E = Chemfilm Z2 = Gold UC = Black Zinc Cobalt J = Yellow Cadmium NF = Olive Drab Cadmium						
Hardware Option	G = Guide Bushing N = None						
Backshell Geometry	C = Clam Shell S = Single Piece (Screw Mount)						
Optional Shell Keying	See Mod Code 1104 Omit for None						



Hardware Options	
N No Hardware	B Guide Bushing
Thread Size is #10-32	Connector Supplied with Non-Removable Guide Bushing

NOTES


1. Refer to drawing 799-008 for complete materials and finishes specifications.
2. Contacts are ordered separately. SpeedMaster contacts may be ordered pre-terminated via 8585-0001, or contact the factory for complete cable contact.

Insert Arrangements		
A1 1X SPEEDMASTER	B2 2X SPEEDMASTER	B1-16 1X SPEEDMASTER 16X #22HD
C3 3X SPEEDMASTER	C2-23 2X SPEEDMASTER 23X #22HD	C1-46 1X SPEEDMASTER 46X #22HD
D4 4X SPEEDMASTER	D2-48 2X SPEEDMASTER 48X #22HD	

SERIES 79
Advanced-Performance Rectangular
with SpeedMaster™ 10G High-Speed Contacts



7925-006 Float Mount Connector Receptacle



Dimensions

Shell Size	A Max	B	C Max	D
A	2.320 (58.93)	1.075 (27.30)	0.685 (17.40)	1.815 (46.10)
B	2.760 (70.10)	1.515 (38.48)	1.125 (28.58)	2.255 (57.28)
C	3.200 (81.28)	1.955 (49.66)	1.565 (39.75)	2.695 (68.45)
D	3.640 (92.46)	2.395 (60.83)	2.005 (50.93)	3.135 (79.63)

BUSHING FLOAT DETAILS

