




GT-26-253

COAX CONNECTOR, ATNC FEMALE BULKHEAD
GRF01-0300-ATNC-FB-086 FOR CABLE 962-025-086
RF Signal Integrity Report





Revision History

Rev	Date	Issued	Approved	Description
1	9/14/2026	L. Blackwell	G. Hunziker	Initial Release

Table of Contents

1. Introduction	3
2. Test Information	3
2.1. Test Samples	3
2.2. Test Setup	3
3. Test Results	4
3.1.1. Connector Insertion Loss	4
3.1.2. Connector VSWR	5

Table of Figures

Figure 1. GRF01-0300-ATNC-FB-086 Test Article	3
Figure 2. Connector Insertion Loss	4
Figure 3. Connector VSWR	5

1. Introduction

This document contains results from testing that was performed to evaluate the high-frequency electrical performance of the Glenair ATNC female bulkhead connector, part number GRF01-0300-ATNC-FB-086. This report outlines the frequency domain performances of Insertion Loss (IL) and Voltage Standing Wave Ratio (VSWR).

2. Test Information

2.1. Test Samples

Test samples consisted of GRF01-0300-ATNC-FB-086 connectors terminated to Glenair cable 962-025-086.




Figure 1. GRF01-0300-ATNC-FB-086 Test Article

2.2. Test Setup

Measurements were taken using an Anritsu MS46524B Vector Network Analyzer. Test adapters were used to connect to the test equipment. The test data was saved in a touchstone (.s2p) format.



3. Test Results

3.1.1. Connector Insertion Loss




Figure 2. Connector Insertion Loss



3.1.2. Connector VSWR




Figure 3. Connector VSWR