


MIL-DTL-38999 Series I Type  
 Quick selection guide

BACKSHELLS AND ACCESSORIES

QUICK SELECTION GUIDE		
Part Number	Description	Page
<b>310F*045</b>	Shrink boot adapter, composite	143
<b>310F*048</b>	Shrink boot adapter, pre-installed boot, composite	144
<b>370F*001</b>	Backshell, environmental, spin coupling	145
<b>440F*143</b>	Composite, shrink boot, ultra low profile 90°	147
<b>447F*326</b>	Composite, shrink boot, micro band	148
<b>870F001</b>	Swing-Arm® saddle clamp	149
<b>870F002</b>	Swing-Arm® saddle clamp, braid sock, composite	151
<b>870F005</b>	Swing-Arm® saddle clamp, EMI banding adapter, aluminum/SST	153
<b>871F004</b>	Swing-Arm® clamp, EMI banding adapter, composite	155
<b>667-467</b>	Proseal™ spring-action receptacle cover	157
<b>660-012</b>	Plug protective cover	158
<b>661-002</b>	Receptacle cover, spring-loaded EMI	159
<b>M85049</b>	Nut plate	160
	Composite Swing-Arm® strain relief assembly procedure	161
<b>470-013</b>	Starshield™ EMI/RFI shield termination backshell	163
<b>770-003S</b>	Lipped, straight shrink boots, without eyelet	165
<b>770-001S</b>	Lipped, straight shrink boot, with eyelet	167
<b>770-004S</b>	Lipped, short straight shrink boot, without eyelet	169
<b>770-005/-006</b>	Autoshrink D cold-action boots, standard / short	171
<b>770-015</b>	Autoshrink D cold-action boot, 90°, lipless, no eyelet	173
<b>600-117</b>	Jam nut wrench for connectors	174



**310F\*045**



**660-012**



**310F\*048**



**870F001**



**870F002**



**870F005**



**871F004**



**667-467**