

MIL-DTL-38999 Series III Type

239-215 Standard jam nut

How to Order 239-202				
Sample Part Number		239-215	ME	11
Series	Replacement Jam Nut for .125" panels			
Material / Finish	See Table II			
Dash No.	See Table I			
Alternate Crimp Design	C = Alternate Crimp Design			




Table I: Dimensions						
Dash No.	Shell Size	A Thread Isometric	B Hex Max		C +.018 -.000	
			in	mm	in	mm
9	9	M17 X 1.0 - 6H	.945 .860	24.00 21.84	.125	3.175
11	11	M20 X 1.0 - 6H	1.063 .984	27.00 24.99		
13	13	M25 X 1.0 - 6H	1.260 1.172	32.00 29.77		
15	15	M28 X 1.0 - 6H	1.417 1.296	35.99 32.92		
17	17	M32 X 1.0 - 6H	1.457 1.422	37.01 36.12		
19	19	M35 X 1.0 - 6H	1.614 1.545	41.00 39.24		
21	21	M38 X 1.0 - 6H	1.811 1.672	46.00 42.47		
23	23	M41 X 1.0 - 6H	1.969 1.796	50.01 45.62		
25	25	M44 X 1.0 - 6H	2.017 1.939	51.23 49.25		

Table II: Material and Finish		
Sym	Material	Finish
NF	Aluminum Alloy	Cad Plate / Olive Drab over Electroless Nickel
MA		Electroless Nickel, Matte
MT		Nickel-PTFE
ME		Electroless Nickel
MN		Mega-Nickel
TZ		Tin-Zinc
ZN		Zinc-Nickel, Olive Drab
ZR		Zinc-Nickel, Black (Tri-Valent CR)
TD	Titanium	Natural-No Plate
Z1	Stainless Steel	Passivate
ZL		Electrodeposited Nickel
AB	Marine Bronze	None