



# TEST REPORT

7/25/25
GT-23-261
Revision 2
Page 1 of 6

# GT-23-261

## Glenair GS22759-32 Commercial Equivalent Wire Test Summary (Ref. QTP-1347)

Revision	Description of Changes	Date	Author
1	Initial Release	12/20/2023	JCR
2	Updated conclusion	7/25/25	JCR



# TEST REPORT

7/25/25
GT-23-261
Revision 2
Page 2 of 6

## 1.0 Scope

This report summarizes the test results of Glenair's GS22759-32 commercial equivalent wire to AS22759/32. All tests were performed according to AS22759 and QTP-1347 except the ovens were not calibrated per ASTM Type II oven requirements, where applicable.

## 2.0 Reference Documents

AS22759 Revision D	Wire, Electrical, Fluoropolymer-Insulated, Copper or Copper Alloy
AS4373 Revision F	Test Methods for Insulated Electric Wire
ASTM D3032 Revision 21A	Standard Test Methods for Hookup Wire Insulation
AS29606 Revision B	General Specification for Wire, Electrical, Stranded, Uninsulated Copper, Copper Alloy, or Aluminum, or Thermocouple Extension
AS5768 Revision C	General Specification for Tool, Stripper, Electrical Insulation
GS22759-32 Revision 3	Wire, Electrical, Fluoropolymer-Insulated, Cross-linked Modified ETFE, Light Weight, Tin-Coated Copper, 150°C, 600-Volt, RoHS



# TEST REPORT

7/25/25
GT-23-261
Revision 2
Page 3 of 6

### 3.0 Test Specimens

The part number and description of the wire tested are listed in Table I.

Table I

Part Number	Description
GS22759-32-22-9	Glenair AS22759/32 22 AWG Wire Tin-Coated Copper Conductor Cross-Linked ETFE-Insulated

### GS22759-32


THIS COPYRIGHTED DOCUMENT IS THE PROPERTY OF GLENAIR, INC. AND IS FURNISHED ON THE CONDITION THAT IT IS NOT TO BE DISCLOSED, REPRODUCED IN WHOLE OR IN PART, OR USED TO SOLICIT QUOTATIONS FROM COMPETITIVE SOURCES, OR USED FOR MANUFACTURE BY ANYONE OTHER THAN GLENAIR, INC. WITHOUT WRITTEN PERMISSION FROM GLENAIR, INC. THE INFORMATION HEREIN HAS BEEN DEVELOPED AT GLENAIR'S EXPENSE AND MAY BE USED FOR ENGINEERING EVALUATION AND INCORPORATION INTO TECHNICAL SPECIFICATIONS AND OTHER DOCUMENTS WHICH SPECIFY PROCUREMENT OF PRODUCTS FROM GLENAIR, INC.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
1	PRELIMINARY	02/01/22	LKJ
2	PRELIMINARY: ADDED STRIPES TO PART NUMBER.	09/12/22	NHJ
3	PRELIMINARY: TEMP RATING, FROM COND. TO WIRE.	09/26/22	NHJ

PART NUMBER	WIRE SIZE	STRANDING (NUMBER OF STRANDS X SIZE GAGE OF STRANDS)	DIAMETER OF STRANDED CONDUCTOR (INCHES)		RESISTANCE AT 20°C (68°F) (OHMS/1000 FEET)		WEIGHT (LB/1000 FEET) (MAX)
			(MIN)	(MAX)	(MAX)	(MAX)	
GS22759-32-30→	30	7 X 38	.0105	.0134	108.4	.024 ± .002	.66
GS22759-32-28→	28	7 X 36	.0135	.0164	68.6	.027 ± .002	.91
GS22759-32-26→	26	19 X 38	.0175	.0204	41.3	.032 ± .002	1.4
GS22759-32-24→	24	19 X 36	.0225	.0254	26.2	.037 ± .002	2.0
GS22759-32-22→	22	19 X 34	.0285	.0314	16.2	.043 ± .002	2.8
GS22759-32-20→	20	19 X 32	.0365	.0394	9.88	.050 ± .002	4.3
GS22759-32-18→	18	19 X 30	.0455	.0494	6.23	.060 ± .002	6.5
GS22759-32-16→	16	19 X 29	.0515	.0554	4.81	.068 ± .002	8.3
GS22759-32-14→	14	19 X 27	.0645	.0694	3.06	.085 ± .003	13.0
GS22759-32-12→	12	37 X 28	.0835	.0894	2.02	.103 ± .003	19.7

PART NUMBER DEVELOPMENT:

EXAMPLE: GS22759-32 - 24 - 9 0 1 2



COLOR CODE	COLOR
0	BLACK
1	BROWN
2	RED
3	ORANGE
4	YELLOW
5	GREEN
6	BLUE
7	VIOLET
8	GRAY
9	WHITE

NOTES:

1. WIRE IS MADE IN ACCORDANCE WITH AS22759/32.
2. CONDUCTOR IS TIN COATED COPPER PER AS29606.
3. INSULATION IS CROSSLINKED MODIFIED ETFE (ETHYLENE-TETRAFLUOROETHYLENE).
4. WIRE MAXIMUM CONTINUOUS TEMPERATURE RATING IS 150°C (302°F).
5. VOLTAGE RATING IS 600 VOLTS (RMS) AT SEA LEVEL.
6. COLOR CODE PER MIL-STD-681. SEE MIL-STD-681 FOR ADDITIONAL WIRE COLOR CODES.
7. CONSULT FACTORY FOR CUSTOM STRIPE COLOR ORDER.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES:	DRAWN LKJ 02/01/22 CHECK SF 02/01/22 ENGR LKJ 02/01/22	<b>GLENAIR, INC.</b> C40 1007° 1211 AIR WAY - GLENDALE - CALIFORNIA 91201
FRACTIONS ± 1/16 DECIMALS .XX ± .030 .XXX ± .015 ANGLES ± 1°	<i>L. Brown</i>	AS22759/32 WIRE, TIN COATED COPPER CONDUCTOR CROSSLINKED MODIFIED ETFE INSULATED, 600-VOLT, 150°C
DO NOT SCALE THIS DRAWING	ISSUE DATE REVISE DATE	CODE IDENT. NO. SIZE 06324 C GS22759-32
B/F 21A343 P/C	NON REPAIRABLE COMMERCIAL ITEM	SCALE N/A WEIGHT N/A SHEET 1 OF 1

Figure 1 – Glenair AS22759/32 Wire Drawing GS22759-32



# TEST REPORT

7/25/25
GT-23-261
Revision 2
Page 4 of 6

## 4.0 Summary of Results

The test results are summarized in Table II.

**Table II**

Test	Specification	Test Requirements	Results	Results
Insulated Conductor Tin Solderability	AS4373 Method 105	95%, min.	Pass	Pass
Insulated Conductor Geometric Characteristics (Diameter)	AS29606 AS22759/32	22 AWG: 0.0285-0.0314"	0.02892"	Pass
Insulated Conductor Elongation	AS29606 AS4373 Method 402	22 AWG: 10%, min.	10.9%	Pass
Insulation Construction (Material Type)	AS22759/32	Cross-linked Modified ETFE	Pass	Pass
Insulation Tensile Strength and Elongation	AS4373 Method 705	5000 psi tensile strength, min. 75% elongation, min.	6620 psi 169%	Pass
Short-Term Thermal Stability	AS4373 Method 811	7 hours at 300°C ± 3°C DWV 2500 VDC, 60 seconds	Pass	Pass
Insulation Blocking	AS4373 Method 808	24 hours at 200°C ± 3°C	Pass	Pass
Insulation Shrinkage	AS4373 Method 104	6 hours at 200°C ± 3°C 0.125" max. shrinkage	Pass	Pass
Wire Conductor Electrical Resistance	AS4373 Method 403	22 AWG: 16.2 Ω/1000 ft., max.	13.6 Ω/1000 ft	Pass



# TEST REPORT

7/25/25
GT-23-261
Revision 2
Page 5 of 6

Wire Electrical Insulation Resistance	AS4373 Method 504	22 AWG: 5000 MΩ-1000 ft., min.	68,000 MΩ-1000	Pass
Wire Electrical Surface Resistance	AS4373 Method 506	22 AWG: 500 MΩ-inches, min. at 500 VDC	Pass	Pass
Electrical Dielectric Resistance – Wet Dielectric Voltage	AS4373 Method 510	2500 V (rms) at 60Hz, min.	Pass	Pass
Wire Diameter	AS4373 Method 901	22 AWG: 0.043 ± 0.002"	0.0421"	Pass
Wire Weight	AS4373 Method 902	22 AWG: 2.8 lbs./1000 ft., max.	2.8 lbs./1000 ft	Pass
Wire Insulation Stripping	AS5768/1 AS5768/2	Insulation readily removable without damage to the conductor	Pass	Pass
Wire Insulation Concentricity and Wall Thickness	AS4373 Method 101	70 %, min.	88.1%	Pass
Wire Identification Printed Marking and Location	AS22759	Marking intervals of 6 to 60 inches	N/A	N/A
Workmanship	AS22759	No cracks, splits, irregularities, or embedded foreign material	Pass	Pass
Wire Color Designators and Munsell Limits	EIA-359-A	Visual inspection against Munsell color chart	Pass	Pass



# TEST REPORT

7/25/25
GT-23-261
Revision 2
Page 6 of 6

Wire Identification Mark, Stripe, and Band Durability	AS4373 Method 710	125 cycles (250 strokes) with a 500-gram weight	N/A	N/A
Wrap Back Bend Mechanical Resistance for Extruded Insulation	AS4373 Method 708	2 hours at 200°C ± 3°C No cracking or splitting	Pass	Pass
Insulation Low Temperature Mechanical Resistance/Cold Bend	AS4373 Method 702	4 hours at -65°C ± 3°C DWV 2500 V (rms) at 60 Hz	Pass	Pass
Insulation Thermal Shock Mechanical Resistance	AS4373 Method 805	-55°C ± 3°C to 200°C ± 3°C 0.060" max. shrinkage	0.02"	Pass
Thermal Mechanical Resistance – Life Cycle	AS4373 Method 807	500 hours at 200°C ± 3°C DWV 2500 V (rms) at 60 Hz	Pass	Pass
Fluid Resistance – Immersion	AS4373 Method 601	Diameter increase 5% max. DWV 2500 V (rms) at 60 Hz	Pass	Pass
Humidity Resistance	AS4373 Method 603	22 AWG: 5000 MΩ-1000 ft., min.	Pass	Pass
Smoke Resistance	AS4373 Method 513	200°C ± 2°C No visible smoke	Pass	Pass
Flammability	AS4373 Method 801	Self-extinguishing flame within 3 seconds max. Flame travel 3" min.	Pass	Pass

## 5.0 Conclusion

Glenair's GS22759-32-22 wire meets all performance requirements of AS22759/32 in 20-26 AWG range. GS22759-44, GS22759-45, and GS22759-46 wires meet AS22759/44, AS22759/45, and AS22759/46 in 20-26 AWG range requirements by similarity.