




SERIES 70 10K PSI / 700 BAR / 7000 M



SeaKing™ High-Pressure Subsea Connectors, Cables, and PBOF Assemblies

7071-1659 Flange Connector Receptacle/Bulkhead Connector Receptacle COAX Cable Assembly

SeaKing CCP - How To Order				
Sample Part Number	7071-1658	-6	N	-12
Product Series	7071-1658 = Cable Connector Plug COAX Cable Assembly, 50 Ohm			
Shell Style	6 = FCR (Flange Connector Receptacle) 7 = BCR (Bulkhead Connector Receptacle)			
Key Position	A, B, C, N = Normal			
"L" Length In Inches	Consult Factory for Lengths Greater than 360 inches (30ft)			



NOTES

100% Electrical test for continuity, shorts, dielectric withstanding voltage (at 500 VAC or DC equivalent) and insulation resistance (500 VDC) IAW IPC/WHMA-A-620.

See component drawings for additional dimensions, materials and finishes.

Unit pack: 1 ea. in poly bag, heat-sealed. Include dust cap. Tag and bag per illustration. For FCR assemblies flange shall be packaged with cable assembly (not installed) in same poly bag. End user installation required.

SUBSEA/DEEPWATER: SEAKING™

