




SERIES 70 10K PSI / 700 BAR / 7000 M



SeaKing™ High-Pressure Subsea Connectors, Cables, and PBOF Assemblies

7071-1658 Cable Connector Plug COAX Cable Assembly

SeaKing CCP - How To Order			
Sample Part Number	7071-1658	-N	-12
Product Series	7071-1658 = Cable Connector Plug COAX Cable Assembly, 50 Ohm		
Key Position	A, B, C, N = Normal		
"L" Length In Inches	Consult Factory for Lengths Greater than 360 inches (30ft)		



NOTES

100% Electrical test for continuity, shorts, dielectric withstanding voltage (at 500 vac or dc equivalent) and insulation resistance (500 vdc) law ipc/whma-a-620.

100% Hydrostatic isolation test (capped pressure test):

Cycles total: 2 cycles at 5 minutes, 1 cycle at 30 minutes

Min test pressure: 1.1x assy pressure rating (i.E. 11000 psi or 1x10000) assy pressure rating: 10,000 psi

Unit pack: 1 ea.

For connector dimensions, materials, finishes, and key positions, refer to individual component drawings

SUBSEA/DEEPWATER: SEAKING™

