





10K PSI / 700 BAR / 7000M SuperG66™ High-Pressure, Dry-Mate Subsea Connectors



G6601 moulded straight assembly cable connector plug



SuperG66™ Xxxxx - How To Order						
Sample Part Number	G6601	-XXXX	-XXXX	.X	-XX	-CODE SHEET
Series	66 Connector Series Moulded Straight Assembly Cable Connector Plug					
Shell Size/Insert Arrangement	See Contact Configurations Table					
Cable Length	Replace xxxx with 0004 = 4 ft					
Inch Increments	Either 3, 6 or 9 Inches Omit for Whole Feet Lengths					
Material Option	Omit For Standard Connector (Stainless Steel) PK = Peek Barrel B = Brass Barrel					
Code Sheet	For Non-Standard Cable (Omit for Standard Wiring) Consult Factory for Code Sheet Number					



MATERIALS / FINISH

- Shell - 316L stainless steel / passivation.
- Coupling nut - stainless steel / protective coating
- Insert - neoprene
- Contacts - copper alloy / gold over nickel
- Potting cap - PEEK
- Overmould - polyurethane or neoprene

NOTES

- All contacts / pin configurations suit 16 AWG wire.
- Unless requested otherwise, all moulded connectors are supplied with SOOW neoprene type cable as standard.

Dimensions		
Shell Size	Dim A ±.006 (0.15)	Dim B ±.010 (0.25)
15	1.070 (27.18)	1.000 (25.40)
20	1.450 (36.85)	1.380 (35.05)

Contact Configurations (Face View of Plug Connector)				
Shell Size 15 1503* 3 x #12	Shell Size 20 2003** 3 x #10	Shell Size 20 2004*** 4 x #10	Shell Size 20 2008** 8 x #16	Shell Size 20 2013** 13 x #16

* Unique Glenair contact configuration.

** Industry standard contact configuration.

*** Unique Glenair contact configuration, <50bar applications.

SUBSEA/DEEPWATER: SUPERG66™