




10K PSI / 700 BAR / 7000M SuperG66™ High-Pressure, Dry-Mate Subsea Connectors



G66R2 moulded right angle assembly cable connector receptacle




SuperG66™ Connector Receptacle - How To Order						
Sample Part Number	G66R2	-XXXX	-XXXX	.X	-XX	-CODE SHEET
Series	66 Connector Series Moulded Right Angle Assembly Cable Connector Receptacle					
Shell Size/Insert Arrangement	See Contact Configurations Table					
Cable Length	Replace XXXX with 0004 = 4 Ft					
Inch Increments	Either 3, 6 or 9 Inches Omit for Whole Feet Lengths					
Material Option	Omit For Standard Connector (Stainless Steel) PK = Peek Barrel B = Brass Barrel					
Code Sheet	For Non-Standard Cable (Omit for Standard Wiring) Consult Factory for Code Sheet Number					

MATERIALS / FINISH

- Shell - 316L stainless steel / passivation.
- Coupling nut - stainless steel / protective coating
- Insert - neoprene
- Contacts - copper alloy / gold over nickel
- Potting cap - PEEK
- Overmould - polyurethane or neoprene


NOTES

- Mating cycles - 500
- Op. Temp. -20°C / +90°C
- Voltage rating - 600VDC/440VAC
- Current rating (max.) - 5 to 18 amps dependent on cable and conductor size
- All contacts / pin configurations suit 16 AWG wire.
- Unless requested otherwise, all moulded connectors are supplied with SOOW neoprene type cable as standard.



Dimensions		
Shell Size	Dim A ±.006 (0.15)	Dim B ±.010 (0.25)
15	.930 (23.62)	.945 (24.00)
20	1.250 (31.76)	1.102 (27.99)

Contact Configurations (Face View of Receptacle Connector)



* Unique Glenair contact configuration.

** Industry standard contact configuration.

*** Unique Glenair contact configuration, <50bar applications.