




10K PSI / 700 BAR / 7000M

SuperG66™ High-Pressure, Dry-Mate Subsea Connectors



G66D2 dummy sealing cable connector receptacle



SuperG66™ Connector Receptacle - How To Order						
Sample Part Number	G66D2	-XXXX	-0001	-XX	-XX	-XX
Series	66 Connector Series Dummy Sealing Cable Connector Receptacle					
Shell Size/Insert Arrangement	See Contact Configurations Table					
Lanyard Length	E.G. 0001 = 1 Foot Lanyard (Standard) -0000 = No Lanyard					
Material Option	Omit for Standard Connector (Stainless Steel) PK = Peek Coupling Nut and Barrel B = Brass Coupling Nut and Barrel Contact Glenair for Additional Options					
Attachment Type	See Attachment Type Table					
Dash No.	See Eyelet Diameter Table					

Attachment Type	
Sym.	Attachment
1	Stainless Steel Rope with Wire Loop
2	Polyester Rope with Wire Loop
3	Stainless Steel Rope with Lug
4	Polyester Rope with Lug

Eyelet Diameter	
Dash No.	D Dia.
A	MS [10-32] Size 15
B	M8 [5/16] Size 32


Standard ø6.5 (M6) supplied if dash number omitted.

MATERIALS / FINISH

- Shell - 316L stainless steel / passivation
- Insert / plug - neoprene

NOTES

- Wire loops are sized to fit over cable whips
- Standard terminal lug diameter size is 6.6mm suitable for M6 or 1/4" fasteners
- Lug, crimp and screw material stainless steel as standard. Contact Glenair for custom options



Dimensions		
Shell Size	Dim A ±.006 (0.15)	Dim B Nom
15	.850 (21.59)	1.447 (36.75)
20	1.250 (31.75)	1.500 (38.10)

Contact Configurations (Face View of Receptacle Connector)				
Shell Size 15 1503* 3 x #12	Shell Size 20 2003** 3 x #10	Shell Size 20 2004*** 4 x #10	Shell Size 20 2008** 8 x #16	Shell Size 20 2013** 13 x #16

* Unique Glenair contact configuration.

** Industry standard contact configuration.

*** Unique Glenair contact configuration, <50bar applications.