

GS22759-43

Silver-Coated Copper Wire, Dual-Wall with Modified XL-ETFE Insulation


NOTES

1. Wire is made in accordance with AS22759/43.
2. Conductor is silver-coated copper per AS29606.
3. Insulation is crosslinked modified ETFE
4. Wire maximum continuous temperature rating is 200°C (392°F).
5. Voltage rating is 600 volts (RMS) at sea level.
6. Color code per MIL-STD-681. See MIL-STD-681 for additional wire color codes. Jacket color code must be white (9) if adding color stripes.
7. Consult factory for custom stripe color order.

HOW TO ORDER

Sample Part Number	GS22759-43	-24	-9	0	1	2
Basic Part Number	GS22759-43					
Wire Size	See Table I					
Jacket Color Code	See Table II					
First Stripe Color Code	(Omit for none) See Table II					
Second Stripe Color Code	(Omit for none) See Table II					
Third Stripe Color Code	(Omit for none) See Table II					

Primary Insulation - Crosslinked, Extruded, Modified ETFE



Jacket - Crosslinked, Extruded, Modified ETFE

Table II: Jacket and Stripe Color Codes

Color code	Color
0	Black
1	Brown
2	Red
3	Orange
4	Yellow
5	Green
6	Blue
7	Violet
8	Gray
9	White

Table I: Part Number and Wire Specifications

Part Number	Wire Size	Stranding (Number of strands x AWG of strands)	Diameter of stranded conductor (inches)		Finished Wire		
			min.	max.	Resistance at 20° C (68° F) (Ohms/1000 ft) max.	Diameter (inches)	Weight (lbs/1000 ft) max.
GS22759-43-26-*	26	19 X 38	0.0175	0.0194	38.4	.040±.002	1.7
GS22759-43-24-*	24	19 X 36	0.0225	0.0244	24.3	.045±.002	2.3
GS22759-43-22-*	22	19 X 34	0.0285	0.0304	15.1	.050±.002	3.3
GS22759-43-20-*	20	19 X 32	0.0365	0.0384	9.19	.058±.002	4.7
GS22759-43-18-*	18	19 X 30	0.0455	0.0484	5.79	.070±.003	7.2
GS22759-43-16-*	16	19 X 29	0.0515	0.0544	4.52	.077±.003	9.0
GS22759-43-14-*	14	19 X 27	0.0645	0.0684	2.88	.094±.003	13.8
GS22759-43-12-*	12	37 X 28	0.0835	0.0874	1.90	.111±.003	20.5
GS22759-43-10-*	10	37 X 26	0.106	0.112	1.19	.134±.004	32.4
GS22759-43-8-*	8	133 x 29	0.158	0.169	0.658	.195±.008	65.0