GS22759-48

Silver-Coated Copper Wire with Lightweight XL-ETFE Insulation

NOTES

1. Wire is made in accordance with AS22759/48.
2. Conductor is 80 microinch silver-coated copper per SAE-AS29606.
3. Insulation is crosslinked modified ETFE
4. Wire maximum continuous temperature rating is 200°C (392°F).
5. Voltage rating is 600 volts (RMS) at sea level.
6. Color code per MIL-STD-681. See MIL-STD-681 for additional wire color codes. Jacket color code must be white (9) if adding color stripes.
7. Consult factory for custom stripe color order.

HOW TO ORDER						
Sample Part Number	**GS22759-48**	**-24**	**-9**	**0**	**1**	**2**

Basic Part Number	**GS22759-48**
Wire Size	**30**, **28**, **26**, **24**, **22**, **20**, **18**, **16**, **14**, **12** See Table I
Jacket Color Code	**0**, **1**, **2**, **3**, **4**, **5**, **6**, **7**, **8**, **9** See Table II
First Stripe Color Code	Color Codes **0**, **1**, **2**, **3**, **4**, **5**, **6**, **7**, **8**, **9** (Omit for none) See Table II
Second Stripe Color Code	Color Codes **0**, **1**, **2**, **3**, **4**, **5**, **6**, **7**, **8**, **9** (Omit for none) See Table II
Third Stripe Color Code	Color Codes **0**, **1**, **2**, **3**, **4**, **5**, **6**, **7**, **8**, **9** (Omit for none) See Table II



Table II: Jacket and Stripe Color Codes

Color code	Color
0	Black
1	Brown
2	Red
3	Orange
4	Yellow
5	Green
6	Blue
7	Violet
8	Gray
9	White

Table I: Part Number and Wire Specifications

Part Number	Wire Size	Stranding (Number of strands x size gage of strands)	Diameter of stranded conductor (inches)		Finished Wire		
			min	max	Resistance at 20° C (68° F) (Ohms/ 1000 ft) max	Diameter (inches)	Weight (lbs/1000 ft) max
GS22759-48-30-*	30	7 X 38	0.0105	0.0124	100.7	.024±.002	.66
GS22759-48-28-*	28	7 X 36	0.0135	0.0154	63.8	.027±.002	.91
GS22759-48-26-*	26	19 X 38	0.0175	0.0194	38.4	.032±.002	1.4
GS22759-48-24-*	24	19 X 36	0.0225	0.0244	24.3	.037±.002	2.0
GS22759-48-22-*	22	19 X 34	0.0285	0.0304	15.1	.043±.002	2.8
GS22759-48-20-*	20	19 X 32	0.0365	0.0384	9.19	.050±.002	4.3
GS22759-48-18-*	18	19 X 30	0.0455	0.0484	5.79	.060±.002	6.5
GS22759-48-16-*	16	19 X 29	0.0515	0.0544	4.52	.068±.002	8.3
GS22759-48-14-*	14	19 X 27	0.0645	0.0684	2.88	.085±.003	13.0
GS22759-48-12-*	12	37 X 28	0.0835	0.0874	1.90	.103±.003	19.7

© 2026 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324 •
Glenair Signature Wire and Cable · Dimensions in Inches (millimeters) are subject to change without notice.

Rev. 10.30.26