

# HIGH-AVAILABILITY · NO MOQ

## Aerospace-Grade Hook-Up Wire



GS22759-55

Silver-Coated Lightweight Extra High-Strength Copper Conductor, Crosslinked Modified ETFE

### FEATURES

- Order with Mod Code 1304B for wire supplied with 80 microinch-thick silver plating for red plague mitigation in space applications

### NOTES

- Wire is made in accordance with AS22759/55.
- Conductor silver-coated high-strength copper per AS29606
- Insulation is crosslinked modified ETFE
- Voltage rating is 600 VRMS at sea level
- Temperature rating is 200°C (392°F) max. continuous
- Color code per MIL-STD-681. See MIL-STD-681 for additional wire color codes. Jacket color code must be white (9) if adding color stripes.
- Consult factory for custom stripe color order.

HOW TO ORDER						
Sample Part Number	GS22759-55	-24	-9	0	1	2
Basic Part Number	GS22759-55					
Wire Size	See Table I					
Jacket Color Code	See Table II					
First Stripe Color Code	(Omit for none) See Table II					
Second Stripe Color Code	(Omit for none) See Table II					
Third Stripe Color Code	(Omit for none) See Table II					




Table I: Part Number and Wire Specifications							
Part Number	Wire Size	Stranding (Number of strands x size gage of strands)	Diameter of stranded conductor (inches)		Finished Wire		
			min	max	Resistance at 20° C (68° F) (Ohms/1000 ft) max	Diameter (inches)	Weight (lbs/1000 ft) max
GS22759-55-30-*	30	7 X 38	0.0105	0.0124	117.4	.032±.002	1.0
GS22759-55-28-*	28	7 X 36	0.0135	0.0154	74.4	.035±.002	1.3
GS22759-55-26-*	26	19 X 38	0.0175	0.0204	44.8	.040±.002	1.7
GS22759-55-24-*	24	19 X 36	0.0225	0.0244	28.4	.045±.002	2.3
GS22759-55-22-*	22	19 X 34	0.0285	0.0314	17.5	.050±.002	3.3
GS22759-55-20-*	20	19 X 32	0.0365	0.0395	10.7	.058±.002	4.8

Table II: Jacket and Stripe Color Codes

Color code	Color
0	Black
1	Brown
2	Red
3	Orange
4	Yellow
5	Green
6	Blue
7	Violet
8	Gray
9	White