

FLIGHT HERITAGE

SPACE MECHANISMS

Release Mechanisms · Blind Mate (ASF) Connectors · Lanyard-Release Connectors

AUGUST 2017




Commander Ed White on the
first American spacewalk, 1965

SPACE PROVEN Interconnect Technologies

We like to begin every discussion of Glenair's proven-performance space-grade products with the golden umbilical life support cable used by Commander Ed White in the first American space walk in 1965. This was a complex cable assembly with an exacting set of performance requirements. Even though this application is now over 50 years old, it still reflects Glenair's design and fabrication expertise and that we have been a go-to supplier for the space industry for over 5 decades.

Today we continue to manufacture a broad range of high-performance cables and components for space—from our innovative line of non-pyrotechnic HDRMs to high-reliability assisted separation force connectors. Glenair's proven space flight heritage includes interconnect and electromechanical technology on dozens of robotic spacecraft, including orbiters, landers, and rovers.



Many customers of discrete HDRM technology look to Glenair for the turnkey supply of interconnect wire and cabling. Non-pyrotechnic separation nuts utilize EMI shielded harness assemblies to supply primary and redundant initiation energy to the split spool actuator, and to transmit telemetry data from release sensors. Glenair operates the largest and best equipped wire harness assembly shop in the mission-critical interconnect industry and has supplied countless turnkey space-grade cable assemblies of this type.




PROVEN PERFORMANCE IN SPACE

- The "Golden Umbilical" life-support cable
- JPL Mars probes (orbiters, landers, and the Curiosity rover)
- AIRS satellite
- Gravity Probe mission
- Titan II launch vehicles
- EADS Astrium
- ESA Ariane 5
- Countless others

FLIGHT HERITAGE Space Mechanisms




For interconnection and release applications Table of contents



Pyrotechnic-Free Hold-Down and Release Mechanisms

Non-explosive light, medium, and heavy-duty preload HDRMs, pin pullers and pin pushers for spacecraft, satellite, and payload hold-down and release. Special-purpose ultra-lightweight small form-factor split-spool release mechanisms for near-simultaneous CubeSat and NanoSat deployment as well as for antenna, solar array, reflector, boom, and mast release.



Series 28 HiPer-D Advanced Performance M24308 intermateable D-sub

Small form factor CubeSat applications typically use dispenser canisters for deployment. D-sub miniature cable assemblies are used for activation of the dispenser hold-down release mechanism, interconnection of the door status sensor, and in some cases direct signal interconnection to the satellite. Series 28 HiPer-D machined shells deliver improved shock and vibration performance, advanced electromagnetic compatibility and are rated to 200° C.



Blind-Mate, Float Mount, and Assisted Release (ASF) Connectors

Space-grade circular blind-mate connectors IAW MIL-DTL-38999 for use in interconnection and separation of instrumentation panels, satellites, scientific research payloads, and other release applications.



Lanyard-Release Quick-Disconnect Connectors IAW AS81703 Series 3

For mission-critical interconnection and release of launch and payload systems that depend on reliable, jam-free mating and disengagement.



Space-Grade Clean Room Manufacturing, Test, and Certification / Screening Capabilities

Complete in-house capabilities including clean room manufacturing, NASA/ESA screening and outgassing, qualification testing and readiness programs.




NASA NanoRack CubeSats deployed from the International Space Station. The ISS solar array panels provide the backdrop.

SERIES 06

Pyrotechnic-Free Hold-Down and Release Mechanisms

High-reliability, non-explosive (split-spool) separation nuts and electromechanical release mechanisms for dependable preload stowage and release of deployable space systems

Glenair HDRMs are optimized for foolproof near-simultaneous release reliability with built-in mechanical and electrical redundancy. The planned release of deployable satellites and structures is activated by a pre-determined value of electrical current to a fuse-wire system which causes the wire to break under tension and allows a pre-loaded mechanical bolt to actuate. Glenair's line of low-shock, redundant and non-redundant space mechanisms includes both HDRM devices as well as a family of pin pushers and pin pullers. Customer-defined electrical initiation (with no amperage max limit), as well as housing and mounting configurations are available. Consult factory for specific device TR level and qualification test reports.



Glenair pyrotechnic-free release mechanisms offer near-simultaneous release time, low shock, with relatively low power input requirements. The Glenair family of HDRMs includes separation nuts, HDRMs, pin pushers, and pin pullers which deliver a higher preload carrying capacity in comparison to similar devices.

- Pyrotechnic-free alternative for single-event release of deployable space systems
- Configurable electrical initiation with no (amperage) upper limit
- Near-simultaneous release dependent on temperature and power
- User-serviceable and refurbishable units
- Standard catalog as well as custom designs
- Not susceptible to transient and noise (EMI/EMP/ESD/RFI) inputs
- Extended temperature ranges: -150°C to +150°C

SERIES 06

Hold-Down and Release Mechanisms

Technology Overview



A

FUSE-WIRE TECHNOLOGY Glenair non-pyrotechnic hold-down and release mechanism technology is based on a fusible wire-actuated separation nut design, increasingly popular for its reliability and low-shock release action. Fuse wire-actuated nut technology has the added benefit of being partially reusable and refurbishable post-deployment.

LEGACY HDRM DEVICES A broad range of hold down release mechanism technologies have been historically used to deploy satellites and appendages (solar arrays, antenna reflectors, radiators, instruments, doors, sensors, booms, and so on) in space. Most of these technologies relied on non-reusable (explosive/pyrotechnic) designs that suffered from a broad range of deficiencies, including susceptibility to electromagnetic interference, problematic synchronization of release with mission requirements, high-shock release action, and significantly, the inability to reuse or refurbish the device during test. Glenair HDRMs solve every one of these problems.

HDRM FUNCTIONALITY The Glenair family of HDRMs, pin pullers and pin pushers are non-pyrotechnic release mechanisms with the ability to carry defined tensile preloads until fuse wire release is initiated with an electrical current applied to the actuation circuit, at which time the restraint wire—wrapped under tension—unwinds, initiating actuation and releasing the associated preload. Any potential energy release during actuation is fully countered by the measured delivery system.

KEY COMPONENTS All three key components of Glenair HDRMs (preloading assembly, release actuator, and load-carrying structure) may be packaged according to specific customer requirements including connectorization in place of wire leads. Electrical initiation current level is also configurable, with no amperage upper limit. Packaging options include cylindrical or rectangular housings, lightweight materials, unique shapes and profiles, non-standard mounting dimensions and more.

PERFORMANCE Glenair HDRMs, pin pullers and pushers are immune to all forms of EMI or ESD, and capable of easily sustaining significant defined preloads—with release deployment times comparable to conventional explosive actuators. Near-simultaneous release of multiple HDRMs is ± 7 msec with 3.5A supplied as a nominal current (within the same temperature range). Improved simultaneity is achieved with the application of higher-current initiation.

FLIGHT HERITAGE Glenair HDRMs have achieved flight heritage and are now marketed by the company with TRLs of 9. Consult the factory for test reports and TRL qualification levels for specific devices.

DEPLOYMENT APPLICATIONS




Solar Arrays



Booms and Masts



Antennas



Reflectors

SCALABLE DESIGNS: FROM CUBESATS TO 20,000 POUND PAYLOADS

- Fuse-wire based technology
- Redundant or non-redundant actuation circuit
- Space-rated and screened materials
- Configurable electrical initiation with no (amperage) upper limit



Catalog and custom solutions available, including redundant- and non-redundant HDRMs, power draw resistor-equipped units, and connectorized solutions with space-grade micro miniature Series 806 Mil-Aero connectors.

061-002

Light-duty hold-down release mechanism

**5 lb. (Delrin) or 20 lb. (Stainless Steel) release preload
Non-redundant circuit**




A

NON-REDUNDANT CIRCUIT HOLD DOWN RELEASE MECHANISM, LIGHT-DUTY



| How To Order | | | |
|----------------------------|--|------|---|
| Sample Part No. | 061 | -002 | S |
| Basic Part No. | Light-Duty HDRM | | |
| Dash No. | Non-Redundant Circuit | | |
| Release Component Material | S - Stainless Steel D - Delrin | | |



NOTES


- Unit is identified with Glenair name, CAGE code, part number, and date code, space permitting.
- Release preload:
Stainless steel release component: max. limit 20 lbs (89 N)
Delrin release component: max. limit 5 lbs (22 N)
- Full qualification pending
- Reference Glenair P/N 060-102 for refurbishment initiator
- Metric threads available, consult factory for options

| Physical characteristics | |
|--|--|
| Mass | 9 grams nominal weight |
| Release component thread | 0.112-40 UNC-3B* |
| Material list | IAW MSFC-STD-3029 |
| Epoxy | Outgassing requirements per GSC19384 |
| Device features | |
| Field refurbishable | Initiator can be replaced in less than 15 minutes by trained personnel |
| Packaging | External housing typically supplied with two mounting points. Custom housings and mountings available |
| Connectorization | Standard design supplied with wire inputs. Consult factory for connectorization options |
| Scalable bolt size | Bolt size determines preload and can be scaled to accommodate a wide range of requirements |
| *Size callout based on the bolt size to be used. Metric thread also available. Consult factory for qualification test report. | |

Light-duty hold-down release mechanism



5 lb. (Delrin) or 20 lb. (Stainless Steel) release preload
Actuation curve



061-014

Light-duty hold-down release mechanism


24 lb. release preload

Non-redundant circuit • side load



A


NON-REDUNDANT CIRCUIT HOLD DOWN RELEASE MECHANISM, LIGHT DUTY



| How To Order | | |
|-----------------|----------------------------------|------|
| Sample Part No. | 061 | -014 |
| Basic Part No. | Light-Duty HDRM | |
| Dash No. | Side Load, Non-Redundant Circuit | |

INITIATION CIRCUIT
WIRES IAW MS22759/44-20-0.
AND MS22759/44-20-2.
LENGTH = 18 INCHES MIN.

| PART NUMBER DEFINITION | | |
|------------------------|-------------|------------------------------------|
| DESIGNATOR | PART NUMBER | THREAD |
| BLANK | 061-014 | 112-40 UNC-3B .15 MIN THD DEPTH |
| M3 | 061-014M3 | M3 X 0.5 HH 3.8 MIN THD DEPTH |



NOTES


- Unit is identified with Glenair name, CAGE code, part number, and date code, space permitting. Primary initiation circuit identified with "P" and redundant with "R".
- Release preload: 24 lbs. (106.7N)
- Full qualification complete, consult factory for test report.
- Reference Glenair P/N 060-114 for refurbishment initiator
- Metric threads available, consult factory for options

| Physical characteristics | |
|---|---|
| Mass | 20.6 grams approximate weight |
| Release component thread | 0.115-40 UNC-3B* |
| Material list | IAW MSFC-STD-3029 |
| Device features | |
| Field refurbishable | Initiator can be replaced in less than 15 minutes by trained personnel |
| Packaging | External housing typically supplied with two mounting points. Custom housings and mountings available |
| Connectorization | Standard design supplied with wire inputs. Consult factory for connectorization options |
| Scalable bolt size | Bolt size determines preload and can be scaled to accommodate a wide range of requirements |
| *Size callout based on the bolt size to be used. Metric thread also available. Consult factory for qualification test report. | |

Light-duty hold-down release mechanism

24 lb. release preload

Actuation curve



| Qualification Test Parameters | |
|-------------------------------|--|
| Random Vibration | 28.2 GRMS |
| Shock Input | 442 Gs max |
| Thermal Vacuum | 3 cycles -65° C to +70° C, 1.0×10^{-5} torr |
| Life Cycle | 6 releases on one unit |


061-007

Medium-duty hold-down release mechanism



600 lb. release preload
Redundant circuit



REDUNDANT CIRCUIT HOLD DOWN RELEASE MECHANISM, MEDIUM-DUTY



| How To Order | | |
|-----------------|-------------------|------|
| Sample Part No. | 061 | -007 |
| Basic Part No. | Medium-Duty HDRM | |
| Dash No. | Redundant Circuit | |



| Physical characteristics | |
|--|---|
| Mass | 38.5 grams approximate weight |
| Release component thread | 0.138-32 UNJC-3B* |
| Material list | IAW MSFC-STD-3029 |
| Epoxy | Outgassing requirements per GSC19384 |
| Device features | |
| Redundant initiation | 2 initiation points |
| Field refurbishable | Initiator can be replaced in less than 15 minutes by trained personnel |
| Reliability prediction | 0.9999994 (based off scaled design) |
| Packaging | External housing typically supplied with two mounting points. Custom housings and mountings available |
| Connectorization | Standard design supplied with wire inputs. Connectorized versions available |
| Scalable bolt size | Bolt size determines preload and can be scaled to accommodate a wide range of requirements |
| *Size callout based on the bolt size to be used. Metric thread also available. Consult factory for qualification test report. | |

NOTES

- Unit is identified with Glenair name, CAGE code, part number, and date code, space permitting. Primary initiation circuit identified with "P" and redundant with "R".
- Release preload 600 lbs. (2.67 kN)
- Qualification report available upon request.
- Reference Glenair P/N 060-107 for refurbishment initiator
- Metric threads available, consult factory for options


061-007

Medium-duty hold-down release mechanism



**600 lb. release preload
Actuation curve**



A



| Tested Capability for 061-007 | |
|------------------------------------|--|
| Nominal Release Preload | 600 pounds |
| Electrical Resistance | 0.8 to 1.5 ohms |
| Sine Vibration 3 orthogonal axes | 25 G's |
| Random Vibration 3 orthogonal axes | 50.9 G _{rms} |
| Actuation Time | Under 60 ms @3.5 Amps |
| Source Shock | Under 150 G's @600 pounds |
| Life Test | 10 refurbishments during qualification and an expected continued usage |
| Temperature | -150°C to +150°C released in a vacuum (1x10 ⁻⁶ Torr) |




061-025

Medium-duty hold-down release mechanism

600 lb. release preload
Redundant circuit, metric thread



REDUNDANT CIRCUIT HOLD DOWN RELEASE MECHANISM, MEDIUM DUTY



NOTES

- Unit is identified with Glenair name, CAGE code, part number, and date code, space permitting. Primary initiation circuit identified with "P" and redundant with "R".
- Release preload 600 lbs. (2.67 kN)
- Qualification report for 061-007 available upon request.
- Reference Glenair P/N 060-125 for refurbishment initiator
- Nominal actuation current
3.5 Amps

| Physical characteristics | |
|--------------------------|---|
| Mass | 40.7 grams nominal weight |
| Release component thread | M4 x 0.7-6H* |
| Material list | IAW MSFC-STD-3029 |
| Epoxy | Outgassing requirements per GSC19384 |
| Device features | |
| Redundant initiation | 2 initiation points |
| Field refurbishable | Initiator can be replaced in less than 15 minutes by trained personnel |
| Packaging | External housing typically supplied with two mounting points. Custom housings and mountings available |
| Connectorization | Standard design supplied with wire inputs. Connectorized versions available |
| Scalable bolt size | Bolt size determines preload and can be scaled to accommodate a wide range of requirements |


*Size callout based on the bolt size to be used.
 Consult factory for qualification test report.

Medium-duty hold-down release mechanism





**1000 lb. release preload
Redundant circuit**



REDUNDANT CIRCUIT HOLD DOWN RELEASE MECHANISM, MEDIUM-DUTY



| How To Order | | |
|-----------------|-------------------|------|
| Sample Part No. | 061 | -006 |
| Basic Part No. | Medium-Duty HDRM | |
| Dash No. | Redundant Circuit | |



| Physical characteristics | |
|--|---|
| Mass | 65.1 grams approximate weight |
| Release component thread | 0.190-32 UNJF-3B* |
| Material list | IAW MSFC-STD-3029 |
| Epoxy | Outgassing requirements per GSC19384 |
| Device features | |
| Redundant initiation | 2 initiation points |
| Field refurbishable | Initiator can be replaced in less than 15 minutes by trained personnel |
| Reliability prediction | 0.9999994 (based off scaled design) |
| Packaging | External housing typically supplied with two mounting points. Custom housings and mountings available |
| Connectorization | Standard design supplied with wire inputs. Connectorized versions available |
| Scalable bolt size | Bolt size determines preload and can be scaled to accommodate a wide range of requirements |
| *Size callout based on the bolt size to be used. Metric thread also available. Consult factory for qualification test report. | |

NOTES

- Unit is identified with Glenair name, CAGE code, part number, and date code, space permitting. Primary initiation circuit identified with "P" and redundant with "R".
- Release preload 1000 lbs. (4.5 kN) on similar model, contact factory
- Qualification complete
- Reference Glenair P/N 060-106 for refurbishment initiator
- Metric threads available, consult factory for options

061-006


Medium-duty hold-down release mechanism

1000 lb. release preload

Actuation curve



A




Medium-duty hold-down release mechanism


**1000 lb. release preload
Redundant circuit, metric thread**



REDUNDANT CIRCUIT HOLD DOWN RELEASE MECHANISM, MEDIUM DUTY



| How To Order | | |
|-----------------|-------------------|------|
| Sample Part No. | 061 | -024 |
| Basic Part No. | Medium Duty HDRM | |
| Dash No. | Redundant Circuit | |



NOTES

- Unit is identified with Glenair name, CAGE code, part number, and date code, space permitting. Primary initiation circuit identified with "P" and redundant with "R".
- Release preload 1000 lbs. (4.5 kN) on similar model, contact factory
- Similar model qualification complete, consult factory for details
- Reference Glenair P/N 060-124 for refurbishment initiator

| Physical characteristics | |
|--------------------------|---|
| Mass | 65.2 grams approximate weight |
| Release component thread | M5x0.8-6H* |
| Material list | IAW MSFC-STD-3029 |
| Epoxy | Outgassing requirements per GSC19384 |
| Device features | |
| Redundant initiation | 2 initiation points |
| Field refurbishable | Initiator can be replaced in less than 15 minutes by trained personnel |
| Reliability prediction | 0.9999994 |
| Packaging | External housing typically supplied with two mounting points. Custom housings and mountings available |
| Connectorization | Standard design supplied with wire inputs. Connectorized versions available |
| Scalable bolt size | Bolt size determines preload and can be scaled to accommodate a wide range of requirements |

*Size callout based on the bolt size to be used.
Consult factory for qualification test report.

061-005


Medium-duty hold-down release mechanism

2500 lb. release preload
Redundant circuit







A

ELECTRICALLY REDUNDANT HOLD DOWN RELEASE MECHANISM, MEDIUM-DUTY



| How To Order | | |
|-----------------|-------------------|------|
| Sample Part No. | 061 | -005 |
| Basic Part No. | Medium-Duty HDRM | |
| Dash No. | Redundant Circuit | |



NOTES

- Unit is identified with Glenair name, CAGE code, part number, and date code, space permitting. Primary initiation circuit identified with "P" and redundant with "R".
- Release preload 2500 lbs. (11.1 kN)
- Reference Glenair P/N 060-105 for refurbishment initiator
- Nominal actuation current
3.5 Amps
- Qualification test report available
- See 061-023 for metric thread version
- Mechanical release version available, consult factory

| Physical characteristics | |
|---|---|
| Mass | 85.1 grams nominal weight |
| Release component thread | 0.190-32 UNJF-3B* |
| Material list | IAW MSFC-STD-3029 |
| Epoxy | Outgassing requirements per GSC19384 |
| Device features | |
| Redundant initiation | 2 initiation points |
| Field refurbishable | Initiator can be replaced in less than 15 minutes by trained personnel |
| Reliability prediction | 0.999994 |
| Packaging | External housing typically supplied with two mounting points. Custom housings and mountings available |
| Connectorization | Standard design supplied with wire inputs. Connectorized versions available |
| Scalable bolt size | Bolt size determines preload and can be scaled to accommodate a wide range of requirements |
| *Size callout based on the bolt size to be used. Metric thread also available. Consult factory for qualification test report. | |

061-005


Medium-duty hold-down release mechanism

2500 lb. release preload



Summary of qualification test data



A



| Tested Capability for 061-005 | |
|------------------------------------|--|
| Nominal Release Preload | 2,250 pounds |
| Proof Preload | 2,500 pounds |
| Ultimate Load | 3,250 pounds |
| Electrical Resistance | 1.5 ohms max |
| Sine Vibration 3 orthogonal axes | 25 G's |
| Random Vibration 3 orthogonal axes | 50.9 G _{rms} |
| Actuation Time | Under 100 ms @3.5 Amps |
| Shock Input | 2,849 G's |
| Source Shock | Under 300 G's @2,500 pounds |
| Life Test | 10 refurbishments during qualification and an expected continued usage |
| Temperature | -150°C to +150°C released in a vacuum (1x10 ⁻⁶ Torr) |
| Extended Preload | <4.0% loss |



061-023


Medium-duty hold-down release mechanism

2500 lb. release preload





Redundant circuit, metric thread



REDUNDANT CIRCUIT HOLD DOWN RELEASE MECHANISM, MEDIUM DUTY



| How To Order | | |
|-----------------|-------------------|------|
| Sample Part No. | 061 | -023 |
| Basic Part No. | Medium Duty HDRM | |
| Dash No. | Redundant Circuit | |



| Physical characteristics | |
|--|---|
| Mass | 84.3 grams nominal weight |
| Release component thread | M5x0.8-6H* |
| Material list | IAW MSFC-STD-3029 |
| Epoxy | Outgassing requirements per GSC19384 |
| Device features | |
| Redundant initiation | 2 initiation points |
| Field refurbishable | Initiator can be replaced in less than 15 minutes by trained personnel |
| Reliability prediction | 0.999994 |
| Packaging | External housing typically supplied with two mounting points. Custom housings and mountings available |
| Connectorization | Standard design supplied with wire inputs. Connectorized versions available |
| Scalable bolt size | Bolt size determines preload and can be scaled to accommodate a wide range of requirements |
| *Size callout based on the bolt size to be used. Standard thread also available. Qualification report for 061-005 available. | |

NOTES


- Unit is identified with Glenair name, CAGE code, part number, and date code, space permitting. Primary initiation circuit identified with "P" and redundant with "R".
- Release preload 2500 lbs. (11.1 kN)
- Reference Glenair P/N 060-123 for refurbishment initiator
- Nominal actuation current
3.5 Amps

Medium-duty hold-down release mechanism


**4000 lb. release preload
Redundant circuit**



REDUNDANT CIRCUIT HOLD DOWN RELEASE MECHANISM, MEDIUM DUTY



| How To Order | | |
|-----------------|-------------------|------|
| Sample Part No. | 061 | -022 |
| Basic Part No. | Medium Duty HDRM | |
| Dash No. | Redundant Circuit | |



NOTES

- Unit is identified with Glenair name, CAGE code, part number, and date code, space permitting. Primary initiation circuit identified with "P" and redundant with "R".
- Release preload 4000 lbs. (17.8 kN)
- Reference Glenair P/N 060-122 for refurbishment initiator
- Nominal actuation current 3.5 Amps
- Qualification test report available

| Physical characteristics | |
|--------------------------|---|
| Mass | 224 grams nominal weight |
| Release component thread | 0.250-28 UNJF-3 B* |
| Material list | IAW MSFC-STD-3029 |
| Epoxy | Outgassing requirements per GSC19384 |
| Device features | |
| Redundant initiation | 2 initiation points |
| Field refurbishable | Initiator can be replaced in less than 15 minutes by trained personnel |
| Packaging | External housing typically supplied with two mounting points. Custom housings and mountings available |
| Connectorization | Standard design supplied with wire inputs. Connectorized versions available |
| Scalable bolt size | Bolt size determines preload and can be scaled to accommodate a wide range of requirements |

*Size callout based on the bolt size to be used. Metric thread also available.
Consult factory for qualification test report.


061-022

Medium-duty hold-down release mechanism



**4000 lb. release preload
Redundant circuit**



A



| Tested capability for 061-022 | |
|-------------------------------------|--|
| Nominal Release Preload | 4,000 pounds |
| Electrical resistance | 0.5 to 1.5 ohms |
| Random vibration: 3 orthogonal axes | 50.9 G _{rms} |
| Sine vibration: 3 orthogonal axes | 25 G |
| Actuation time | Under 100 ms @ 3.5 Amps |
| Source shock | Under 200 G's @ 4,000 pounds |
| Life test | 10 refurbishments during qualification and an expected continued usage |
| Temperature | -150°C to +150°C released in a vacuum (1×10^{-5} Torr) |



Medium-duty hold-down release mechanism






**Low profile 300 lb. release preload
Non-redundant circuit**


NON-REDUNDANT CIRCUIT, HOLD DOWN RELEASE MECHANISM, MEDIUM DUTY




| How To Order | | |
|-----------------|-----------------------|------|
| Sample Part No. | 061 | -017 |
| Basic Part No. | Medium Duty HDRM | |
| Dash No. | Non-Redundant Circuit | |



INITIATION CIRCUIT,
WIRES IAW
M22759/44-20-0 AND
M22759/44-20-2.
LENGTH 18 INCHES MIN.
MEASURED FROM THE
OD 1.230



RELEASE FITTING DIMENSIONS



NOTES

1. Unit is identified with Glenair name, CAGE code, part number, and date code, space permitting.
2. Release preload 300 lbs. (1.33 kN)
3. Reference Glenair P/N 060-117 for refurbishment initiator
4. Qualification report available upon request

| Physical characteristics | |
|--------------------------|---|
| Mass | 33.1 grams approximate weight |
| Release component thread | .112-40 UNC-3B* |
| Material list | IAW MSFC-STD-3029 |
| Epoxy | Outgassing requirements per GSC19384 |
| Device features | |
| Field refurbishable | Initiator can be replaced in less than 15 minutes by trained personnel |
| Reliability prediction | 0.999999983 |
| Packaging | External housing typically supplied with two mounting points. Custom housings and mountings available |
| Connectorization | Standard design supplied with wire inputs. Connectorized versions available |
| Scalable bolt size | Bolt size determines preload and can be scaled to accommodate a wide range of requirements |

*Size callout based on the release fitting size to be used.
Consult factory for qualification test report.


061-017

Medium-duty hold-down release mechanism


Low profile 300 lb. release preload Summary of qualification test data




A



| Tested Capability for 061-005 (LoLa III) | |
|--|--|
| Nominal Release Preload | 300 pounds |
| Maximum Rated Release Preload | 375 pounds |
| Ultimate Load | 420 pounds |
| Electrical Resistance | 1.5 ohms max |
| Sine Vibration 3 orthogonal axes | 25 G's |
| Random Vibration 3 orthogonal axes | 50.9 G _{rms} |
| Actuation Time | Under 60 ms @3.5 Amps |
| Shock Input | 2,528 G's |
| Source Shock | Under 150 G's @300 pounds |
| Life Test | 10 refurbishments during qualification and an expected continued usage |
| Temperature | -150°C to +150°C released in a vacuum (1x10 ⁻⁶ Torr) |



— Current




Heavy-duty hold-down release mechanism


**5000 lb. release preload
Redundant circuit**



REDUNDANT CIRCUIT HOLD DOWN RELEASE MECHANISM, HEAVY-DUTY



| How To Order | | |
|-----------------|-------------------|------|
| Sample Part No. | 062 | -002 |
| Basic Part No. | Heavy-Duty HDRM | |
| Dash No. | Redundant Circuit | |



Available 069-201 mechanical release for use in place of refurbishment initiator. Consult factory for application notes.

| Physical characteristics | |
|--------------------------|---|
| Mass | 241 grams nominal weight with 18 inch lead wire included |
| Release component thread | 0.250-28 UNJF-3B* |
| Material list | IAW MSFC-STD-3029 |
| Epoxy | Outgassing requirements per GSC19384 |
| Device features | |
| Redundant initiation | 2 initiation points |
| Field refurbishable | Initiator can be replaced in less than 15 minutes by trained personnel |
| Reliability prediction | 0.9999995 |
| Packaging | External housing typically supplied with two mounting points. Custom housings and mountings available |
| Connectorization | Standard design supplied with wire inputs. Connectorized versions available |
| Scalable bolt size | Bolt size determines preload and can be scaled to accommodate a wide range of requirements |

*Size callout based on the bolt size to be used. Metric thread also available.
Complete test report available upon request




062-002

Heavy-duty hold-down release mechanism

5000 lb. release preload Summary of qualification test data



A



| Tested capability for 1/4 inch unit* | |
|--------------------------------------|--|
| Nominal Release Preload | 5,000 pounds |
| Proof Preload | 6,500 pounds |
| Ultimate Load | 8,000 pounds |
| Electrical resistance | 1.50 ohms Max |
| Random vibration: 3 orthogonal axes | 50.9 G _{rms} |
| Sine vibration: 3 orthogonal axes | 25 G's |
| Actuation time | Under 45 ms @ 3.5 Amps |
| Source shock | Under 625 G's @ 5,000 pounds |
| Life test | 10 refurbishments during qualification and an expected continued usage |
| Temperature | -150°C to +150°C released in a vacuum (1x10 ⁻⁶ Torr) |

*The size callout is based off the bolt size that is to be used. Metric thread can also be called out. Complete test report available upon request

NOTES


1. Unit is identified with Glenair name, CAGE code, part number, and date code, space permitting. Primary initiation circuit identified with "P" and redundant with "R".
2. Release preload 5000 lbs. (22.4 kN)
3. Reference Glenair P/N 060-202 for refurbishment initiator
4. Qualification test complete
5. Metric threads available, consult factory for options

Heavy-duty hold-down release mechanisms



**8750 lb. release preload
Redundant circuit**



ELECTRICALLY REDUNDANT HOLD DOWN RELEASE MECHANISM, HEAVY-DUTY



| How To Order | | |
|-----------------|-------------------|------|
| Sample Part No. | 063 | -001 |
| Basic Part No. | Heavy-Duty HDRM | |
| Dash No. | Redundant Circuit | |



| Physical characteristics | |
|--------------------------|--|
| Mass | 335 grams approximate weight |
| Bolt | 0.375-24 UNJF-3B* |
| Material list | IAW MSFC-STD-3029 |
| Epoxy | Outgassing requirements per GSC19384 |
| Device features | |
| Redundant initiation | 2 initiation points |
| Field refurbishable | Initiator can be replaced in less than 15 minutes by trained personnel |
| Reliability prediction | 0.99999975 |
| Packaging | External housing typically supplied with two mounting points. Custom housings and mountings available |
| Connectorization | Standard design supplied with wire inputs. Connectorized versions available |
| Scalable bolt size | Bolt size determines preload and can be scaled to accommodate a wide range of requirements |

*Size callout based on the bolt size to be used. Metric thread also available.
Consult factory for qualification test report.

NOTES

1. Unit is identified with Glenair name, CAGE code, part number, and date code, space permitting. Primary initiation circuit identified with "P" and redundant with "R".
2. Release preload: 8,750 lbs. (38.9 kN)
3. Test report available upon request
4. Reference Glenair P/N 060-301 for refurbishment initiator
5. Metric threads available, consult factory for options
6. Mechanical release version available, consult factory

063-001


Heavy-duty hold-down release mechanisms

8750 lb. release preload
Actuation curve



A

**Actuation Curve for 063-001 Mechanism
 (Nominal Conditions)**



| Tested Capability for 063-001 | |
|------------------------------------|--|
| Nominal Release Preload | 8,750 pounds |
| Proof load | 10,938 pounds |
| Ultimate preload | TBD |
| Electrical Resistance | 0.8 to 1.5 ohms |
| Sine Vibration 3 orthogonal axes | 25 G's |
| Random Vibration 3 orthogonal axes | 50.9 Grams |
| Actuation Time | Under 60 ms @ 3.5 Amps |
| Source Shock | Under 600 G's @ 8750 pounds |
| Life Test | 10 refurbishments during qualification and an expected continued usage |
| Temperature | -150°C to +150°C released in a vacuum (1×10^{-5} Torr) |

063-001



Heavy-duty hold-down release mechanisms

8750 lb. release preload

Redundant circuit



A




Heavy-duty hold-down release mechanisms




**12,500 lb. release preload
Redundant circuit**



ELECTRICALLY REDUNDANT HOLD DOWN RELEASE MECHANISM, HEAVY-DUTY



| How To Order | | |
|-----------------|-------------------|------|
| Sample Part No. | 064 | -001 |
| Basic Part No. | Heavy-Duty HDRM | |
| Dash No. | Redundant Circuit | |



Available 069-401 mechanical release for use in place of refurbishment initiator. Consult factory for application notes.

Full qualification pending. Design and dimensions are subject to change.

| Physical characteristics | |
|--------------------------|---|
| Mass | 870.4 grams nominal weight |
| Bolt | .500-20 UNJF-3B* |
| Material list | IAW MSFC-STD-3029 |
| Epoxy | Outgassing requirements per GSC19384 |
| Device features | |
| Redundant initiation | 2 initiation points |
| Field refurbishable | Initiator can be replaced in less than 15 minutes by trained personnel |
| Reliability prediction | 0.9999995 (based off scaled design) |
| Packaging | External housing typically supplied with two mounting points. Custom housings and mountings available |
| Connectorization | Standard design supplied with wire inputs. Connectorized versions available |
| Scalable bolt size | Bolt size determines preload and can be scaled to accommodate a wide range of requirements |

*Size callout based on the bolt size to be used. Metric thread also available.
Consult factory for complete test report

NOTES

- Unit is identified with Glenair name, CAGE code, part number, and date code, space permitting. Primary initiation circuit identified with "P" and redundant with "R".
- Release preload 12,500 lbs. (55.6 kN)
- Full qualification pending
- Reference Glenair P/N 060-401 for refurbishment initiator
- Metric threads available, consult factory for options

064-001


Heavy-duty hold-down release mechanisms

12,500 lb. release preload

Actuation curve



A




Heavy-duty hold-down release mechanisms





**20,000 lb. release preload
Redundant circuit**



ELECTRICALLY REDUNDANT HOLD DOWN RELEASE MECHANISM, HEAVY-DUTY



| How To Order | | |
|-----------------|-------------------|------|
| Sample Part No. | 064 | -006 |
| Basic Part No. | Heavy-Duty HDRM | |
| Dash No. | Redundant Circuit | |



SECTION A-A

NOTES

- Unit is identified with Glenair name, CAGE code, part number, and date code, space permitting. Primary initiation circuit identified with "P" and redundant with "R".
- Release preload 20,000 lbs. (88.96 kN). Proof load 25,000 lbs. (111.21 kN)
- Full qualification pending
- Reference Glenair P/N 060-406 for refurbishment initiator
- Consult factory for additional options and configurations.

Full qualification pending. Design and dimensions are subject to change.



Available 069-406 mechanical release for use in place of refurbishment initiator. Consult factory for application notes.


Light-duty pin pushers and pullers




6 lb. push force

Non-redundant circuit

NON-REDUNDANT CIRCUIT PIN PUSHER MECHANISM, LIGHT-DUTY



| How To Order | | |
|------------------------|-----------------------|-------------|
| Sample Part No. | 061 | -010 |
| Basic Part No. | Light-Duty Pin Pusher | |
| Dash No. | Non-Redundant Circuit | |



NOTES

1. Unit is identified with Glenair name, CAGE code, part number, and date code, space permitting.
2. Push load: 6 lbs. (26.7 N)
3. Full qualification pending
4. Reference Glenair P/N 060-110 for refurbishment initiator
5. Metric threads available, consult factory for options

| Physical characteristics | |
|--------------------------|--|
| Mass | 15.2 grams approximate weight |
| Material list | IAW MSFC-STD-3029 |
| Device features | |
| Field refurbishable | Initiator can be replaced in less than 15 minutes by trained personnel |
| Packaging | External housing typically supplied with two mounting points. Custom housings and mountings available |

*Size callout based on the bolt size to be used. Metric thread also available.
Consult factory for qualification test report.


Light-duty pin pushers and pullers

12 lb. pull force


Non-redundant circuit



NON-REDUNDANT CIRCUIT PIN PULLER MECHANISM, LIGHT-DUTY



| How To Order | | |
|-----------------|-----------------------|------|
| Sample Part No. | 061 | -009 |
| Basic Part No. | Light-Duty Pin Puller | |
| Dash No. | Non-Redundant Circuit | |



NOTES

1. Unit is identified with Glenair name, CAGE code, part number, and date code, space permitting.
2. Release preload 12 lbs. (53.3 N)
3. Full qualification pending
4. Reference Glenair P/N 060-109 for refurbishment initiator
5. Metric threads available, consult factory for options
6. Unit cannot take any side load

| Physical characteristics | |
|--|--|
| Mass | 16.2 grams nominal weight |
| Material list | IAW MSFC-STD-3029 |
| Epoxy | Outgassing requirements per GSC19384 |
| Device features | |
| Field refurbishable | Initiator can be replaced in less than 15 minutes by trained personnel |
| Packaging | External housing typically supplied with two mounting points. Custom housings and mountings available |
| Scalable bolt size | Bolt size determines preload and can be scaled to accommodate a wide range of requirements |
| *Size callout based on the bolt size to be used. Metric thread also available. Consult factory for complete test report | |

061-012


Light duty pin pushers and pullers

18 lb. pull force
Non-redundant circuit




A

NON-REDUNDANT CIRCUIT PIN PULLER MECHANISM, LIGHT-DUTY



| How To Order | | |
|-----------------|-----------------------|------|
| Sample Part No. | 061 | -012 |
| Basic Part No. | Light-Duty Pin Puller | |
| Dash No. | Non-Redundant Circuit | |



NOTES

- Unit is identified with Glenair name, CAGE code, part number, and date code, space permitting.
- Release preload: 16 lbs. (71.2 N) (TBC)
- Full qualification pending
- Reference Glenair P/N 060-112 for refurbishment initiator

| Physical characteristics | |
|--|--|
| Mass | 34.8 grams approximate weight |
| Material list | IAW MSFC-STD-3029 |
| Device features | |
| Field refurbishable | Initiator can be replaced in less than 15 minutes by trained personnel |
| Packaging | External housing typically supplied with two mounting points. Custom housings and mountings available |
| Connectorization | Standard design supplied with wire inputs. Connectorized versions available |
| *Size callout based on the bolt size to be used. Metric thread also available. Consult factory for qualification test report. | |

061-013

Medium duty pin pushers and pullers


**50 lb. pull force
Redundant circuit**



ELECTRICALLY REDUNDANT PIN PULLER MECHANISM, MEDIUM DUTY



| How To Order | | |
|-------------------------|------------------------|------|
| Sample Part No. | 061-013 | -190 |
| Basic Part No. | Medium-Duty Pin Puller | |
| Pin Diameter/Side Load: | Per Table I | |




NOTES

- Primary initiation circuit identified with "P" and redundant with "R".
- Pull force: 50 lbs. (222 N)
- Baseline pin puller qualification test parameters:
 - Survive static load: 330 Lbs
 - Hold and release: 40 Lbs
 - Random vibration 28.2 GRMS
 - Shock input: 2849 Gs
 - Thermal vacuum: 3 cycles -65°C to +70°C, 1.5×10^{-6} Torr, actuations at each extreme
 - Thermal vacuum no fire current: .250A, 5 minutes
 - Life cycle: 5 releases (one unit)
- Reference Glenair P/N 060-113 for refurbishment initiator
- Threads are available on the pin if needed. Metric threads also available
- Consult factory for additional options

| Physical characteristics | |
|---|---|
| Mass | 145.8 grams approximate weight |
| Material list | IAW MSFC-STD-3029 |
| Device features | |
| Redundant initiation | 2 initiation points |
| Field refurbishable | Initiator can be replaced in less than 15 minutes by trained personnel |
| Packaging | External housing typically supplied with two mounting points. Custom housings and mountings available |
| Connectorization | Standard design supplied with wire inputs. Connectorized versions available |
| *Size callout based on the bolt size to be used. Metric thread also available. Consult factory for qualification test report. | |

| Part Number Definition | | |
|------------------------|-------------|--------------------------------|
| Dash Number | "X" (Pin Ø) | Maximum Static Side Load (LBS) |
| -190 | .190 | 330 |
| -375 | .375 | 1200 |

50 lb. pull force,
Actuation curve



JAXA Kounotori H2
Transfer Vehicle and the
Canadian arm on the ISS

B


ADVANCED-PERFORMANCE HiPer-D Connectors

Space-grade M24308 intermateable


The HiPer-D connector is a M24308-type D-Subminiature connector with superior design features. Unlike standard M24308 connectors with stamped steel shells, the HiPer-D connector features such as a one-piece machined shell, 200°C continuous operating temperature rating and enhanced, mated shell EMI/RFI protection via an integrated ground spring. Aerospace grade fluorosilicone grommets and face seals (JAXA / NASA outgassing available) provide environmental protection. The HiPer-D is intermateable, intermountable and interchangeable with standard M24308 D-Sub connectors.

- Advanced temperature, vibration and EMC/electrical performance
- 11 standard and 20 combo insert arrangements
- High temperature epoxy insulators
- Watertight sealing
- Rugged machined one-piece shell

STANDARD AND HIGH DENSITY HIPER-D® - CUTAWAY



SERIES 28
HiPer-D Space Grade Connectors
Product Selection Guide




**280-018 In-line or Panel Mount
Crimp Terminated, Pin Connector for Attaching Wires**

Pages B-2




**280-019 In-line or Panel Mount
Crimp Terminated, Socket Connector for Attaching Wires**

Pages B-4




**280-030 Float Mount
Crimp Terminated, Pin Connector for Attaching Wires**

Page B-6



**280-031 Float Mount
Crimp Terminated, Socket Connector for Attaching Wires**

Page B-8



Glenair HiPer-D M24308 D-sub connectors are ideally suited for CubeSat or NanoSat canister dispenser applications where rack and panel or connectorized wire assemblies are used to communicate with HDRMs, pin pullers, pin pushers, door status sensors, as well as system communications and testing prior to deployment of satellite equipment. Standardized usage of M24308 connectors on hardware interfaces simplifies interconnection and communication. Glenair HiPer-D space grade M24308 D-sub connectors eliminate potential interconnect electrical problems on mission critical systems. Connectors are supplied with NASA/ESA/JAXA outgassing and screening in accordance with NASA EEE-INST-0002.

B

OTHER M24308 HIPER-D SOLUTIONS ALSO AVAILABLE - SEE OUR HIPER-D CATALOG

Sealed Panel Mount
Technology



Combo HiPer-D Contact
Arrangements



Ground Fingers for
Improved EMC



Advanced Board
Mount Features



Modern EMI backshells



SERIES 28
HiPer-D Space Grade Connectors
Available shell sizes and contact arrangements




STANDARD AND HIGH DENSITY CONTACT ARRANGEMENTS (face view of pin connector)

| | Standard Density | High Density |
|-------------|-------------------------|---------------------|
| Arrangement | 1S9 | 1H15 |
| Shell Size | 1 | 1 |
| Contacts | 9 #20 | 15 #22 |
| | | |
| Arrangement | 2S15 | 2H26 |
| Shell Size | 2 | 2 |
| Contacts | 15 #20 | 26 #22 |
| | | |
| Arrangement | 3S25 | 3H44 |
| Shell Size | 3 | 3 |
| Contacts | 25 #20 | 44 #22 |
| | | |
| Arrangement | 4S37 | 4H62 |
| Shell Size | 4 | 4 |
| Contacts | 37 #20 | 62 #22 |
| | | |
| Arrangement | 5S50 | 5H78 |
| Shell Size | 5 | 5 |
| Contacts | 50 #20 | 78 #22 |
| | | |
| Arrangement | | 6H104 |
| Shell Size | | 6 |
| Contacts | | 104 #22 |
| | | |

B

SERIES 28
HiPer-D Space Grade Connectors
Reference and Technical Data



| Description | Requirement | | | Procedure | | |
|------------------------------|---|---|----------------------------------|---|--|--|
| Voltage Rating (DWV) | 1000 VAC Sea Level | | | EIA-364-20 | | |
| Operating Temperature | -65° C. to +200° C. | | | | | |
| Insulation Resistance | 5000 megohms minimum | | | EIA-364-21 | | |
| Current Rating | Size #20 7.5A, #22 5A | | | | | |
| Contact Resistance | Wire Size 20 22 24 | Test Current 7.5 5 3 | Millivolt Drop 55 73 45 | EIA-364-06 | | |
| Low Level Contact Resistance | Wire Size 20 22 24 | Max Milliohms 9 15 20 | | EIA-364-23 | | |
| Shell-to-Shell Resistance | 2.5 milliohm max (ground spring required) | | | EIA-364-83 | | |
| Shielding Effectiveness | Freq. GHz 0.1 0.4 0.8 1.0 3.0 6.0 10.0 | Min Attenuation (dB) 100 90 85 80 55 40 30 | | EIA-364-66 Electroless nickel plated shells with ground spring installed | | |
| Water Immersion, mated | 1 hour immersion at a depth of 1 meter | | | MIL-STD-810F Method 512.4 | | |
| Ingress Protection Rating | IP67, mated connectors | | | IEC-60529 | | |
| Vibration, Sine | 20 g's | | | EIA-364-28 | | |
| Vibration, Random | 43 g's | | | EIA-364-28 | | |
| Mechanical Shock | 300 g's | | | EIA-364-27 | | |
| Thermal Shock | -65° C. to +200° C. | | | EIA-364-32 | | |
| Humidity | 10 cycles, 10 days, 25°C to 65°C | | | EIA-364-31 | | |
| Altitude Immersion | 75,000 feet | | | EIA-364-03 | | |
| Fluid Immersion | No damage from solvents, oils, and fuels | | | EIA-364-10 | | |
| Magnetic Permeability | 2 μ maximum | | | EIA-364-54 | | |
| Mechanical Durability | 500 Mating Cycles | | | EIA-364-09 | | |

| Description | Material | Finish |
|--|---------------------------------------|--------------------------------|
| Contacts | Copper Alloy | Gold (50 microin.) over nickel |
| Socket Contact Hood (Size 20, 22) | Stainless steel | Passivated |
| Shell | Aluminum Alloy or stainless steel | See ordering information |
| Insulators | Thermoset epoxy resin per ASTM D-5948 | None |
| Interfacial Seal | Fluorosilicone | None |
| Grommet | Fluorosilicone | None |
| EMI Spring | Copper alloy | Electroless nickel |
| Contact retention clips | Copper alloy | None |
| Insert retention clip | Copper alloy | None |
| Sealant | RTV silicone | None |
| Hardware | Stainless steel (300 series) | Passivated |
| O-ring | Fluorosilicone | None |

SERIES 28

HiPer-D Space Grade Connectors

**280-018P inline cable or panel mount pin connector,
crimp termination**




HiPer-D pin connectors for cable or panel mount feature crimp, rear-releaseable size #20 or #22 contacts. Intermateable with standard M24308-type D-Subminiature connectors, the HiPer-D features a rugged machined aluminum shell, waterproof sealing and optional ground springs for improved resistance to electromagnetic interference. Gold-plated size #20 contacts conform to M39029/64-369 and accept #20 to #24 AWG wire. Gold-plated size #22 contacts conform to M39029/58-360 and accept #22 to #28 AWG wire. Contacts are packaged with connector. Glass-reinforced thermoset epoxy insulators, copper alloy retention clips. Fluorosilicone face seal and rear grommet meet IP67 immersion requirement. 1000 VAC, 5 Amps (#22) or 7.5 Amps (#20).

B

| How To Order | | | | | |
|---------------------------------------|---|--|-------------|-----------|----------|
| Sample Part Number | 280-018P | | 3S25 | ME | G |
| Basic Part Number | 280-018P | | | | P |
| Shell Size-Contact Arrangement | See Shell Size - Contact Arrangements Table | | | | |
| Shell Finish | ME = Electroless Nickel (RoHS) Z2 = Gold (RoHS) Z1 = Passivated Stainless Steel (RoHS) | | | | |
| Ground Spring | G = Supplied with EMI Ground Spring | N = No Ground Spring | | | |
| Mating Hardware | N = No Hardware (Through-Hole) L = Jackscrew, Hex Head, Low Profile S = Screwlock, Male, Hex Head, Low Profile | P = #4-40 Female Jackpost K = Jackscrew, Slot Head, Extended Length T = Screwlock, Male, Slot Head, Extended Length | | | |

| Shell Size - Contact Arrangements | | |
|-----------------------------------|----------------------|-----|
| Shell Size-Contact Arr. | Contact Size and Qty | |
| | #20 | #22 |
| Standard Density | | |
| 1S9 | 9 | |
| 2S15 | 15 | |
| 3S25 | 25 | |
| 4S37 | 37 | |
| 5S50 | 50 | |
| High Density | | |
| 1H15 | | 15 |
| 2H26 | | 26 |
| 3H44 | | 44 |
| 4H62 | | 62 |
| 5H78 | | 78 |
| 6H104 | | 104 |




| Materials and Finishes | |
|------------------------|---------------------------------------|
| Shell | Aluminum alloy |
| Contacts | Copper alloy, 50 microin. gold plated |
| Insulators | Thermoset epoxy |
| Retention Clips | Copper alloy |
| Grommet and Seal | Fluorosilicone rubber |
| EMI Spring | Copper alloy, nickel plated |
| Hardware | 300 series stainless steel |

| Specifications | |
|-----------------------|--------------------------|
| Current Rating | #22 5 AMPS, #20 7.5 AMPS |
| Test Voltage | 1000 VAC RMS |
| Insulation Resistance | 5000 megohms minimum |
| Operating Temperature | -65° C. to +200° C. |
| Ingress Protection | IP 67 |
| Shock | 300 g. |
| Vibration, Random | 43.92 g. |


SERIES 28

HiPer-D Space Grade Connectors

280-018P inline cable or panel mount pin connector,
crimp termination



280-018P DIMENSIONS



| Shell Size | Dimensions | | | | | | | | | | | | | |
|------------|------------|-------|------|-------|---------|-------|-------|-------|------|-------|--------|-------|--------|-------|
| | A | | B | | C Basic | | D | | E | | F Max. | | G Max. | |
| | in | mm | in | mm | in. | mm | in | mm | in | mm | in. | mm | in. | mm |
| 1 | 1.213 | 30.81 | .494 | 12.55 | .984 | 24.99 | .726 | 18.44 | .389 | 9.88 | .769 | 19.53 | .432 | 10.97 |
| 2 | 1.541 | 39.14 | .494 | 12.55 | 1.312 | 33.32 | 1.054 | 26.77 | .389 | 9.88 | 1.093 | 27.76 | .432 | 10.97 |
| 3 | 2.088 | 53.04 | .494 | 12.55 | 1.852 | 47.04 | 1.594 | 40.49 | .389 | 9.88 | 1.635 | 41.53 | .432 | 10.97 |
| 4 | 2.729 | 69.32 | .494 | 12.55 | 2.500 | 63.50 | 2.242 | 56.95 | .389 | 9.88 | 2.282 | 57.96 | .432 | 10.97 |
| 5 | 2.635 | 66.93 | .605 | 15.37 | 2.406 | 61.11 | 2.139 | 54.33 | .501 | 12.73 | 2.188 | 55.58 | .544 | 13.82 |
| 6 | 2.729 | 69.32 | .668 | 16.97 | 2.500 | 63.50 | 2.272 | 57.71 | .563 | 14.30 | 2.312 | 58.72 | .606 | 15.39 |

NOTES

1. HiPer-D connectors are available with a wide variety of materials and finishes. See [About Series 28 HiPer-D® Shell Plating Options](#) for additional choices. Glenair offers the industry's widest selection of plating and material choices with no setup charge, no minimum order quantity and no schedule impact.
2. For panel cutout dimensions, refer to [Panel Cutouts and Printed Circuit Board Footprints](#).
3. Connectors are supplied with crimp contacts per M39029. Contacts are not installed. Refer to [HiPer-D® Contacts and Crimp Tools](#) for contact part numbers, specifications, crimp tool information, and insertion/extraction tools.
4. HiPer-D connectors meet the requirements of MIL-DTL-24308 and are intermateable with standard M24308-type D-Subminiature connectors with corresponding contact arrangements and type.
5. Additional electrical, mechanical and environmental specifications are listed in [HiPer-D® Product Specification](#).

B

SERIES 28

HiPer-D Space Grade Connectors

280-019S inline cable or panel mount socket connector, crimp termination




HiPer-D socket connectors for in-line cable or panel mount feature crimp, rear-releaseable size #20 or #22 contacts. Intermateable with standard M24308-type D-Subminiature connectors, the HiPer-D features a rugged machined aluminum shell and waterproof sealing. Gold-plated size #20 contacts conform to M39029/63-368 and accept #20 to #24 AWG wire. Gold-plated size #22 contacts conform to M39029/57-354 and accept #22 to #28 AWG wire. Contacts are packaged with connector. Glass-reinforced thermoset epoxy insulators, copper alloy retention clips. Fluorosilicone rear grommet meets IP67 immersion requirement. Shell has backshell attachment groove. 1000 VAC, 5 Amps (#22) or 7.5 Amps (#20).

B

| How To Order | | | | |
|---------------------------------------|---|--|-----------|----------|
| Sample Part Number | 280-019S | 4H62 | ME | L |
| Basic Part Number | 280-019S | | | |
| Shell Size-Contact Arrangement | See Shell Size - Contact Arrangements Table | | | |
| Shell Finish | ME = Electroless Nickel (RoHS) Z2 = Gold (RoHS) Z1 = Passivated Stainless Steel (RoHS) | | | |
| Mating Hardware | N = No Hardware (Through-Hole) L = Jackscrew, Hex Head, Low Profile S = Screwlock, Male, Hex Head, Low Profile | P = #4-40 Female Jackpost K = Jackscrew, Slot Head, Extended Length T = Screwlock, Male, Slot Head, Extended Length | | |

| Shell Size - Contact Arrangements | | |
|-----------------------------------|----------------------|-----|
| Shell Size-Contact Arr. | Contact Size and Qty | |
| | #20 | #22 |
| Standard Density | | |
| 1S9 | 9 | |
| 2S15 | 15 | |
| 3S25 | 25 | |
| 4S37 | 37 | |
| 5S50 | 50 | |
| High Density | | |
| 1H15 | | 15 |
| 2H26 | | 26 |
| 3H44 | | 44 |
| 4H62 | | 62 |
| 5H78 | | 78 |
| 6H104 | | 104 |



| Materials and Finishes | |
|------------------------|---------------------------------------|
| Shell | Aluminum alloy |
| Contacts | Copper alloy, 50 microin. gold plated |
| Insulators | Thermoset epoxy |
| Retention Clips | Copper alloy |
| Grommet | Fluorosilicone rubber |
| Hardware | 300 series stainless steel |

| Specifications | |
|-----------------------|--------------------------|
| Current Rating | #22.5 AMPS, #20 7.5 AMPS |
| Test Voltage | 1000 VAC RMS |
| Insulation Resistance | 5000 megohms minimum |
| Operating Temperature | -65° C. to +200° C. |
| Ingress Protection | IP 67 |
| Shock | 300 g. |
| Vibration, Random | 43.92 g. |


SERIES 28

HiPer-D Space Grade Connectors

280-019S inline cable or panel mount socket
connector, crimp termination



280-019S DIMENSIONS



B

| Dimensions | | | | | | | | | | |
|------------|-------|-------|------|-------|---------|-------|-------|-------|------|-------|
| Shell Size | A | | B | | C Basic | | D | | E | |
| | in | mm | in | mm | in. | mm | in | mm | in | mm |
| 1 | 1.213 | 30.81 | .494 | 12.55 | .984 | 24.99 | .769 | 19.53 | .432 | 10.97 |
| 2 | 1.541 | 39.14 | .494 | 12.55 | 1.312 | 33.32 | 1.093 | 27.76 | .432 | 10.97 |
| 3 | 2.088 | 53.04 | .494 | 12.55 | 1.852 | 47.04 | 1.635 | 41.53 | .432 | 10.97 |
| 4 | 2.729 | 69.32 | .494 | 12.55 | 2.500 | 63.50 | 2.282 | 57.96 | .432 | 10.97 |
| 5 | 2.635 | 66.93 | .605 | 15.37 | 2.406 | 61.11 | 2.188 | 55.58 | .544 | 13.82 |
| 6 | 2.729 | 69.32 | .668 | 16.97 | 2.500 | 63.50 | 2.312 | 58.72 | .606 | 15.39 |


NOTES

1. HiPer-D connectors are available with a wide variety of materials and finishes. See [About Series 28 HiPer-D® Shell Plating Options](#) for additional choices. Glenair offers the industry's widest selection of plating and material choices with no setup charge, no minimum order quantity and no schedule impact.
2. For panel cutout dimensions, refer to [Panel Cutouts and Printed Circuit Board Footprints](#).
3. Connectors are supplied with crimp contacts per M39029. Contacts are not installed. Refer to [HiPer-D® Contacts and Crimp Tools](#) for contact part numbers, specifications, crimp tool information, and insertion/extraction tools.
4. HiPer-D connectors meet the requirements of MIL-DTL-24308 and are intermateable with standard M24308-type D-Subminiature connectors with corresponding contact arrangements and type.
5. Additional electrical, mechanical and environmental specifications are listed in [HiPer-D® Product Specification](#).

SERIES 28

HiPer-D Space Grade Connectors

**280-030P float mount pin connector for blind mating
with float bushings or guide pins, crimp termination**




280-030P HiPer-D pin connectors feature stainless steel float bushings for blind mating. Attach to panel with #4-40 screws (not supplied with connector). Crimp, rear-releaseable size #20 or #22 contacts. Intermateable with standard M24308-type D-Subminiature connectors, the HiPer-D features a rugged machined aluminum shell, rubber seals and optional ground springs for improved resistance to electromagnetic interference. Threaded holes on the rear of the connector allow direct attachment of HiPer-D EMI backshells. Contacts are packaged with connector. Terminate contacts with crimp tools purchased separately. Glass-reinforced thermoset epoxy insulators, copper alloy retention clips. Fluorosilicone face seal and rear grommet meet IP67 immersion requirement (mated). 1000 VAC, 5 Amps (#22) or 7.5 Amps (#20).

B

| How To Order | | | | | |
|---------------------------------------|---|--|-----------------------------|-----------|----------|
| Sample Part Number | 280-030P | | 6H104 | MT | N |
| Basic Part Number | 280-030P | | | | |
| Shell Size-Contact Arrangement | See Shell Size - Contact Arrangements Table | | | | |
| Shell Finish | ME = Electroless Nickel (RoHS) Z2 = Gold (RoHS) Z1 = Passivated Stainless Steel (RoHS) | | | | |
| Ground Spring | G = Supplied with EMI Ground Spring | | N = No Ground Spring | | |
| Mating Hardware | N = No Hardware (supplied with #8-32 tapped hole) B = Female Guide Bushings | | G = Male Guide Pins | | |

| Shell Size - Contact Arrangements | | |
|-----------------------------------|----------------------|-----|
| Shell Size-Contact Arr. | Contact Size and Qty | |
| | #20 | #22 |
| Standard Density | | |
| 1S9 | 9 | |
| 2S15 | 15 | |
| 3S25 | 25 | |
| 4S37 | 37 | |
| 5S50 | 50 | |
| High Density | | |
| 1H15 | | 15 |
| 2H26 | | 26 |
| 3H44 | | 44 |
| 4H62 | | 62 |
| 5H78 | | 78 |
| 6H104 | | 104 |




| Materials and Finishes | |
|------------------------|---------------------------------------|
| Shell | Aluminum alloy |
| Contacts | Copper alloy, 50 microin. gold plated |
| Insulators | Thermoset epoxy |
| Retention Clips | Copper alloy |
| Grommet, Seal, O-ring | Fluorosilicone rubber |
| Hardware | 300 series stainless steel |

| Specifications | |
|-----------------------|--------------------------|
| Current Rating | #22 5 AMPS, #20 7.5 AMPS |
| Test Voltage | 1000 VAC RMS |
| Insulation Resistance | 5000 megohms minimum |
| Operating Temperature | -65° C. to +200° C. |
| Ingress Protection | IP 67 |
| Shock | 300 g. |
| Vibration, Random | 43.92 g. |


SERIES 28

HiPer-D Space Grade Connectors

280-030P float mount pin connector for blind mating
with float bushings or guide pins, crimp termination



280-030P DIMENSIONS



B

| Dimensions | | | | | | | | | | | | |
|------------|--------------|--------------|--------------|--------------|-----------|-----------|--------------|--------------|--------------|--------------|--------------|--------------|
| Shell Size | A | | B | | C Basic | | D | | E | | F Basic | |
| | in ± .015 | mm ± 0.38 | in ± .015 | mm ± 0.38 | in. mm | in. mm | in ± .005 | mm ± 0.13 | in ± .005 | mm ± 0.13 | in ± .005 | mm ± 0.13 |
| 1 | 1.986 | 50.44 | .494 | 12.55 | .984 | 24.99 | .726 | 18.44 | .389 | 9.88 | 1.636 | 41.55 |
| 2 | 2.314 | 58.78 | .494 | 12.55 | 1.312 | 33.32 | 1.054 | 26.77 | .389 | 9.88 | 1.964 | 49.89 |
| 3 | 2.854 | 72.49 | .494 | 12.55 | 1.852 | 47.04 | 1.594 | 40.49 | .389 | 9.88 | 2.504 | 63.60 |
| 4 | 3.502 | 88.95 | .494 | 12.55 | 2.500 | 63.50 | 2.242 | 56.95 | .389 | 9.88 | 3.152 | 80.06 |
| 5 | 3.408 | 86.56 | .600 | 15.24 | 2.406 | 61.11 | 2.139 | 54.33 | .501 | 12.73 | 3.058 | 77.67 |
| 6 | 3.502 | 88.95 | .662 | 16.81 | 2.500 | 63.50 | 2.272 | 57.71 | .563 | 14.30 | 3.152 | 80.06 |


NOTES

- HiPer-D connectors are available with a wide variety of materials and finishes. See [About Series 28 HiPer-D® Shell Plating Options](#) for additional choices. Glenair offers the industry's widest selection of plating and material choices with no setup charge, no minimum order quantity and no schedule impact.
- For panel cutout dimensions, refer to [Panel Cutouts and Printed Circuit Board Footprints](#).
- Connectors are supplied with crimp contacts per M39029. Contacts are not installed. Refer to [HiPer-D® Contacts and Crimp Tools](#) for contact part numbers, specifications, crimp tool information, and insertion/extraction tools.
- HiPer-D connectors meet the requirements of MIL-DTL-24308 and are intermateable with standard M24308-type D-Subminiature connectors with corresponding contact arrangements and type.
- Additional electrical, mechanical and environmental specifications are listed in [HiPer-D® Product Specification](#).

SERIES 28

HiPer-D Space Grade Connectors

280-031S float mount socket connectors for blind mating with float mount bushings or guide pins, crimp termination




280-031S HiPer-D socket connectors feature stainless steel floating bushings for blind mate applications. Attach to panel with #4-40 screws (not supplied with connector). Crimp, rear-releaseable size #20 or #22 contacts. Intermateable with standard M24308-type D-Subminiature connectors, the HiPer-D features a rugged machined aluminum shell and rubber grommet. Threaded holes on the rear of the connector allow attachment of HiPer-D EMI backshells. Contacts are packaged with connector. Terminate contacts with crimp tools purchased separately. Glass-reinforced thermoset epoxy insulators, copper alloy retention clips. Connector meets IP67 immersion requirement. 1000 VAC, 5 Amps (#22) or 7.5 Amps (#20).

B

| How To Order | | | | |
|--------------------------------|---|------|----|---|
| Sample Part Number | 280-031S | 2H26 | Z2 | G |
| Basic Part Number | 280-031S | | | |
| Shell Size-Contact Arrangement | See Shell Size - Contact Arrangements Table | | | |
| Shell Finish | ME = Electroless Nickel (RoHS) Z2 = Gold (RoHS) Z1 = Passivated Stainless Steel (RoHS) | | | |
| Mating Hardware | N = No Hardware (supplied with #8-32 tapped holes) G = Male Guide Pins B = Female Guide Bushings | | | |

| Shell Size - Contact Arrangements | | |
|-----------------------------------|----------------------|-----|
| Shell Size-Contact Arr. | Contact Size and Qty | |
| | #20 | #22 |
| Standard Density | | |
| 1S9 | 9 | |
| 2S15 | 15 | |
| 3S25 | 25 | |
| 4S37 | 37 | |
| 5S50 | 50 | |
| High Density | | |
| 1H15 | | 15 |
| 2H26 | | 26 |
| 3H44 | | 44 |
| 4H62 | | 62 |
| 5H78 | | 78 |
| 6H104 | | 104 |




| Materials and Finishes | |
|------------------------|---------------------------------------|
| Shell | Aluminum alloy |
| Contacts | Copper alloy, 50 microin. gold plated |
| Insulators | Thermoset epoxy |
| Retention Clips | Copper alloy |
| Grommet | Fluorosilicone rubber |
| Hardware | 300 series stainless steel |

| Specifications | |
|-----------------------|--------------------------|
| Current Rating | #22 5 AMPS, #20 7.5 AMPS |
| Test Voltage | 1000 VAC RMS |
| Insulation Resistance | 5000 megohms minimum |
| Operating Temperature | -65° C. to +200° C. |
| Ingress Protection | IP 67 |
| Shock | 300 g. |
| Vibration, Random | 43.92 g. |


SERIES 28

HiPer-D Space Grade Connectors

280-031S float mount socket connectors for blind mating
with float mount bushings or guide pins, crimp termination



280-031S DIMENSIONS



| Shell Size | Dimensions | | | | | | | |
|------------|------------|-----------|-----------|-----------|---------|-------|---------|-------|
| | A | | B | | C Basic | | D Basic | |
| | in ± .015 | mm ± 0.38 | in ± .015 | mm ± 0.38 | in. | mm | in | mm |
| 1 | 1.986 | 50.44 | .494 | 12.55 | .984 | 24.99 | 1.636 | 41.55 |
| 2 | 2.314 | 58.78 | .494 | 12.55 | 1.312 | 33.32 | 1.964 | 49.89 |
| 3 | 2.854 | 72.49 | .494 | 12.55 | 1.852 | 47.04 | 2.504 | 63.60 |
| 4 | 3.502 | 88.95 | .494 | 12.55 | 2.500 | 63.50 | 3.152 | 80.06 |
| 5 | 3.408 | 86.56 | .600 | 15.24 | 2.406 | 61.11 | 3.058 | 77.67 |
| 6 | 3.502 | 88.95 | .662 | 16.81 | 2.500 | 63.50 | 3.152 | 80.06 |

NOTES

1. HiPer-D connectors are available with a wide variety of materials and finishes. See [About Series 28 HiPer-D® Shell Plating Options](#) for additional choices. Glenair offers the industry's widest selection of plating and material choices with no setup charge, no minimum order quantity and no schedule impact.
2. For panel cutout dimensions, refer to [Panel Cutouts and Printed Circuit Board Footprints](#).
3. Connectors are supplied with crimp contacts per M39029. Contacts are not installed. Refer to [HiPer-D® Contacts and Crimp Tools](#) for contact part numbers, specifications, crimp tool information, and insertion/extraction tools.
4. HiPer-D connectors meet the requirements of MIL-DTL-24308 and are intermateable with standard M24308-type D-Subminiature connectors with corresponding contact arrangements and type.
5. Additional electrical, mechanical and environmental specifications are listed in [HiPer-D® Product Specification](#).



Space-Grade Circular Blind-Mate Connectors



Application: Glenair Series 253 blind-mate connectors are designed to meet applicable environmental, electrical and mechanical performance characteristics of D38999 Series III. The technology is well suited for use in commercial rack-and-panel instrumentation applications, as well as a blind-mate solution for satellite deployment, scientific research and development payloads, interstage, UAV, and munitions release and more.

- Blind-mate, fixed and float-mount interconnects for non-ITAR commercial as well as military/defense applications
- Adjustable separation force (AKA assisted-release, zero extraction force) solutions
- Misalignment accommodation and special auxiliary sealing for trouble-free blind mating in environmental applications
- Available in most symmetrical MIL-STD-1560 insert arrangements with contacts sizes from #23 to #8
- Selected materials offer low outgassing properties and high resistance to both corrosion and stress corrosion cracking
- NASA outgassing bake-out process available
- Designed to withstand the rigors of launch and flight—including shock, vibration, thermal vacuum, acceleration, and temperature extremes
- Standard accessory threads and teeth per MIL-DTL-38999 accommodate a wide range of backshell accessories
- Crimp-removable contacts standard. Consult factory for PC tails, dual-flange standoffs, custom blind-mate configurations, and hermetically sealed options

| Current Rating | |
|----------------|------|
| Size Contact | Amps |
| 23 | 5 |
| 22D | 5 |
| 20 | 7.5 |
| 16 | 13 |
| 12 | 23 |

| Unmated Test Voltages, AC RMS, 60 Hz | | | | |
|--------------------------------------|------------------|------------------|------------------|-------------------|
| Altitude (Feet) | Service Rating M | Service Rating N | Service Rating I | Service Rating II |
| Sea Level | 1300 | 1000 | 1800 | 2300 |
| 50,000 | 550 | 400 | 600 | 800 |
| 70,000 | 350 | 260 | 400 | 500 |
| 100,000 | 200 | 260 | 200 | 200 |

Space-grade, blind-mate connectors

MIL-DTL-38999 Series III Type Space-Grade Connectors

Fixed and float mount blind mate connectors



CRITICAL MECHANICAL FEATURES OF BLIND-MATE CONNECTORS



Roll-off nose: provides smooth disconnection of blind mate plugs and receptacles. Without this feature, connectors can catch or hang during mate and demate cycle.




Float mount: allows for a modicum of coplanar movement of the receptacle during rack-and-panel and other blind mate applications, preventing both contact and shell damage.



Misalignment accommodation: additional radial, axial, and angular misalignment during mating is accounted for in the receptacle design with integral wave springs.



Sealing: Misalignment accommodation makes environmental sealing difficult in blind-mate connectors. The problem is solved with auxiliary external seals.



EMI shielding: Glenair incorporates ground springs in receptacle connectors as well as grounding fingers in special coupling nut-equipped plugs (253-018-G6 feed-thru shown) to optimize 360° shell-to-shell continuity.



Assisted separation force: Glenair supplies two styles of spring-loaded blind-mate connectors. **Adjustable kick-off styles** feature spring-loaded posts on the plug and an adjustment ring on the receptacle used to calibrate separation force. The second style uses wave springs on the shell body.

| Available non-ITAR environmental blind-mate and adjustable separation force solutions | | |
|---|---|-------------------------|
| Basic Part No. | Description | Mates With |
| 253-014 | Fixed jam-nut mount plug with roll-on/roll-off nose and Accessory threads | 253-015 |
| 253-015 | Floating jam-nut mount receptacle with misalignment accommodation and optional sealing | 253-014 |
| 253-016 | Fixed wall mount plug with spring assist (zero separation force) | 253-017 |
| 253-017 | Floating wall mount receptacle with adjustable separation force and misalignment accommodation | 253-016 |
| 253-018-07 | Blind-mate feed-thru, jam-nut mount plug with B-side D38999 type receptacle mating interface and assisted kick-off (spring force) | 253-019 |
| 253-018-G6 | Blind-mate in-line feed-thru with B-side D38999 type plug mating interface and assisted kick-off (spring force) | 253-019 |
| 253-019 | Floating jam-nut mount receptacle with misalignment accommodation and optional sealing | 253-018 |
| 253-031 | Blind-mate jam-nut mount plug with kick-off spring and accessory threads | 253-032 |
| 253-032 | Floating jam-nut mount receptacle with misalignment accommodation | 253-031 |
| 253-033 | Float mount feed-thru, jam nut mount receptacle to 38999 type Series III plug mating interface | 253-019 |
| 253-025 | Locking circuit and test mate connector | 253-016 |



ENVIRONMENTAL SERIES 23

Space-Grade Guidelines for SuperNine® Connectors

Outgassing

Space flight equipment requires low-outgassing components in order to prevent degradation to optics and other sensitive instruments. SuperNine® connectors contain nonmetallic materials such as rubber, plastic, adhesives and potting compounds which can give off gasses when subjected to a vacuum or high heat. Unless the connector is specially processed, the TML and CVCM can exceed allowable limits. The space industry has adopted a standardized test procedure, ASTM E595, to evaluate outgassing properties. The MIL-DTL-38999 specification Class G also details specific TVM and CVCM values in addition to finish specifications. In Glenair's 186T process, for example, connectors and connector materials are heated to 175° C at a vacuum of 5×10^{-6} Torr for 48 hours. Items under test are then weighed to calculate the Total Mass Loss (TML), which may not exceed 1.0% of the total initial mass. A collector plate is used to determine the Collected Volatile Condensable Material (CVCM), which may not exceed 0.1% of the total original specimen mass for Class G rated connectors. Glenair is able to offer outgas processing which assures all materials comply with their respective standards.

Note on Connector Material and Finish Options

Some types of metals are prohibited for space flight. "Pure Tin, Cadmium and Zinc shall not be used as a final finish on EEE parts." (NASA EEE-INSTR-002 Instructions for EEE Parts Selection, Screening, Qualification, and Derating). NASA recommends electroless nickel or gold finish on connector shells and gold finish for contacts.

- SuperNine® environmental series connectors may be subjected to outgas processing and/or NASA screening IAW MIL-DTL-38999 Class G
- Modification codes are a convenient way to specify outgassing / screening requirements per NASA specifications and/or D38999 Class G
- Cadmium and silver finish are prohibited in space
- Specify electroless nickel finish on connector shells and gold finish on contacts

ADVANCED PERFORMANCE


SuperNine® Environmental Series
MIL-DTL-38999 Series III Type**Class G and NASA space-grade guidelines****NASA and Class G Screening**

The MIL-DTL-38999 specification defines TML and CVCM values for Class G space flight. Glenair modification code 186T assures parts are outgassed to meet the Class G requirements for outgassing. Additionally, NASA recommends that connectors for space flight be specially screened. NASA EEE-INST-002 instructions for EEE parts selection, screening, qualification, and derating contains three levels of screening for space-grade components. These outgassing and screening modification codes are listed at right. To add a modification code append code to end of part number: 253-016-00ME25-35PNMS-**429C**.

- “Mission critical” connectors for space flight should undergo rigorous 100% final inspection
- Modification codes are available to invoke special screening for both MIL-DTL-38999 and NASA applications
- Outgassing properties of materials used in Glenair SuperNine® connectors are detailed in the table below

| Outgassing Properties of Materials Used in MIL-DTL-38999 Type SuperNine® Connectors | | | | |
|---|---|-------|--------|--|
| Component | Material | TML % | CVCM % | Test Reference |
| Front and Rear Insulator | EpiAll 1908 | 0.84 | 0.0 | NASA Test # GSC15435 (48 hours at 180°C) |
| Rear Grommet, Interfacial Seal, Peripheral Seal, and Special Auxiliary Seals | Blended fluorosilicone/silicone elastomer | 0.04 | 0.0 | Glenair test |
| Front-To-Rear Insulator Bonding Material | Eccobond 104 A/B | 0.52 | 0.08 | Emerson & Cuming Data Sheet |
| Insulator-to-Rubber Bonding Material | RTV, per MIL-A-46146 | <1.0 | <0.1 | Glenair Test |
| White Epoxy Ink for Silk-screening | Markem 7224 White | 0.49 | 0.03 | NASA Test #GSC19899 |


| MIL-DTL-38999 Type SuperNine® Connector Materials Approved for Space Flight | | |
|---|---|--------------------------------|
| Component | Material | Notes |
| Shells, Coupling Nuts, Jam Nuts | Aluminum alloy | Approved for Space Flight |
| Rigid Insulators | Glass reinforced thermoset plastic, EpiAll 1908 | Approved for Space Flight |
| Contact Retention Clip | Beryllium copper, heat-treated, unplated | Approved for Space Flight |
| Grommet, Peripheral Seal, Interfacial Seal, Special Auxiliary Seals, O-ring | Blended fluorosilicone/silicone elastomer | Requires outgassing processing |
| Pin/Socket Contact | Gold plated beryllium copper alloy | Approved for Space Flight |
| Socket Contact Hood | Stainless steel | Approved for Space Flight |
| Potting Compounds and Adhesives | RTV and epoxies | Requires outgassing processing |

ADVANCED PERFORMANCE

 SuperNine®

MIL-DTL-38999 Series III Type

MIL-STD-1560 standard contact arrangements

 SuperNine®


| Size #22 | Size #20 | Size #16 | Size #12 |
|-------------------|-------------------|-------------------|-------------------|
| 857-151-22 Pin | 857-151-20 Pin | 857-151-16 Pin | 857-151-12 Pin |
| 857-150-22 Socket | 857-150-20 Socket | 857-150-16 Socket | 857-150-12 Socket |

| Environmental and Hermetic Contact Arrangements | | | | | |
|---|--------------------|-----|-----|-----|--------------------|
| Contact | Number of Contacts | | | | Insert Arrangement |
| | #22D | #20 | #16 | #12 | |
| Size #22D 5 Amp Max. Current #22-#28 AWG | 6 | | | | 9-35 |
| | 13 | | | | 11-35 |
| | 22 | | | | 13-35 |
| | 37 | | | | 15-35 |
| | 55 | | | | 17-35 |
| | 66 | | | | 19-35 |
| | 67 | | | | 19-35 |
| | 79 | | | | 21-35 |
| | 100 | | | | 23-35 |
| | 128 | | | | 25-35 |
| | | 2 | | | 9-94 |
| | | 3 | | | 9-98 |
| Size #20 7.5 Amp Max. Current #20-#24 AWG | | 4 | | | 11-4 |
| | | 5 | | | 11-5 |
| | | 6 | | | 11-98 |
| | | 7 | | | 11-99 |
| | | 8 | | | 13-8 |
| | | 10 | | | 13-98 |
| | | 18 | | | 15-18 |
| | | 19 | | | 15-19 |
| | | 26 | | | 17-26 |
| | | 32 | | | 19-32 |
| | | 24 | | | 21-24 |
| | | 25 | | | 21-25 |
| | | 27 | | | 21-27 |
| | | 41 | | | 21-41 |
| | | 32 | | | 23-32 |
| | | 34 | | | 23-34 |
| | | 36 | | | 23-36 |
| | | 53 | | | 23-53 |
| | | 55 | | | 23-55 |
| | | 61 | | | 25-61 |
| Environmental and Hermetic Contact Arrangements | | | | | |
| Size #16 Contacts 13 Amp Max. Current #16-#20 AWG | Number of Contacts | | | | Insert Arrangement |
| | #22D | #20 | #16 | #12 | |
| | | | 2 | | 11-2 |
| | | | 4 | | 13-4 |
| | | | 5 | | 15-5 |
| | | | 8 | | 17-8 |
| | | | 11 | | 19-11 |
| | | | 16 | | 21-16 |
| | | | 21 | | 23-21 |
| | | | 16 | | 23-97 |
| | | | 11 | | 23-99 |
| | | | 29 | | 25-29 |
| | | | 37 | | 25-37 |
| Size #12 Contacts 23 Amp Max. Current #12-14 AWG | | | | | |
| Size #12 Contacts 23 Amp Max. Current #12-14 AWG | | | | 6 | 17-6 |
| | | | | 11 | 21-11 |
| | | | | 19 | 25-19 |

See Appendix for PCB Footprints

C

ADVANCED PERFORMANCE



MIL-DTL-38999 Series III Type MIL-STD-1560 standard contact arrangements

All views are pin face

Contact Legend
 #22D • #16 +
 #20 Θ #12 ●



Insert Arrangement

9-35

9-98

11-2

11-4

11-5

11-35

11-98

No. of Contacts

6

3

2

4

5

13

6

Contact Size

#22D

#20

#16

#20

#20

#22D

#20

Service Rating

M

I

I

I

I

M

I

Contact Legend
 #22D • #16 +
 #20 Θ #12 ●



Insert Arrangement

11-99

13-4

13-8

13-98

13-35

15-5

No. of Contacts

7

4

8

10

22

5

Contact Size

#20

#16

#20

#20

#22D

#16

Service Rating

I

I





I

I

M

II

Contact Legend
 #22D • #16 +
 #20 Θ #12 ●



Insert Arrangement

15-18

15-19

15-35

17-6

17-8

No. of Contacts

18

19

37

6

8

Contact Size

#20

#20

#22D

#12

#16

Service Rating

I




I

M

I

II

Contact Legend
 #22D • #16 +
 #20 Θ #12 ●



Insert Arrangement

17-26

17-35

19-11

19-32

No. of Contacts

26

55

11

32

Contact Size

#20

#22D

#16

#20

Service Rating

I

M

II

I

II





ADVANCED PERFORMANCE

SuperNine®





MIL-DTL-38999 Series III Type MIL-STD-1560 standard contact arrangements

SuperNine®





Contact Legend
#22D • #16 +
#20 Θ #12 ●







Insert Arrangement
No. of Contacts
Contact Size
Service Rating



Insert Arrangement
No. of Contacts
Contact Size
Service Rating



Insert Arrangement
No. of Contacts
Contact Size
Service Rating



Insert Arrangement
No. of Contacts
Contact Size
Service Rating



ADVANCED PERFORMANCE

SuperNine®




MIL-DTL-38999 Series III Type

MIL-STD-1560 standard contact arrangements

Glenair®

Contact Legend

#22D • #16 +
#20 Θ #12 ●



Insert Arrangement

23-97

No. of Contacts

16

Contact Size


#16

Service Rating

I

Contact Legend

#22D • #16 +
#20 Θ #12 ●




23-99

11

#16


II



25-19

19

#12



Insert Arrangement

25-29

No. of Contacts

29

Contact Size


#16

Service Rating

I

Contact Legend

#22D • #16 +
#20 Θ #12 ●



25-35

128

#22D

M

25-37

37

#16

II

Insert Arrangement

25-61

No. of Contacts

61

Contact Size

#20

Service Rating

I

| Test Voltage AC RMS 60Hz IAW MIL-DTL-38999 | | | | | | | | |
|--|-----------|-------|------------|-------|------------|-------|-------------|-------|
| Service Rating | Sea Level | | 50,000 Ft. | | 70,000 Ft. | | 100,000 Ft. | |
| | unmated | mated | unmated | mated | unmated | mated | unmated | mated |
| M | 1300 | 1300 | 550 | 800 | 350 | 800 | 200 | 800 |
| N | 1000 | 1000 | 400 | 600 | 260 | 600 | 200 | 600 |
| I | 1800 | 1800 | 600 | 1000 | 400 | 1000 | 200 | 1000 |
| II | 2300 | 2300 | 800 | 1000 | 500 | 1000 | 200 | 1000 |

Note: The provision of electrical safety factors in each particular application, including peak voltages, switching currents, transients, etc. is the responsibility of the electrical engineer.

ADVANCED PERFORMANCE

 SuperNine®


MIL-DTL-38999 Series III Type

MIL-STD-1560 high-density contact arrangements




 SuperNine®

| Environmental and Hermetic Contact Arrangements | | |
|---|----------------------------|--------------------|
| Contact | Number of Size 23 Contacts | Insert Arrangement |
|  | 9 | 9-23 |
| | 19 | 11-23 |
| | 32 | 13-23 |
| | 55 | 15-23 |
| | 73 | 17-23 |
| | 88 | 19-23 |
| | 121 | 21-23 |
| | 151 | 23-23 |
| | 187 | 25-23 |



857-189 Pin and 857-90 Socket
Size #23 High-Density (HD)
5 Amp Max. Current
#22-#26 AWG





| | | | | |
|--------------------|------|-------|-------|-------|
| Insert Arrangement | 9-23 | 11-23 | 13-23 | 15-23 |
| No. of Contacts | 9 | 19 | 32 | 55 |
| Contact Size | #23 | #23 | #23 | #23 |
| Service Rating | N | N | N | N |



| | | | | |
|--------------------|-------|-------|-------|--|
| Insert Arrangement | 17-23 | 19-23 | 21-23 | |
| No. of Contacts | 73 | 88 | 121 | |
| Contact Size | #23 | #23 | #23 | |
| Service Rating | N | N | N | |



| | | | |
|--------------------|-------|-------|--|
| Insert Arrangement | 23-23 | 25-23 | |
| No. of Contacts | 151 | 187 | |
| Contact Size | #23 | #23 | |
| Service Rating | N | N | |



ADVANCED PERFORMANCE

 SuperNine®




MIL-DTL-38999 Series III Type MIL-STD-1560 combo contact arrangements

Glenair®

Contact Legend

#22D • #20 Θ #16 ⊕

#12 ◑ #10 ◎



Insert Arrangement

15-15

No. of Contacts and Size

1X #16

14X #20

Service Rating

15-97

4X #16

8X #20

17-99




2X #16

21X #20

Contact Legend

#22D • #20 Θ #16 ⊕

#12 ◑ #10 ◎



Insert Arrangement

19-28

No. of Contacts and Size

2X #16

26X #20

Service Rating

19-30

1X #16

29X #20

21-29

4x #12




4X #16

19X #20

Contact Legend

#22D • #20 Θ #16 ⊕

#12 ◑ #10 ◎



Insert Arrangement

21-39

No. of Contacts and Size

2X #16

37X #20

Service Rating

25-4

8X #16

48X #20

25-11



9X #10

2x #20

Contact Legend

#22D • #20 Θ #16 ⊕

#12 ◑ #10 ◎



Insert Arrangement

25-24

No. of Contacts and Size

12X #12

12X #16

Service Rating

25-43

20X #16


23X #20

MIL-DTL-38999 Series III Type

Recommended panel cut-out dimensions

RECOMMENDED PANEL CUT-OUT

Recommended Panel Cut-Out



| Panel Cut-Out Dimensions | | | | | | | | |
|--------------------------|------------|---------------|---------------|---------------|---------------|---------------|--------------------|---------------|
| Shell Size Code | Shell Size | Jam Nut Mount | | Wall Mount | | | | |
| | | A Flat | B Dia | C BSC | CC BSC | D Dia Min | E Dia Flange Holes | F Dia Min |
| A | 9 | .661 (16.79) | .703 (17.58) | .719 (18.26) | .594 (15.09) | .656 (16.66) | | .516 (13.12) |
| | | .654 (16.61) | .693 (17.60) | | | | | .625 (15.88) |
| B | 11 | .771 (19.58) | .835 (21.21) | .812 (20.62) | .719 (18.26) | .796 (20.22) | | .750 (19.05) |
| | | .761 (19.33) | .825 (20.96) | | | | | .906 (23.01) |
| C | 13 | .955 (24.26) | 1.020 (25.91) | .906 (23.01) | .812 (20.62) | .922 (23.42) | | .133 (3.38) |
| | | .945 (24.00) | 1.010 (25.65) | | | | | .123 (3.12) |
| D | 15 | 1.085 (27.56) | 1.145 (29.08) | .969 (24.61) | .906 (23.01) | 1.047 (26.59) | | 1.016 (25.81) |
| | | 1.075 (27.31) | 1.135 (28.83) | | | | | 1.141 (28.98) |
| E | 17 | 1.210 (30.73) | 1.270 (32.26) | 1.062 (26.97) | .969 (24.61) | 1.219 (30.96) | | 1.266 (32.16) |
| | | 1.200 (30.48) | 1.260 (32.00) | | | | | |
| F | 19 | 1.335 (33.91) | 1.395 (35.43) | 1.156 (29.36) | 1.062 (26.97) | 1.297 (32.94) | | |
| | | 1.325 (33.66) | 1.385 (35.18) | | | | | |
| G | 21 | 1.460 (37.08) | 1.520 (38.61) | 1.250 (31.75) | 1.156 (29.36) | 1.422 (36.12) | | |
| | | 1.450 (36.83) | 1.510 (38.35) | | | | | |
| H | 23 | 1.585 (40.26) | 1.645 (41.78) | 1.375 (34.93) | 1.250 (31.75) | 1.547 (39.29) | .159 (4.04) | 1.375 (34.93) |
| | | 1.575 (40.01) | 1.635 (41.53) | | | | .149 (3.78) | |
| J | 25 | 1.710 (43.43) | 1.770 (44.96) | 1.500 (38.10) | 1.375 (34.92) | 1.672 (42.47) | .155 (3.94) | 1.484 (37.69) |
| | | 1.700 (43.18) | 1.760 (44.70) | | | | .145 (3.68) | |

ADVANCED PERFORMANCE


 SuperNine®



MIL-DTL-38999 Series III Type

Alternate key polarization

ALTERNATE POLARIZATIONS IAW MIL-DTL-38999 SERIES III



**Alternate Keyway,
Receptacles**

**Alternate Key,
Plugs**

| Series III Alternate Key and Keyway Polarization | | | | | |
|--|---------------------|----------------|----------------|----------------|----------------|
| Shell Size | Key and Keyway Code | AR° or AP° BSC | BR° or BP° BSC | CR° or CP° BSC | DR° or DP° BSC |
| 9 | N | 105 | 140 | 215 | 265 |
| | A | 102 | 132 | 248 | 320 |
| | B | 80 | 118 | 230 | 312 |
| | C | 35 | 140 | 205 | 275 |
| | D | 64 | 155 | 234 | 304 |
| | E | 91 | 131 | 197 | 240 |
| 11 | N | 95 | 141 | 208 | 236 |
| | A | 113 | 156 | 182 | 292 |
| | B | 90 | 145 | 195 | 252 |
| | C | 53 | 156 | 220 | 255 |
| | D | 119 | 146 | 176 | 298 |
| | E | 51 | 141 | 184 | 242 |
| 13 | N | 80 | 142 | 196 | 293 |
| | A | 135 | 170 | 200 | 310 |
| | B | 49 | 169 | 200 | 244 |
| | C | 66 | 140 | 200 | 257 |
| | D | 62 | 145 | 180 | 280 |
| | E | 79 | 153 | 197 | 272 |
| 15 | N | 80 | 142 | 196 | 293 |
| | A | 135 | 170 | 200 | 310 |
| | B | 49 | 169 | 200 | 244 |
| | C | 66 | 140 | 200 | 257 |
| | D | 62 | 145 | 180 | 280 |
| | E | 79 | 153 | 197 | 272 |
| 17 | N | 80 | 142 | 196 | 293 |
| | A | 135 | 170 | 200 | 310 |
| | B | 49 | 169 | 200 | 244 |
| | C | 66 | 140 | 200 | 257 |
| | D | 62 | 145 | 180 | 280 |
| | E | 79 | 153 | 197 | 272 |
| 19 | N | 80 | 142 | 196 | 293 |
| | A | 135 | 170 | 200 | 310 |
| | B | 49 | 169 | 200 | 244 |
| | C | 66 | 140 | 200 | 257 |
| | D | 62 | 145 | 180 | 280 |
| | E | 79 | 153 | 197 | 272 |
| 21 | N | 80 | 142 | 196 | 293 |
| | A | 135 | 170 | 200 | 310 |
| | B | 49 | 169 | 200 | 244 |
| | C | 66 | 140 | 200 | 257 |
| | D | 62 | 145 | 180 | 280 |
| | E | 79 | 153 | 197 | 272 |
| 23 | N | 80 | 142 | 196 | 293 |
| | A | 135 | 170 | 200 | 310 |
| | B | 49 | 169 | 200 | 244 |
| | C | 66 | 140 | 200 | 257 |
| | D | 62 | 145 | 180 | 280 |
| | E | 79 | 153 | 197 | 272 |
| 25 | N | 80 | 142 | 196 | 293 |
| | A | 135 | 170 | 200 | 310 |
| | B | 49 | 169 | 200 | 244 |
| | C | 66 | 140 | 200 | 257 |
| | D | 62 | 145 | 180 | 280 |
| | E | 79 | 153 | 197 | 272 |

Glenair's Universal Key is intermateable with all MIL-DTL-38999 Series III polarizations.

Space-grade, blind-mate connectors

MIL-DTL-38999 Series III Type Space-Grade Connectors

Environmental flange mount plug, blind mate, crimp removable contacts

| Part Number Development | | | | | | | |
|----------------------------------|--|--|---|----|----|-------|-----|
| Sample Part Number | 253-014 | | - | 07 | ME | 25-35 | P N |
| Series / Basic Part No. | 253-014 = Plug (fixed mount) Blind-mate | | | | | | |
| Accessory Option | B = Integral Banding Porch - (dash) = Accessory Thread | | | | | | |
| Connector Style | 07 = Jam nut mount 00 = Plug, wall mount with slotted holes D0 = Plug, wall mount with round holes | | | | | | |
| Material/Finish | ME = Aluminum, electroless nickel ZL = CRES, electrodeposited nickel MT = Aluminum, nickel PTFE Z1 = CRES, passivated | | | | | | |
| Shell Size - Insert Arrangement* | Per MIL-STD-1560; symmetrical layouts only, consult factory for complete details | | | | | | |
| Contact Type | P = Pin, crimp removable S = Socket, crimp removable A = Pin insert, less contacts B = Socket insert, less contacts | | | | | | |
| Alternate Polarization | A, B, C, D, E, N = Normal (Polarization for intermateability with 253-014 is per MIL-DTL-38999 Series I) | | | | | | |



*Refer to C-5 to C-12 for insert arrangements.

For Space-Grade modification codes see pages C-3 thru C-4. Modification codes may be added directly to the end of any valid part number

NOTES:

1. Material/finish
 - Shell, jam-nut: see P/N development, finish
 - Insulator: high grade rigid dielectric/N.A.
 - Seals: fluorosilicone blend/N.A.
 - Contacts: copper alloy/gold plated
2. Glenair 253-014 is designed to mate with 253-015 with same insert arrangement.
3. Insert arrangements are in accordance with MIL-STD-1560, except for arrangements with size 8 contacts. Contact factory for available options.
4. Polarization for intermateability with 253-015 is per MIL-DTL-38999 Series I
5. Contact manufacturer for outgassing options
6. Misalignment capabilities are possible with mated pair. Reference Glenair connector 253-015
7. Stainless steel locating pin ($\varnothing 0.079$) to be shipped with connector
8. For part numbers consisting of P (pin) or S (socket), the contacts provided are IAW with AS39029/56 or AS39029/58

DISTANCE BETWEEN MATED FLANGES




Space-grade, blind-mate connectors

MIL-DTL-38999 Series III Type Space-Grade Connectors

Environmental flange mount plug, blind mate, crimp removable contacts



253-014-07 FIXED JAM-NUT MOUNT PLUG WITH ROLL-ON/ROLL-OFF NOSE




| 253-014-07 Dimensions | | | | | | | | | |
|-----------------------|---------------|-------------------|---------------|---------------|---------------|-------------------|---------------|---------------|---------------|
| Shell Size | A Max Dia. | Thread B Class 2A | C Max | E (.±016) | F Max Dia. | G Thread Class 2A | H (+0/-0.008) | Ø Y | Ø Z |
| 11 | .673 (17.09) | .8125-20 UNEF | 1.016 (25.81) | 1.250 (31.75) | 1.386 (35.20) | .5625-24 | .604 (15.34) | 0.600 (15.24) | 0.662 (16.81) |
| 13 | .798 (20.27) | 1.0000-20 UNEF | 1.181 (30.00) | 1.375 (34.92) | 1.511 (38.38) | .6875-24 | .666 (16.92) | 0.700 (17.78) | 0.762 (19.35) |
| 15 | .923 (23.44) | 1.1250-18 UNEF | 1.300 (33.02) | 1.500 (38.10) | 1.636 (41.55) | .8125-20 | .729 (18.52) | 0.835 (21.21) | 0.898 (22.81) |
| 17 | 1.048 (26.62) | 1.2500-18 UNEF | 1.457 (37.01) | 1.625 (41.28) | 1.761 (44.73) | .9375-20 | .791 (20.09) | 0.960 (24.38) | 1.022 (25.96) |
| 19 | 1.173 (29.79) | 1.3750-18 UNEF | 1.575 (40.00) | 1.812 (46.02) | 1.949 (49.50) | 1.0625-18 | .893 (22.68) | 1.062 (26.97) | 1.125 (28.58) |
| 21 | 1.298 (32.97) | 1.5000-18 UNEF | 1.693 (43.00) | 1.938 (49.23) | 2.073 (52.65) | 1.1875-18 | .955 (24.26) | 1.188 (30.18) | 1.250 (31.75) |
| 23 | 1.423 (36.14) | 1.6250-18 UNEF | 1.880 (47.75) | 2.062 (52.37) | 2.200 (55.88) | 1.3125-18 | 1.017 (25.83) | 1.275 (32.39) | 1.338 (33.99) |
| 25 | 1.548 (39.32) | 1.7500-18 UNS | 2.016 (51.21) | 2.187 (55.55) | 2.323 (59.00) | 1.4375-18 | 1.096 (27.84) | 1.475 (37.47) | 1.538 (39.07) |

Space-grade, blind-mate connectors

MIL-DTL-38999 Series III Type Space-Grade Connectors

Plug and receptacle pair with misalignment accommodation and optional sealing

253-014-00 PLUG, WALL MOUNT WITH ROLL-ON/ROLL-OFF NOSE AND ACCESSORY THREADS



| 253-014-00 Dimensions | | | | | | | | |
|-----------------------|-------------------|---------------|---------------|---------------|--------------|--------------|---------------------|----------------|
| Shell Size | Diameter AA, Max. | D +/- .012 | J | L | M +/- .008 | N +/- .008 | Thread GG, Class 2a | KK +.011/-0.10 |
| 11 | 0.673 (17.09) | 1.031 (26.19) | 0.812 (20.62) | 0.719 (18.26) | 0.194 (4.93) | 0.128 (3.25) | 0.5625-24 | 0.109 (2.77) |
| 13 | 0.798 (20.27) | 1.126 (28.60) | 0.906 (23.01) | 0.812 (20.62) | 0.194 (4.93) | 0.128 (3.25) | 0.6875-24 | 0.109 (2.77) |
| 15 | 0.923 (23.44) | 1.220 (30.99) | 0.969 (24.61) | 0.906 (23.01) | 0.173 (4.39) | 0.128 (3.25) | 0.8125-20 | 0.109 (2.77) |
| 17 | 1.048 (26.62) | 1.311 (33.30) | 1.062 (26.97) | 0.969 (24.61) | 0.194 (4.93) | 0.128 (3.25) | 0.9375-20 | 0.109 (2.77) |
| 19 | 1.173 (29.79) | 1.437 (36.50) | 1.156 (29.36) | 1.062 (26.97) | 0.194 (4.93) | 0.128 (3.25) | 1.0625-18 | 0.140 (3.56) |
| 21 | 1.298 (32.97) | 1.563 (39.70) | 1.250 (31.75) | 1.156 (29.36) | 0.194 (4.93) | 0.128 (3.25) | 1.1875-18 | 0.140 (3.56) |
| 23 | 1.423 (36.14) | 1.689 (42.90) | 1.375 (34.92) | 1.250 (31.75) | 0.242 (6.15) | 0.154 (3.91) | 1.3125-18 | 0.140 (3.56) |
| 25 | 1.548 (39.32) | 1.811 (46.00) | 1.500 (38.10) | 1.375 (34.92) | 0.242 (6.15) | 0.154 (3.91) | 1.4375-18 | 0.140 (3.56) |

| Recommended Panel Cutout for Slotted Hole and Round Hole Connectors | | |
|---|---------------|------------------|
| Shell Size | WW | Diameter BB Min. |
| 11 | 0.812 (20.62) | 0.796 (20.22) |
| 13 | 0.906 (23.01) | 0.922 (23.42) |
| 15 | 0.969 (24.61) | 1.047 (26.59) |
| 17 | 1.062 (26.97) | 1.219 (30.96) |
| 19 | 1.156 (29.36) | 1.297 (32.94) |
| 21 | 1.250 (31.75) | 1.422 (36.12) |
| 23 | 1.375 (34.92) | 1.547 (39.29) |
| 25 | 1.500 (38.10) | 1.672 (42.47) |


Space-grade, blind-mate connectors

MIL-DTL-38999 Series III Type Space-Grade Connectors

Environmental flange mount plug, blind mate, crimp removable contacts



253-014-DO WALL MOUNT PLUG WITH ROUND HOLES AND ROLL-ON/ROLL-OFF NOSE



| 253-014-00 Dimensions | | | | | | |
|-----------------------|------------------|---------------|---------------|---------------|--------------------|------------------|
| Shell Size | Diameter U, Max. | P $^{+.012}$ | R | T $.010/-005$ | Thread V, Class 2A | L $[+.011/-010]$ |
| 11 | 0.673 (17.09) | 1.031 (26.19) | 0.812 (20.62) | 0.128 (3.25) | 0.5625-24 | 0.109 (2.77) |
| 13 | 0.798 (20.27) | 1.126 (28.60) | 0.906 (23.01) | 0.128 (3.25) | 0.6875-24 | 0.109 (2.77) |
| 15 | 0.923 (23.44) | 1.220 (30.99) | 0.969 (24.61) | 0.128 (3.25) | 0.8125-20 | 0.109 (2.77) |
| 17 | 1.048 (26.62) | 1.311 (33.30) | 1.062 (26.97) | 0.128 (3.25) | 0.9375-20 | 0.109 (2.77) |
| 19 | 1.173 (29.79) | 1.437 (36.50) | 1.156 (29.36) | 0.128 (3.25) | 1.0625-18 | 0.140 (3.56) |
| 21 | 1.298 (32.97) | 1.563 (39.70) | 1.250 (31.75) | 0.128 (3.25) | 1.1875-18 | 0.140 (3.56) |
| 23 | 1.423 (36.14) | 1.689 (42.90) | 1.375 (34.92) | 0.154 (3.91) | 1.3125-18 | 0.140 (3.56) |
| 25 | 1.548 (39.32) | 1.811 (46.00) | 1.500 (38.10) | 0.154 (3.91) | 1.4375-18 | 0.140 (3.56) |

| Recommended Panel Cutout for Slotted Hole and Round Hole Connectors | | |
|---|---------------|------------------|
| Shell Size | WW | Diameter BB Min. |
| 11 | 0.812 (20.62) | 0.796 (20.22) |
| 13 | 0.906 (23.01) | 0.922 (23.42) |
| 15 | 0.969 (24.61) | 1.047 (26.59) |
| 17 | 1.062 (26.97) | 1.219 (30.96) |
| 19 | 1.156 (29.36) | 1.297 (32.94) |
| 21 | 1.250 (31.75) | 1.422 (36.12) |
| 23 | 1.375 (34.92) | 1.547 (39.29) |
| 25 | 1.500 (38.10) | 1.672 (42.47) |

Space-grade blind-mate connectors

MIL-DTL-38999 Series III Type Space-Grade Connectors

Receptacle with misalignment accommodation and optional sealing

| Part Number Development | | | | | | | | | |
|----------------------------------|--|---|----|----|-------|---|---|----|---|
| Sample Part Number | 253-015 | B | 07 | ME | 25-35 | P | N | NS | H |
| Series / Basic Part No. | 253-015 = Receptacle (float mount) | | | | | | | | |
| Accessory Option | B = Integral Backshell — (dash) = Accessory Threads | | | | | | | | |
| Connector Style | 07 = Jam nut mount 00 = Receptacle Wall Mount with Slotted Holes D0 = Receptacle, Wall Mount with Round Holes | | | | | | | | |
| Material/Finish | ME = Aluminum, electroless nickel ZL = CRES, electrodeposited nickel MT = Aluminum, nickel PTFE Z1 = CRES, passivated | | | | | | | | |
| Shell Size - Insert Arrangement* | Per MIL-STD-1560; symmetrical layouts only, consult factory for complete details | | | | | | | | |
| Contact Type | P = Pin, crimp removable S = Socket, crimp removable A = Pin insert, less contacts B = Socket insert, less contacts | | | | | | | | |
| Alternate Polarization | A, B, C, D, E, N = Normal (Polarization for intermateability with 253-014 is per MIL-DTL-38999 Series I) | | | | | | | | |
| Non Sealing | NS = Non-Sealing (omit for external elastomer seal version) | | | | | | | | |
| Jam-Nut Type | H = Hex S = Spanner with wire holes | | | | | | | | |


*Refer to C-5 to C-12 for insert arrangements.

For Space-Grade modification codes see pages C-3 thru C-4. Modification codes may be added directly to the end of any valid part number

NOTES:

1. Material/finish
 - Shell, jam-nut: see P/N dev., finish
 - Wave spring: CRES 17-7PH/Passivate
 - Insulator: high grade rigid dielectric/N.A.
 - Seals: fluorosilicone blend/N.A.
 - Contacts: copper alloy/gold plated
2. Glenair 253-015 is designed to mate with 253-014 with same insert arrangement and polarization.
3. Insert arrangements are in accordance with MIL-STD-1560, except for arrangements with size 8 contacts. Contact factory for available options.
4. Polarization for intermateability with 253-014 is per MIL-DTL-38999 Series I
5. See Space Grade and Outgassing Options of this section
6. Misalignment capabilities are possible with mated pair. Reference Glenair connector 253-014
7. Stainless steel locating pin ($\varnothing 0.079$) to be shipped with connector
8. Blue color band indicates rear release retention system
9. Jam nut style 'H' or 'S' per dimensions listed in 253-015-07
10. For part numbers consisting of P (pin) or S (socket), the contacts provided are IAW with AS39029/56 or AS39029/58

253-015-07 BOOT GROOVE EXAMPLE OF JAM-NUT CONNECTOR



| 253-015-07 Boot Groove Dimensions | | | | | | | |
|-----------------------------------|------------------|--------------------|-----------------|------------------|----------------------|-----------------|-----------------|
| Shell Size | Diameter A, Max. | Thread B, Class 2A | E [$+/-.016$] | Diameter F, Max. | H [$+.008/-0.008$] | $\varnothing Y$ | $\varnothing Z$ |
| 11 | 0.853 (21.67) | 1.0000-20 UNEF | 1.266 (32.16) | 1.500 (38.10) | 0.666 (16.92) | 0.600 (15.24) | 0.662 (16.81) |
| 13 | 0.978 (24.84) | 1.1250-18 UNEF | 1.391 (35.33) | 1.641 (41.68) | 0.729 (18.52) | 0.700 (17.78) | 0.762 (19.35) |
| 15 | 1.103 (28.02) | 1.2500-18 UNEF | 1.516 (38.51) | 1.750 (44.45) | 0.791 (20.09) | 0.835 (21.21) | 0.898 (22.81) |
| 17 | 1.228 (31.19) | 1.3750-18 UNEF | 1.641 (41.68) | 1.938 (49.23) | 0.893 (22.68) | 0.960 (24.38) | 1.022 (25.96) |
| 19 | 1.353 (34.37) | 1.5000-18 UNEF | 1.828 (46.43) | 2.062 (52.37) | 0.955 (24.26) | 1.062 (26.97) | 1.125 (28.58) |
| 21 | 1.478 (37.54) | 1.6250-18 UNEF | 1.954 (49.63) | 2.188 (55.58) | 1.017 (25.83) | 1.188 (30.18) | 1.250 (31.75) |
| 23 | 1.603 (40.72) | 1.7500-18 UNS | 2.078 (52.78) | 2.312 (58.72) | 1.080 (27.43) | 1.275 (32.39) | 1.338 (33.99) |
| 25 | 1.728 (43.89) | 1.8750-16 UNS | 2.128 (54.05) | 2.327 (59.11) | 1.086 (27.58) | 1.475 (37.47) | 1.538 (39.07) |


Space-grade blind-mate connectors

MIL-DTL-38999 Series III Type Space-Grade Connectors




Receptacle with misalignment accommodation and optional sealing



253-015-07 FLOATING, JAM-NUT MOUNT RECEPTACLE WITH MISALIGNMENT ACCOMMODATION AND OPTIONAL SEALING



| 253-015-07 Dimensions | | | | | | | | | |
|-----------------------|---------------|-------------------|---------------|---------------|---------------|---------------|----------------|-------------------------|------------------------|
| Shell Size | A Max Dia. | Thread B Class 2A | C Max. | Y Hex | E ±.016(.41) | F Max Dia. | G Thd Class 2A | K +.011/.010 (+.28/.25) | H +0/-0.008 (+0/-0.20) |
| 11 | .853 (21.67) | 1.0000-20 UNEF | 1.264 (32.11) | 1.181 (30.00) | 1.266 (32.16) | 1.500 (38.10) | .5625-24 | .109 (2.77) | .666 (16.92) |
| 13 | .978 (24.84) | 1.1250-18 UNEF | 1.388 (35.26) | 1.300 (33.02) | 1.391 (35.33) | 1.641 (41.68) | .6875-24 | .109 (2.77) | .729 (18.52) |
| 15 | 1.103 (28.02) | 1.2500-18 UNEF | 1.512 (38.40) | 1.457 (37.01) | 1.516 (38.51) | 1.750 (44.45) | .8125-20 | .109 (2.77) | .791 (20.09) |
| 17 | 1.228 (31.19) | 1.3750-18 UNEF | 1.638 (41.61) | 1.575 (40.00) | 1.641 (41.68) | 1.938 (49.23) | .9375-20 | .109 (2.77) | .893 (22.68) |
| 19 | 1.353 (34.37) | 1.5000-18 UNEF | 1.823 (46.30) | 1.693 (43.00) | 1.828 (46.43) | 2.062 (52.37) | 1.0625-18 | .140 (3.56) | .955 (24.26) |
| 21 | 1.478 (37.54) | 1.6250-18 UNEF | 1.953 (49.61) | 1.880 (47.75) | 1.954 (49.63) | 2.188 (55.58) | 1.1875-18 | .140 (3.56) | 1.017 (25.83) |
| 23 | 1.603 (40.72) | 1.7500-18 UNS | 2.075 (52.71) | 2.010 (51.05) | 2.078 (52.78) | 2.312 (58.72) | 1.3125-18 | .140 (3.56) | 1.080 (27.43) |
| 25 | 1.728 (43.89) | 1.8750-16 UNS | 2.122 (53.90) | 2.125 (53.97) | 2.128 (54.05) | 2.327 (59.11) | 1.4375-18 | .140 (3.56) | 1.086 (27.58) |



| 253-015 Recommended Panel Cutout Dimensions | | | |
|---|--------------|--------------------|---------------|
| Shell Size | W | B Dia. ±.004 (.10) | S |
| 11 | .504 (12.80) | 1.007 (25.58) | 1.282 (32.56) |
| 13 | .549 (13.94) | 1.134 (28.80) | 1.417 (35.99) |
| 15 | .593 (15.06) | 1.259 (31.98) | 1.559 (39.60) |
| 17 | .665 (16.89) | 1.384 (35.15) | 1.705 (43.31) |
| 19 | .709 (18.01) | 1.507 (38.28) | 1.850 (46.99) |
| 21 | .753 (19.13) | 1.634 (41.50) | 1.992 (50.60) |
| 23 | .797 (20.24) | 1.759 (44.68) | 2.134 (54.20) |
| 25 | .799 (20.29) | 1.884 (47.85) | 2.262 (57.45) |


Space-grade blind-mate connectors

MIL-DTL-38999 Series III Type Space-Grade Connectors

Receptacle with misalignment accommodation and optional sealing

253-015-00 FLOATING, SLOTTED HOLE WALL MOUNT RECEPTACLE WITH MISALIGNMENT ACCOMMODATION AND OPTIONAL SEALING

Connector Shown Does Not Include Sealing Option




| RECOMMENDED PANEL CUTOUT FOR SLOTED HOLE CONNECTORS | | | | |
|---|-------|-------|-----------|------------|
| SHELL SIZE | WW | WW' | Ø BB MIN. | Ø BB' MIN. |
| 11 | 0.906 | 1.062 | 0.984 | 1.062 |
| 13 | 0.969 | 1.156 | 1.109 | 1.156 |
| 15 | 1.062 | 1.250 | 1.234 | 1.250 |
| 17 | 1.156 | 1.375 | 1.359 | 1.375 |
| 19 | 1.250 | 1.500 | 1.484 | 1.500 |
| 21 | 1.375 | 1.625 | 1.609 | 1.625 |
| 23 | 1.500 | 1.750 | 1.734 | 1.750 |
| 25 | 1.625 | 1.875 | 1.859 | 1.875 |

253-015-00 Dimensions


| Shell Size | Diameter AA, Max. | E +/- .012 | E' +/- .012 | J | J' | L | L' | M +/- .008 | M' +/- .008 | N +/- .008 | N' +/- .008 | Thread GG, Class 2A | KK [+0.011/-0.010] |
|------------|-------------------|---------------|---------------|---------------|---------------|---------------|---------------|--------------|--------------|--------------|--------------|---------------------|--------------------|
| 11 | 0.853 (21.67) | 1.126 (28.60) | 1.311 (33.30) | 0.906 (23.01) | 1.062 (26.97) | 0.812 (20.62) | 0.969 (24.61) | 0.194 (4.93) | 0.194 (4.93) | 0.128 (3.25) | 0.128 (3.25) | 0.5625-24 | 0.109 (2.77) |
| 13 | 0.978 (24.84) | 1.220 (30.99) | 1.437 (36.50) | 0.969 (24.61) | 1.156 (29.36) | 0.906 (23.01) | 1.062 (26.97) | 0.173 (4.39) | 0.194 (4.93) | 0.128 (3.25) | 0.128 (3.25) | 0.6875-24 | 0.109 (2.77) |
| 15 | 1.103 (28.02) | 1.311 (33.30) | 1.563 (39.70) | 1.062 (26.97) | 1.250 (31.75) | 0.969 (24.61) | 1.156 (29.36) | 0.194 (4.93) | 0.194 (4.93) | 0.128 (3.25) | 0.128 (3.25) | 0.8125-20 | 0.109 (2.77) |
| 17 | 1.228 (31.19) | 1.437 (36.50) | 1.689 (42.90) | 1.156 (29.36) | 1.375 (34.92) | 1.062 (26.97) | 1.250 (31.75) | 0.194 (4.93) | 0.216 (5.49) | 0.128 (3.25) | 0.128 (3.25) | 0.9375-20 | 0.109 (2.77) |
| 19 | 1.353 (34.37) | 1.563 (39.70) | 1.811 (46.00) | 1.250 (31.75) | 1.500 (38.10) | 1.156 (29.36) | 1.375 (34.92) | 0.194 (4.93) | 0.242 (6.15) | 0.128 (3.25) | 0.154 (3.91) | 1.0625-18 | 0.140 (3.56) |
| 21 | 1.478 (37.54) | 1.689 (42.90) | 1.952 (49.58) | 1.375 (34.92) | 1.625 (41.28) | 1.250 (31.75) | 1.500 (38.10) | 0.242 (6.15) | 0.242 (6.15) | 0.154 (3.91) | 0.154 (3.91) | 1.1875-18 | 0.140 (3.56) |
| 23 | 1.603 (40.72) | 1.811 (46.00) | 2.093 (53.16) | 1.500 (38.10) | 1.750 (44.45) | 1.375 (34.92) | 1.625 (41.28) | 0.242 (6.15) | 0.242 (6.15) | 0.154 (3.91) | 0.154 (3.91) | 1.3125-18 | 0.140 (3.56) |
| 25 | 1.728 (43.89) | 1.952 (49.58) | 2.234 (56.74) | 1.625 (41.28) | 1.875 (47.63) | 1.500 (38.10) | 1.750 (44.45) | 0.242 (6.15) | 0.242 (6.15) | 0.154 (3.91) | 0.154 (3.91) | 1.4375-18 | 0.140 (3.56) |

253-015 Misalignment Capabilities



Distance between mated flanges.

For reference only (not deliverable)




Space-grade blind-mate connectors

MIL-DTL-38999 Series III Type Space-Grade Connectors

Receptacle with misalignment accommodation and optional sealing


253-015-D0 FLOATING, JAM-NUT MOUNT RECEPTACLE WITH MISALIGNMENT ACCOMMODATION AND OPTIONAL SEALING



| RECOMMENDED PANEL CUTOUT FOR SLOTTED HOLE CONNECTORS | | | | |
|--|-------|-------|-----------|------------|
| SHELL SIZE | WW | WW' | Ø BB MIN. | Ø BB' MIN. |
| 11 | 0.906 | 1.062 | 0.984 | 1.062 |
| 13 | 0.969 | 1.156 | 1.109 | 1.156 |
| 15 | 1.062 | 1.250 | 1.234 | 1.250 |
| 17 | 1.156 | 1.375 | 1.359 | 1.375 |
| 19 | 1.250 | 1.500 | 1.484 | 1.500 |
| 21 | 1.375 | 1.625 | 1.609 | 1.625 |
| 23 | 1.500 | 1.750 | 1.734 | 1.750 |
| 25 | 1.625 | 1.875 | 1.859 | 1.875 |


| 253-015-D0 Dimensions | | | | | | | | |
|-----------------------|------------------|---------------|---------------|---------------|---------------|--------------|--------------------|-------------------|
| SHELL SIZE | DIAMETER U, MAX. | P +/- .012 | P' +/- .012 | R | R' | T +/- .008 | THREAD V, CLASS 2A | L +/- .011/- .010 |
| 11 | 0.853 (21.67) | 1.126 (28.60) | 1.311 (33.30) | 0.906 (23.01) | 1.062 (26.97) | 0.128 (3.25) | 0.5625-24 | 0.109 (2.77) |
| 13 | 0.978 (24.84) | 1.220 (30.99) | 1.437 (36.50) | 0.969 (24.61) | 1.156 (29.36) | 0.128 (3.25) | 0.6875-24 | 0.109 (2.77) |
| 15 | 1.103 (28.02) | 1.311 (33.30) | 1.563 (39.70) | 1.062 (26.97) | 1.250 (31.75) | 0.128 (3.25) | 0.8125-20 | 0.109 (2.77) |
| 17 | 1.228 (31.19) | 1.437 (36.50) | 1.689 (42.90) | 1.156 (29.36) | 1.375 (34.92) | 0.128 (3.25) | 0.9375-20 | 0.109 (2.77) |
| 19 | 1.353 (34.37) | 1.563 (39.70) | 1.811 (46.00) | 1.250 (31.75) | 1.500 (38.10) | 0.128 (3.25) | 1.0625-18 | 0.140 (3.56) |
| 21 | 1.478 (37.54) | 1.689 (42.90) | 1.952 (49.58) | 1.375 (34.92) | 1.625 (41.28) | 0.154 (3.91) | 1.1875-18 | 0.140 (3.56) |
| 23 | 1.603 (40.72) | 1.811 (46.00) | 2.093 (53.16) | 1.500 (38.10) | 1.750 (44.45) | 0.154 (3.91) | 1.3125-18 | 0.140 (3.56) |
| 25 | 1.728 (43.89) | 1.952 (49.58) | 2.234 (56.74) | 1.625 (41.28) | 1.875 (47.63) | 0.154 (3.91) | 1.4375-18 | 0.140 (3.56) |

253-015 Misalignment Capabilities



Distance between mated flanges.

For reference only (not deliverable)



Space-grade blind-mate connectors

MIL-DTL-38999 Series III Type Space-Grade Connectors




Hermetic rack and panel receptacle, jam-nut mount

| Part Number Development | | | | | | |
|----------------------------------|--|--|--|-----|----|-------|
| Sample Part Number | 253-022 | | | -H7 | Z1 | 15-18 |
| Series / Basic Part No. | 253-022 = Blind mate, jam-nut mount rack and panel receptacle | | | S | N | |
| Connector Style | H7 = Hermetic jam nut mount; contact factory for wall mount receptacles | | | | | |
| Material/Finish | ZL = CRES, electrodeposited nickel Z1 = CRES, passivated | | | | | |
| Shell Size - Insert Arrangement* | See Dimensions Table. Per MIL-STD-1560. | | | | | |
| Contact Type | P = Pin, crimp removable C = Pin, PCB S = Socket, solder cup D = Socket, PCB | | | | | |
| Alternate Polarization | A, B, C, D, E, N = Normal (Polarization for intermateability with 253-014 is per MIL-DTL-38999 Series I) | | | | | |

*Refer to C-5 to C-12 for insert arrangements.

For Space-Grade modification codes see pages C-3 thru C-4. Modification codes may be added directly to the end of any valid part number

253-022 FIXED JAM-NUT MOUNT HERMETIC RECEPTACLE WITH ROLL-ON/ROLL-OFF NOSE



NOTES:

1. Glenair 253-022 is designed to mate with 253-015 with same insert arrangement.
2. Misalignment capabilities are possible when mated to 253-015.
3. Contact manufacturer for outgassing options.
4. Material/finish
 - Shell, jam-nut: see P/N development; finish
 - Insulator: fused vitreous/N.A.
 - Seals, O-ring: fluorosilicone blend/N.A.
 - Contacts: 52 nickel alloy/gold plated
 - Socket insert: high grade rigid dielectric/N.A.

| Dimensions | | | | | | | | | |
|------------|---------------|--------------------|---------------|---------------|---------------|--------------|---------------------|---------------------|-------------------|
| SHELL SIZE | Ø A MAX | THREAD B, CLASS 2A | C, MAX. | S [±.016] | Ø DD [±.016] | K [±.016] | Ø T [+0.011/-0.000] | Ø M [+0.010/-0.000] | N [+0.000/-0.010] |
| 11 | 0.673 (17.09) | .8125-20 UNEF | 1.016 (25.81) | 1.250 (31.75) | 1.375 (34.92) | 0.109 (2.77) | 0.766 (19.46) | 0.825 (20.96) | 0.771 (19.58) |
| 13 | 0.798 (20.27) | 1.0000-20 UNEF | 1.204 (30.58) | 1.375 (34.92) | 1.500 (38.10) | 0.109 (2.77) | 0.892 (22.66) | 1.010 (25.65) | 0.955 (24.26) |
| 15 | 0.923 (23.44) | 1.1250-18 UNEF | 1.328 (33.73) | 1.500 (38.10) | 1.625 (41.28) | 0.109 (2.77) | 1.018 (25.86) | 1.135 (28.83) | 1.085 (27.56) |
| 17 | 1.048 (26.62) | 1.2500-18 UNEF | 1.454 (36.93) | 1.625 (41.28) | 1.750 (44.45) | 0.109 (2.77) | 1.142 (29.01) | 1.260 (32.00) | 1.210 (30.73) |
| 19 | 1.173 (29.79) | 1.3750-18 UNEF | 1.578 (40.08) | 1.812 (46.02) | 1.938 (49.23) | 0.140 (3.56) | 1.268 (32.21) | 1.385 (35.18) | 1.335 (33.91) |
| 21 | 1.298 (32.97) | 1.5000-18 UNEF | 1.704 (43.28) | 1.938 (49.23) | 2.062 (52.37) | 0.140 (3.56) | 1.392 (35.36) | 1.510 (38.35) | 1.460 (37.08) |
| 23 | 1.423 (36.14) | 1.6250-18 UNEF | 1.828 (46.43) | 2.062 (52.37) | 2.188 (55.58) | 0.140 (3.56) | 1.518 (38.56) | 1.635 (41.53) | 1.585 (40.26) |
| 25 | 1.548 (39.32) | 1.7500-18 UNS | 2.016 (51.21) | 2.188 (55.58) | 2.312 (58.72) | 0.140 (3.56) | 1.642 (41.71) | 1.760 (44.70) | 1.710 (43.43) |

Space-grade, blind mate connectors

MIL-DTL-38999 Series III Type Space-Grade Connectors


Plug and receptacle pair with misalignment accommodation



| Part Number Development | | | | | | | | | | | |
|-------------------------------|--|--|--|--|----|----|-------|---|---|----|---|
| Sample Part Number | 253-016 | | | | 00 | ME | 21-35 | S | N | MS | A |
| Series / Basic Part No. | 253 = Blind-mate connector with adjustable separation force -016 = Plug (fixed mount) -017 = Receptacle (float mount) | | | | | | | | | | |
| Connector Style | 00 = Wall mount | | | | | | | | | | |
| Material/Finish | ME = Aluminum, electroless nickel ZL = CRES, electrodeposited nickel MT = Aluminum, nickel PTFE Z1 = CRES, passivated | | | | | | | | | | |
| Shell Size-Insert Arrangement | Per MIL-STD-1560 | | | | | | | | | | |
| Contact Type | P = Pin, crimp removable S = Socket, crimp removable | | | | | | | | | | |
| Alternate Polarization | A = 40°, B = 65°, C = 80°, D = 210°, E = 250°, F = 280°, G = 310°, H = 330°, N = 135° (Normal) Per L° | | | | | | | | | | |
| Contact Type | MS = Military specification | | | | | | | | | | |
| Adjustment Ring Material | (253-017 receptacle only) A = Aluminum C = Corrosion-resistant steel | | | | | | | | | | |

*Refer to C-5 to C-12 for insert arrangements.

For Space-Grade modification codes see pages C-3 thru C-4. Modification codes may be added directly to the end of any valid part number

253-016 FIXED WALL MOUNT PLUG WITH ADJUSTABLE ZERO SEPARATION FORCE (ZSF)

Recommended Panel Cut-out


| Dimensions for 253-016 and 253-017 | | | | | | | | | |
|------------------------------------|------------------------|---------------|-------------------|--------------|---------------|---------------------|--------------------------------|--------------------------------|---------------|
| Shell Size | F Flange ±.010 (.±.25) | M Square | Ø H ±.005 (.±.13) | Ø D Max. | Ø E Max. | A Thread | Ø P ₁ ±.005 (.±.13) | Ø P ₂ ±.005 (.±.13) | G Square |
| 9 | 1.430(36.32) | 1.150 (29.21) | .128(3.25) | 1.250(31.75) | 1.300 (33.02) | M12 X 1.0-6g-0.100R | 1.300(33.02) | 1.330 (33.78) | 1.150 (29.21) |
| 11 | 1.555(39.50) | 1.200(30.48) | .128(3.25) | 1.375(34.93) | 1.425 (36.20) | M15 X 1.0-6g-0.100R | 1.425(36.20) | 1.455 (36.96) | 1.200 (30.48) |
| 13 | 1.680(42.67) | 1.250(31.75) | .128(3.25) | 1.500(38.10) | 1.550 (39.37) | M18 X 1.0-6g-0.100R | 1.550(39.37) | 1.580 (40.13) | 1.250 (31.75) |
| 15 | 1.805(45.85) | 1.375(34.93) | .128(3.25) | 1.625(41.28) | 1.675 (42.55) | M22 X 1.0-6g-0.100R | 1.675(42.55) | 1.705 (43.31) | 1.375 (34.92) |
| 17 | 1.930(49.02) | 1.500(38.10) | .128(3.25) | 1.750(44.45) | 1.800 (45.72) | M25 X 1.0-6g-0.100R | 1.800(45.72) | 1.830 (46.48) | 1.500 (38.10) |
| 19 | 2.055(52.20) | 1.625(41.28) | .128(3.25) | 1.875(47.63) | 1.925 (48.90) | M28 X 1.0-6g-0.100R | 1.925(48.90) | 1.955 (49.66) | 1.625 (41.28) |
| 21 | 2.180(55.37) | 1.750(44.45) | .128(3.25) | 2.000(50.80) | 2.050 (52.07) | M31 X 1.0-6g-0.100R | 2.050(52.07) | 2.080 (52.83) | 1.750 (44.45) |
| 23 | 2.305(58.55) | 1.875(47.63) | .154(3.91) | 2.125(53.98) | 2.175 (55.25) | M34 X 1.0-6g-0.100R | 2.175(55.25) | 2.205 (56.01) | 1.875 (47.63) |
| 25 | 2.430(61.72) | 2.000(50.80) | .150(3.81) | 2.250(57.15) | 2.300 (58.42) | M37 X 1.0-6g-0.100R | 2.300(58.42) | 2.330 (59.18) | 2.000 (50.80) |

Space-grade, blind-mate connectors


MIL-DTL-38999 Series III Type Space-Grade Connectors

Plug and receptacle pair with misalignment accommodation


253-017 REAR PANEL MOUNT RECEPTACLE WITH ADJUSTABLE ZERO SEPARATION FORCE AND MISALIGNMENT ACCOMMODATION



Recommended Panel Cut Out




253-017 Misalignment Capabilities




Adjustment Ring Geometry and Material Options

Contact manufacturer for other options



Distance between mated flanges.

For reference only
(not deliverable)

NOTES:

1. 253-017 mates with 253-016 fixed series.
2. Distance between mated mounting flanges: 1.170/1.230. Consult manufacturer other distance between mounting flanges is required
3. Separation force is adjustable ± 5 lbs when mated with 253-016 and 253-017 pairs have adjustable separation force of ± 5 lbs
4. See Space-Grade guidelines material, in this section, for outgassing/screening options available
5. Spares: pin or socket contacts IAW AS39029 or per Glenair part number if controlled force contacts
6. Contact factory for PC tail versions
7. Material/finish
 - Shell (016 and 017), ring (017), retainer ring (016): see P/N development, finish
 - Wave spring(017), springs and spring retainer (016): CRES/ passivated
 - Insulators: high grade rigid dielectric/N.A.
 - Seals: fluorosilicone blend/N.A.

Space-grade, blind mate connectors

MIL-DTL-38999 Series III Type Space-Grade Connectors


Plug or receptacle bulkhead feed-thru with assisted kick-off

| Part Number Development | | | | | | | | |
|---------------------------------------|---|--|--|-----|----|-------|----|---|
| Sample Part Number | 253-018 | | | -07 | ME | 25-35 | PP | N |
| Series / Basic Part No. | 253-018 = Blind-mate feed-thru | | | | | | | |
| Connector Style | -07 = Jam-nut mount, feed-thru plug (fixed) with rear D38999 type receptacle interface -G6 = In-line plug with rear D38999 type plug interface and EMI spring | | | | | | | |
| Material/Finish | ME = Aluminum, electroless nickel ZL = CRES, electrodeposited nickel MT = Aluminum, nickel PTFE Z1 = CRES, passivated | | | | | | | |
| Shell Size-Insert Arrangement* | Per MIL-STD-1560 | | | | | | | |
| Contact Type | PP = Pin on both sides BSDP = Blind-mate side socket - D38999 side pin SS = Socket on both sides BPDS = Blind-mate side pin - D38999 side socket | | | | | | | |
| Alternate Polarization* | A = 40°, B = 65°, C = 80°, D = 210°, E = 250°, F = 280°, G = 310°, H = 330°, N = 135° (Normal) Per L°. G6 only Refers to blind mate side. Plug/Receptacle side per MIL-DTL-38999 | | | | | | | |


*Refer to C-5 to C-12 for insert arrangements.

For Space-Grade modification codes see pages C-3 thru C-4. Modification codes may be added directly to the end of any valid part number

253-018-07 BLIND-MATE FEED-THRU, JAM-NUT MOUNT PLUG WITH B-SIDE D38999 TYPE RECEPTACLE MATING INTERFACE AND ASSISTED KICK-OFF (SPRING FORCE)



| Dimensions | | | | | | | |
|------------|---------------|------------------------------------|---------------|-----------------|------------------------------|-------------------|-------------------------|
| Shell Size | F Flange | H (End of Slot) [+0/-0.008 (-.20)] | Ø J, Jam Nut | N, Jam Nut Flat | M, Flange Flats ±.010 (±.25) | T Thread Class 2A | D Thread 0.1P-0.3L-TS-2 |
| 13 | 1.515 (38.48) | .666 (16.92) | 1.375 (34.93) | 1.175 (29.85) | 1.430 (36.32) | 1.000-20 UNEF | 0.875 (22.23) |
| 15 | 1.636 (41.55) | .729 (18.52) | 1.500 (38.10) | 1.300 (33.02) | 1.500 (38.10) | 1.125-18 UNEF | 1.000 (25.40) |
| 21 | 2.065 (52.45) | .955 (24.26) | 1.875 (47.63) | 1.688 (42.88) | 1.930 (49.02) | 1.500-18 UNEF | 1.375 (34.92) |
| 23 | 2.200 (55.88) | 1.017 (25.83) | 2.063 (52.40) | 1.875 (47.63) | 2.060 (52.32) | 1.625-18 UNEF | 1.500 (38.10) |
| 25 | 2.316 (58.83) | 1.096 (27.84) | 2.141 (54.38) | 2.010 (51.05) | 2.180 (55.37) | 1.750-18 UNS | 1.625 (41.28) |




| Panel Cut-Out | | | |
|---------------|----------------------|--------------|---------------|
| Shell Size | Ø G, Thru Hole ±.004 | W (Basic) | S |
| 13 | 1.009 (25.63) | .504 (12.80) | 1.460 (37.08) |
| 15 | 1.134 (28.80) | .549 (13.94) | 1.545 (39.24) |
| 21 | 1.509 (38.33) | .709 (18.01) | 1.995 (50.67) |
| 23 | 1.634 (41.50) | .753 (19.13) | 2.120 (53.85) |
| 25 | 1.759 (44.68) | .809 (20.55) | 2.315 (58.80) |

Space-grade, blind mate connectors


MIL-DTL-38999 Series III Type Space-Grade Connectors

Plug or receptacle bulkhead feed-thrus with assisted kick-off

253-018-G6 BLIND-MATE IN-LINE PLUG WITH B-SIDE D38999 TYPE PLUG MATING INTERFACE AND ASSISTED KICK-OFF (SPRING FORCE)



| Dimensions for 253-018-G6 Plug | | | |
|--------------------------------|---------------|---------------|---------------|
| Shell Size | Ø A Max | Ø B Max. | Ø C Max |
| 13 | 1.020 (25.91) | 1.025 (26.03) | 1.175 (29.85) |
| 15 | 1.145 (29.08) | 1.155 (29.34) | 1.295 (32.89) |
| 21 | 1.520 (38.61) | 1.525 (38.73) | 1.660 (42.16) |
| 23 | 1.645 (41.78) | 1.645 (41.78) | 1.765 (44.83) |
| 25 | 1.770 (44.96) | 1.770 (44.96) | 1.890 (48.01) |



NOTES:

1. Mates with 253-019 and D38999 series III connectors with same insert arrangement and polarization
2. Distance between mated mounting flanges: 1.685/1.645. Consult manufacturer if other distance between mated mounting flanges is required
3. Misalignment capabilities are possible with mated pair reference Glenair connector 253-019.
4. See Space-Grade guidelines material, in this section, for outgassing/screening options available
5. Stainless steel locating pin ($\varnothing 0.079$) shipped with each -07 jam-nut receptacle connector
6. For feed-thru connector configurations that are either pin/pin or socket/socket, the position identification/ marking on the D38999 side of the connector will be as shown in MIL-STD-1560. The blind mate separation side will be the reverse identification marking
7. Blind mate side mates with 253-019 with reverse silkscreen marking for contact type PP (pin on both sides) or SS (socket on both sides)
8. Kick-off spring is not intended to offset all of the contact retention force for each insert arrangement
9. Material/finish
 - Shell, jam-nut coupling nut: see part number development, finish
 - Spring: CRES/passivated
 - Insulators: high grade rigid dielectric/N.A.
 - O-ring: fluorosilicone blend
 - Contacts: copper alloy/gold plated

Space-grade, blind mate connectors

MIL-DTL-38999 Series III Type Space-Grade Connectors


Jam-nut mount receptacle with misalignment capabilities and optional sealing

| Part Number Development | | | | | | | | |
|---------------------------------------|---|--|--|-----|----|-------|---|---|
| Sample Part Number | 253-019 | | | -07 | ME | 25-35 | S | N |
| Series / Basic Part No. | 253-019 = Blind-mate receptacle for use with 253-018 bulkhead feed-thru | | | | | | | |
| Connector Mounting | 07 = Jam-nut mount (float mount), receptacle 007 = Jam-nut mount (float mount), receptacle; reverse silkscreen marking | | | | | | | |
| Material/Finish | ME = Aluminum, electroless nickel ZL = CRES, electrodeposited nickel MT = Aluminum, nickel PTFE Z1 = CRES, passivated | | | | | | | |
| Shell Size-Insert Arrangement* | Per mil-std-1560; symmetrical layouts only, consult factory for complete details | | | | | | | |
| Contact Type | S = Socket, crimp removable P = Pin, crimp removable | | | | | | | |
| Alternate Polarization* | A = 40°, B = 65°, C = 80°, D = 210°, E = 250°, F = 280°, G = 310°, H = 330°, N = 135° (Normal) Per L°. G6 only Refers to blind mate side. Plug/Receptacle side per MIL-DTL-38999 | | | | | | | |

*Refer to C-5 to C-12 for insert arrangements.

For Space-Grade modification codes see pages C-3 thru C-4. Modification codes may be added directly to the end of any valid part number

253-019 FLOATING JAM-NUT MOUNT RECEPTACLE WITH MISALIGNMENT ACCOMMODATION AND OPTIONAL SEALING: MATES WITH 253-018 BULKHEAD FEED-THRU



| Dimensions for 253-019-07 Jam Nut Receptacle | | | | | | | | |
|--|---------------|--|----------------|---------------------------------|---------------------------------|----------------------|----------------------|---------------------|
| Shell Size | F Flange | H (End of Slot) 0.0/-0.008(0.0/-0.20) | Ø J Jam Nut | N, Jam Nut Flat ±.010 (±.25) | M, Flange Flats ±.010 (±.25) | T Thread Class 2A | D Thread Class 2A | Ø A ±.010 (±.25) |
| 13 | 1.640 (41.66) | 0.729 (18.52) | 1.500 (38.10) | 1.300 (33.02) | 1.390 (35.31) | 1.125-18 UNEF | .6875-24 | .970 (24.64) |
| 15 | 1.750 (44.45) | 0.791 (20.09) | 1.625 (41.28) | 1.450 (36.83) | 1.515 (38.48) | 1.250-18 UNEF | .8125-20 | 1.105 (28.07) |
| 21 | 2.180 (55.37) | 1.017 (25.83) | 2.063 (52.40) | 1.875 (47.63) | 1.955 (49.66) | 1.625-18 UNEF | 1.1875-18 | 1.475 (37.47) |
| 23 | 2.315 (58.80) | 1.076 (27.33) | 2.141 (54.38) | 2.010 (51.05) | 2.080 (52.83) | 1.750-18 UNS | 1.3125-18 | 1.595 (40.51) |
| 25 | 2.330 (59.18) | 1.100 (27.94) | 2.300 (58.42) | 2.125 (53.98) | 2.195 (55.75) | 1.875-16 UN | 1.4375-18 | 1.720 (43.69) |




Table IV 253-019-07 Panel Cut-Out




| Shell Size | Ø G, Thru-Hole ±.004 | W (Basic) |
|------------|----------------------|--------------|
| 13 | 1.134 (28.80) | .549 (13.94) |
| 15 | 1.259 (31.98) | .593 (15.06) |
| 21 | 1.634 (41.50) | .753 (19.13) |
| 23 | 1.759 (44.68) | .797 (20.24) |
| 25 | 1.884 (47.85) | .810 (20.57) |

Space-grade, blind mate connectors

MIL-DTL-38999 Series III Type Space-Grade Connectors

Jam-nut mount receptacle with misalignment capabilities and optional sealing

253-019 Misalignment Capabilities



NOTES:

1. Connector mates with Glenair 253-018 and 253-037 fixed series connectors having same insert arrangement and polarization.
2. Distance between mated mounting flanges as shown. Consult manufacturer if other distance between mated mounting flanges is required.
3. Misalignment capability as shown.
4. See Space-Grade guidelines material, in this section, for outgassing/screening options available
5. Stainless steel locating pin (.079) shipped with each connector
6. Contact factory for PC tail versions.
7. Dimensions and features are intended for customer use only.

Dimensions are reference only and not measured during final inspection at factory.

8. Connector style 007, jam nut mount with reverse silkscreen marking is used when mating to 253-018 feed-thru connector that is contact type PP (pin on both sides) or SS (socket on both sides).
9. Material/finish
 - Shell, jam-nut: see part number development, finish
 - Spring: CRES/passivated
 - Insulators: high grade rigid dielectric/N.A.
 - Seals: fluorosilicone blend, silicone
 - Contacts: copper alloy/gold plated

Space-grade, blind mate connectors

MIL-DTL-38999 Series III Type Space-Grade Connectors




Float mount flange plug, rack and panel connector, misalignment capabilities

| Part Number Development | | | | | | |
|--------------------------------|--|-----|----|-------|---|---|
| Sample Part Number | 253-031 | -07 | ME | 25-35 | P | N |
| Series / Basic Part No. | 253-031 Blind-mate plug with non-adjustable assisted separation | | | | | |
| Connector Mounting | -07 = Floating flange mount plug | | | | | |
| Material/Finish | ME = Aluminum, electroless nickel ZL = CRES, electrodeposited nickel MT = Aluminum, nickel PTFE Z1 = CRES, passivated | | | | | |
| Shell Size-Insert Arrangement* | Per MIL-STD-1560 | | | | | |
| Contact Type | P = Pin, crimp removable A = Pin insert less contacts S = Socket, crimp removable B = Socket insert less contacts | | | | | |
| Alternate Polarization* | A = 40°, B = 65°, C = 80°, D = 210°, E = 250°, F = 280°, G = 310°, H = 330°, N = 135° (Normal) Per L° BSC. Refers to blind mate side. | | | | | |

*Refer to section A for complete details. Refer to Space-Grade Guidelines material (IAW NASA EEE INST-002) for outgassing and screening modification codes, on pages 60 and 61. Modification codes may be added directly to the end of any valid part number

253-031 SEALED BLIND-MATE FLOAT MOUNT FLANGE PLUG WITH CRIMP CONTACTS AND ACCESSORY THREADS

07 - Receptacle, Jam Nut Mount



*Dimensions shown are for reference only and not intended to be verified during final inspection

NOTES:

1. Connector mates with Glenair 253-032 series connector, having the same insert arrangement and polarization.
2. Insert arrangement is in accordance with MIL-STD-1560 arrangements only. Contact manufacturer for availability.
3. See Space-Grade guidelines material, in this section, for outgassing/screening options available
4. Blue color band indicates rear release contact retention mechanism.
5. Kick-off spring is not intended to offset all of the contact

retention force for each insert arrangement

6. Misalignment capability possible when mated with 253-032

7. Material/ finish:


- Shell, jam-nut: see part number development table, finish
- Insulators: high grade rigid dielectric / N.A.
- Contacts: copper alloy/gold plated
- O-ring: fluorosilicone blend / N.A.

Space-grade, blind mate connectors

MIL-DTL-38999 Series III Type Space-Grade Connectors

Float mount flange plug, rack and panel connector, misalignment capabilities

| Dimensions | | | | | | | |
|------------|---------------|----------------|---------------|---------------|---------------|----------------|-------------------------|
| Shell Size | ØA Max | Thd B Class 2A | C Max | E ±.016(0.4) | ØF Max | G Thd Class 2A | K .011/-0.010 (.28/.25) |
| 11 | .673 (17.09) | 1.0000-20 UNEF | 1.181 (30.00) | 1.375 (34.92) | 1.511 (38.38) | .5625-24 | .109 (2.77) |
| 13 | .798 (20.27) | 1.1250-18 UNEF | 1.300 (33.02) | 1.500 (38.10) | 1.636 (41.55) | .6875-24 | .109 (2.77) |
| 15 | .923 (23.44) | 1.2500-18 UNEF | 1.457 (37.01) | 1.625 (41.28) | 1.761 (44.73) | .8125-20 | .109 (2.77) |
| 17 | 1.048 (26.62) | 1.3750-18 UNEF | 1.575 (40.00) | 1.812 (46.02) | 1.949 (49.50) | .9375-20 | .140 (3.56) |
| 19 | 1.173 (29.79) | 1.5000-18 UNEF | 1.693 (43.00) | 1.938 (49.23) | 2.073 (52.65) | 1.0625-18 | .140 (3.56) |
| 21 | 1.298 (32.97) | 1.6250-18 UNEF | 1.811 (46.00) | 2.062 (52.37) | 2.200 (55.88) | 1.1875-18 | .140 (3.56) |
| 23 | 1.423 (36.14) | 1.7500-18 UNS | 2.016 (51.21) | 2.187 (55.55) | 2.323 (59.00) | 1.3125-18 | .140 (3.56) |
| 25 | 1.548 (39.32) | 1.8750-16 UNS | 2.125 (53.97) | 2.312 (58.72) | 2.448 (62.18) | 1.4375-18 | .140 (3.56) |



| Recommended Panel Cutout | | |
|--------------------------|----------------------------|--------------------------|
| Shell Size | Ø B .010/-0.000 (0.25/.00) | W +.000/-0.010 (.00/.25) |
| 11 | 1.010 | 0.955 |
| 13 | 1.135 | 1.085 |
| 15 | 1.260 | 1.210 |
| 17 | 1.385 | 1.335 |
| 19 | 1.510 | 1.460 |
| 21 | 1.635 | 1.585 |
| 23 | 1.760 | 1.710 |
| 25 | 1.885 | 1.835 |

Space-grade, blind mate connectors

MIL-DTL-38999 Series III Type Space-Grade Connectors

Float mount flange receptacle, rack and panel connector, misalignment capable




| Part Number Development | | | | | | | |
|--------------------------------|--|-----|----|-------|---|---|----|
| Sample Part Number | 253-032 | -07 | ME | 25-35 | S | N | NS |
| Series / Basic Part No. | 253-032 = Blind-mate receptacle for use with 253-031 plug | | | | | | |
| Connector Mounting | -07 = Floating jam nut mount receptacle | | | | | | |
| Material/Finish | ME = Aluminum, electroless nickel ZL = CRES, electrodeposited nickel MT = Aluminum, nickel PTFE Z1 = CRES, passivated | | | | | | |
| Shell Size-Insert Arrangement* | Per MIL-STD-1560; Symmetrical layouts only, consult factory for complete details. | | | | | | |
| Contact Type | P = Pin, crimp removable A = Pin insert less contacts S = Socket, crimp removable B = Socket insert less contacts | | | | | | |
| Alternate Polarization* | A = 40°, B = 65°, C = 80°, D = 210°, E = 250°, F = 280°, G = 310°, H = 330°, N = 135° (Normal) Per L° BSC. Refers to blind mate side. | | | | | | |
| Non Sealing | NS = Non-Sealing (omit for external elastomer seal version) | | | | | | |

*Refer to C-5 to C-12 for insert arrangements.

For Space-Grade modification codes see pages C-3 thru C-4. Modification codes may be added directly to the end of any valid part number

253-032 FLOATING JAM-NUT MOUNT RECEPTACLE WITH MISALIGNMENT ACCOMMODATION; MATES WITH 253-031 ONLY



NOTES:

1. Connector mates with Glenair 253-031 series connector, having the same insert arrangement and polarization.
2. Insert arrangement is in accordance with MIL-STD-1560 arrangements only. Contact manufacturer for availability.
3. Misalignment capabilities are possible

- when mated with Glenair connector 253-031
4. See Space-Grade guidelines material, in this section, for outgassing/screening options available
5. Material/ finish:
 - Shell, flange, jam-nut: see part number


- development, finish
- Wave spring: CRES 17-7PH/passivate
- Insulators: high grade rigid dielectric/N.A.
- Contacts: copper alloy/gold plated
- O-ring: fluorosilicone blend/N.A.

Space-grade, blind mate connectors

MIL-DTL-38999 Series III Type Space-Grade Connectors


Float mount flange receptacle, rack and panel connector, misalignment capable

Misalignment Capabilities




Distance between mated flanges.

For reference only
(not deliverable)



| Dimensions | | | | | | | |
|------------|---------------|-----------------|---------------|-------------------|---------------|--------------------|----------------------------------|
| Shell Size | ØA Max | B Thd, Class 2A | Y Hex | E ±.016 (0.41) | Ø F Max | Thd G, Class 2A | K .011/-0.010 (0.28/ 0.25) |
| 11 | .853 (21.67) | 1.1250-18 UNEF | 1.300 (33.02) | 1.391 (35.33) | 1.641 (41.68) | .5625-24 | .109 (2.77) |
| 13 | .978 (24.84) | 1.2500-18 UNEF | 1.457 (37.01) | 1.516 (38.51) | 1.750 (44.45) | .6875-24 | .109 (2.77) |
| 15 | 1.103 (28.02) | 1.3750-18 UNEF | 1.575 (40.00) | 1.641 (41.68) | 1.938 (49.23) | .8125-20 | .109 (2.77) |
| 17 | 1.228 (31.19) | 1.5000-18 UNEF | 1.693 (43.00) | 1.828 (46.43) | 2.062 (52.37) | .9375-20 | .140 (3.56) |
| 19 | 1.353 (34.37) | 1.6250-18 UNEF | 1.811 (46.00) | 1.954 (49.63) | 2.188 (55.58) | 1.0625-18 | .140 (3.56) |
| 21 | 1.478 (37.54) | 1.7500-18 UNS | 2.010 (51.05) | 2.078 (52.78) | 2.312 (58.72) | 1.1875-18 | .140 (3.56) |
| 23 | 1.603 (40.72) | 1.8750-16 UNS | 2.209 (56.11) | 2.128 (54.05) | 2.327 (59.11) | 1.3125-18 | .140 (3.56) |
| 25 | 1.728 (43.89) | 2.0000-16 UN | 2.334 (59.28) | 2.253 (57.23) | 2.452 (62.28) | 1.4375-18 | .140 (3.56) |

| Recommended Panel Cutout | | |
|--------------------------|----------------------------------|----------------------------------|
| Shell Size | Ø B .010/-0.000 (0.25/.00) | W +.000/-0.010 (.00/-0.25) |
| 11 | 1.135 (28.83) | 1.085 (27.56) |
| 13 | 1.260 (32.00) | 1.210 (30.73) |
| 15 | 1.385 (35.18) | 1.335 (33.91) |
| 17 | 1.510 (38.35) | 1.460 (37.08) |
| 19 | 1.635 (41.53) | 1.585 (40.26) |
| 21 | 1.760 (44.70) | 1.710 (43.43) |
| 23 | 1.885 (47.88) | 1.835 (46.61) |
| 25 | 2.010 (51.05) | 1.960 (49.78) |



Space-grade, blind mate connectors

MIL-DTL-38999 Series III Type Space-Grade Connectors

Jam-nut mount feed-thru; blind-mate receptacle to D38999 type plug




| Part Number Development | | | | | | |
|--------------------------------|--|--|--|-----|----|-------|
| Sample Part Number | 253-033 | | | -07 | ME | 25-35 |
| Series / Basic Part No. | 253-033 = Floating jam-nut mount, feed-thru receptacle with rear D38999 Series III plug interface. Receptacle interface also available, contact factory | | | | | |
| Connector Style | -07 = Jam-nut mount, float mount | | | | | |
| Material/Finish | ME = Aluminum, electroless nickel ZL = CRES, electrodeposited nickel MT = Aluminum, nickel PTFE Z1 = CRES, passivated | | | | | |
| Shell Size-Insert Arrangement* | Per MIL-STD-1560; symmetrical layouts only, consult factory for complete details | | | | | |
| Contact Type | PP = Pin on both sides BSDP = Blind-mate side socket - D38999 side pin SS = Socket on both sides BPDS = Blind-mate side pin - D38999 side socket | | | | | |
| Alternate Polarization* | A = 40°, B = 65°, C = 80°, D = 210°, E = 250°, F = 280°, G = 310°, H = 330°, N = 135° (Normal) Per L°. Refers to blind mate side. Plug side per MIL-DTL-38999. See alternate polarizations table | | | | | |

*Refer to C-5 to C-12 for insert arrangements.

For Space-Grade modification codes see pages C-3 thru C-4. Modification codes may be added directly to the end of any valid part number

253-033, JAM NUT MOUNT FEED-THRU, MISALIGNMENT CAPABLE



| Dimensions for 253-033 | | | | | | | | |
|------------------------|---------|-------------------|---------------|----------------|----------------|-------------------------|---------------|---------------|
| Shell Size | Ø A Max | T Thread Class 2A | Y Hex Flats | E flange ±.016 | ØF Flange | H End of Slot +0/-0.008 | ØB Max | ØC Max |
| 13 | .978 | 1.1250-18 UNEF | 1.300 (33.02) | 1.391 (35.33) | 1.6441 (41.76) | .729 (18.52) | 1.050 (26.67) | 1.200 (30.48) |
| 15 | 1.103 | 1.2500-18 UNEF | 1.457 (37.01) | 1.516 (38.51) | 1.750 (44.45) | .791 (20.09) | 1.180 (29.97) | 1.320 (33.53) |
| 23 | 1.603 | 1.7500-18 UNEF | 2.010 (51.05) | 2.078 (52.78) | 2.312 (58.72) | 1.072 (27.23) | 1.670 (42.42) | 1.790 (45.47) |
| 25 | 1.728 | 1.8750-18 UNEF | 2.125 (53.97) | 2.200 (55.88) | 2.327 (59.11) | 1.096 (27.84) | 1.800 (45.72) | 1.920 (48.77) |

NOTES:


- Distance between mated mounting flanges: 1.808 Consult manufacturer other distance between mounting flanges is required
- See Space-Grade guidelines material, in this section, for outgassing/screening options available
- Stainless steel locating pin (Ø.079) shipped with each connector
- Misalignment capabilities are possible with mated pair reference Glenair connector 253-018

Space-grade, blind mate connectors



MIL-DTL-38999 Series III Type Space-Grade Connectors

Jam-nut mount feed-thru; blind-mate receptacle to D38999 type plug

MISALIGNMENT CAPABILITIES (see note 4)



Distance Between Mated Flanges



| Recommended Panel Cut-out | | |
|---------------------------|--------------------------------|--------------|
| Shell Size | ØG, Thru Hole ±.0004 (0.10) | W Basic |
| 13 | 1.134 (28.80) | .549 (13.94) |
| 15 | 1.259 (31.98) | .593 (15.06) |
| 23 | 1.759 (44.68) | .797 (20.24) |
| 25 | 1.884 (47.85) | .809 (20.55) |

Space-grade, connectors

MIL-DTL-38999 Series III Type Connectors

Locking circuit and test mate plug connector




| Part Number Development | | | | | |
|--------------------------------|---|-----|----|-------|-----|
| Sample Part Number | 253-025 | -G6 | ME | 23-43 | P N |
| Series / Basic Part No. | 253-025 = Locking circuit and test mate connector | | | | |
| Connector Mounting | -G6 = In-line | | | | |
| Material/Finish | ME = Aluminum, electroless nickel ZL = CRES, electrodeposited nickel MT = Aluminum, nickel PTFE Z1 = CRES, passivated | | | | |
| Shell Size-Insert Arrangement* | Per MIL-STD-1560 | | | | |
| Contact Type | P = Pin, crimp removable A = Pin insert less contacts S = Socket, crimp removable B = Socket insert less contacts | | | | |
| Alternate Polarization* | A = 40°, B = 65°, C = 80°, D = 210°, E = 250°, F = 280°, G = 310°, H = 330°, N = 135° (Normal) Per L° Basic. Refers to blind mate side. Plug side per MIL-DTL-38999. See alternate polarizations table | | | | |

*Refer to C-5 to C-12 for insert arrangements.

For Space-Grade modification codes see pages C-3 thru C-4. Modification codes may be added directly to the end of any valid part number

253-025 LOCKING CIRCUIT AND TEST MATE CONNECTOR, MATES WITH 253-016 PLUG



Space-grade, environmental connectors

MIL-DTL-38999 Series III Type SSQ Connectors

Plug and Receptacle Connectors IAW SSQ 21635

| Part Number Development | | | | | | |
|--------------------------------|--|---|-----|--------|---|---|
| Sample Part Number | 257-745 | M | -6G | -25-35 | S | N |
| Series / Basic Part No. | 257-745 = Plug and Receptacle Connectors IAW SSQ 21635 | | | | | |
| Material/Finish | MA = Aluminum, matte finish, electroless nickel ME = Aluminum, electroless nickel MT = Aluminum, nickel PTFE Z1 = CRES (per SAE-AMS-QQ-S-763), passivated | | | | | |
| Connector Mounting | 6G = Plug with EMI Spring (standard silkscreen marking) 66G = Plug with EMI spring (reverse silkscreen marking) 07 = Receptacle, jam-nut mount 007 = Receptacle, jam-nut mount (reverse silkscreen marking) D0 = Receptacle, wall mount DD0 = Receptacle, wall mount (reverse silkscreen marking) | | | | | |
| Shell Size-Insert Arrangement* | Per MIL-STD-1560 and SSQ 21635 | | | | | |
| Insert Designator | S = Socket insert, with socket contacts B = Socket gender, less socket contacts P = pin insert, with pin contacts A = pin gender, less pin contacts | | | | | |
| Alternate Polarization* | N, A, B, C, D, E | | | | | |

*Refer to section A for complete details. Refer to Space-Grade Guidelines material (IAW NASA EEE INST-002) for outgassing and screening modification codes, on pages 60 and 61. Modification codes may be added directly to the end of any valid part number

NOTES:

1. Material/ finish:
 - Shell, coupling ring, segments - see part number development, finish
 - Insulators - high grade rigid dielectric / N.A.
 - Seals: fluorosilicone/N.A.
 - Rivet: SST/passivate
 - Detent spring: sst/passivate
 - Retaining clip: copper alloy
 - Contacts: copper alloy/gold
 - Grounding spring: copper/gold
2. When ordered with "P" or "S", connector

- supplied with contacts (including spares), insertion/removal tools and sealing plugs IAW MIL-DTL-38999
- 3. For size 8 power contacts (Ref: 680-043-08, 680-044-08 for use in 25L-07 and other arrangements) use crimp tool Astro AMT23B (M22520/23-01), die assembly Astro AMT23218DA and positioner Astro AMT23223L-BX or equivalent, use insertion/extraction tool Astro ATBS5279, or equivalent
- 4. Blue color band indicates rear release retention system

| KEY & KEYWAY LOCATION | | | | |
|-----------------------|------|------|------|------|
| POS | A | B | C | D |
| N | 80° | 142° | 188° | 293° |
| A | 135° | 170° | 188° | 310° |
| B | 49° | 169° | 188° | 244° |
| C | 66° | 140° | 188° | 257° |
| D | 62° | 145° | 188° | 280° |
| E | 79° | 153° | 188° | 272° |


Space-grade, environmental connectors

MIL-DTL-38999 Series III Type SSQ Connectors

Plug and Receptacle Connectors IAW SSQ 21635



6G & 66G - PLUG



| Dimensions | | | | | | | | | | |
|------------|---|------------------|------------------|------------------|------------------|-------------------------------|-----------------------|------------------|----------------------------|-----------------------|
| SHELL SIZE | AA THREAD CLASS 2B (PLATED) TRIPLE BLUNT START | A MAX | B MIN | C MAX | D MAX | ø E +.001 -.005 | ø F +.006 0.000 | ø M MAX | V THREAD 1.0-6g, 0.100R | NO. OF EE PROJECTIONS |
| 9 | .6250-0.1P-0.3L-TS | 1.221 (31.01) | 0.310 (7.87) | 0.840 (21.34) | 0.587 (14.91) | 0.415 (10.54) | 0.727 (18.47) | 0.859 (21.82) | M12 | 12 |
| 11 | .7500-0.1P-0.3L-TS | 1.221 (31.01) | 0.310 (7.87) | 0.840 (21.34) | 0.587 (14.91) | 0.533 (13.54) | 0.832 (21.13) | 0.969 (24.61) | M15 | 16 |
| 13 | 0.875-0.1P-0.3L-TS | 1.221 (31.01) | 0.310 (7.87) | 0.840 (21.34) | 0.587 (14.91) | 0.651 (16.54) | 1.003 (25.48) | 1.141 (28.98) | M18 | 20 |
| 15 | 1.0000-0.1P-0.3L-TS | 1.221 (31.01) | 0.310 (7.87) | 0.840 (21.34) | 0.587 (14.91) | 0.809 (20.55) | 1.131 (28.73) | 1.269 (32.23) | M22 | 24 |
| 17 | 1.1875-0.1P-0.3L-TS | 1.221 (31.01) | 0.310 (7.87) | 0.840 (21.34) | 0.587 (14.91) | 0.927 (23.55) | 1.268 (32.21) | 1.391 (35.33) | M25 | 28 |
| 19 | 1.2500-0.1P-0.3L-TS | 1.221 (31.01) | 0.310 (7.87) | 0.840 (21.34) | 0.587 (14.91) | 1.045 (26.54) | 1.375 (34.92) | 1.500 (38.10) | M28 | 32 |
| 21 | 1.3750-0.1P-0.3L-TS | 1.221 (31.01) | 0.310 (7.87) | 0.840 (21.34) | 0.587 (14.91) | 1.163 (29.54) | 1.502 (38.15) | 1.625 (41.28) | M31 | 36 |
| 23 | 1.5000-0.1P-0.3L-TS | 1.221 (31.01) | 0.310 (7.87) | 0.840 (21.34) | 0.587 (14.91) | 1.281 (32.54) | 1.619 (41.12) | 1.750 (44.45) | M34 | 40 |
| 25 | 1.6250-0.1P-0.3L-TS | 2.579 (65.51) | 1.307 (33.20) | 1.126 (28.60) | 0.845 (21.46) | 1.399 (35.53) | 1.746 (44.35) | 1.750 (44.45) | M34 | 40 |
| 25L | 1.6250-0.1P-0.3L-TS | 2.579 (65.51) | 1.307 (33.20) | 1.126 (28.60) | 0.845 (21.46) | 1.397 (35.48) ±.003 (0.08) | 1.843 (46.81) | 1.875 (47.63) | M37 | 44 |
| 33* | 1.875-0.1P-0.3L-TS | 2.579 (65.51) | 1.170 (29.72) | 1.257 (31.93) | 0.955 (24.26) | 1.681 (42.70) ±.004 (0.10) | 2.162 (54.91) | 2.203 (55.96) | M45 | 56 |
| 37* | 2.1250-0.1P-0.3L-TS | 2.579 (65.51) | 1.170 (29.72) | 1.257 (31.93) | 0.955 (24.26) | 1.856 (47.14) ±.004 (0.10) | 2.352 (59.74) | 2.391 (60.73) | M50 | 64 |


* Contact factory for availability

Space-grade, environmental connectors

MIL-DTL-38999 Series III Type SSQ Connectors

Plug and Receptacle Connectors IAW SSQ 21635

DO & DD0- WALL MOUNT RECEPTACLE WITH STANDARD HOLES



| Dimensions | | | | | | | | | | | |
|------------|----------------------|--------------------------------|---------------|------------------------------|--------------------------------|------------------------|--------------------------------|-------|-----------------|--------------------------|----------------|
| SHELL SIZE | A THREAD | B SQ | C BSC | D | E | F THREAD | AA MAX | T MAX | ø K HOLES | ø GG MAX | ø H1 MAX |
| 9 | .6250-.1P-.3L-TS-2A | 0.948 (24.08) 0.928 (23.57) | 0.719 (18.26) | 0.096 (2.44) 0.085 (2.16) | 0.823 (20.90) 0.767 (19.48) | M12 X 1.0-6g 0.100R | 1.240 (31.50) 0.519 (13.18) | | | 1.262 (32.05) (15.88) | 0.625 (15.88) |
| 11 | .7500-.1P-.3L-TS-2A | 1.041 (26.44) 1.021 (25.93) | 0.812 (20.62) | 0.096 (2.44) 0.085 (2.16) | 0.823 (20.90) 0.767 (19.48) | M15 X 1.0-6g 0.100R | 1.240 (31.50) 0.519 (13.18) | | | 1.387 (35.23) (19.05) | 0.750 (19.05) |
| 13 | .8750-.1P-.3L-TS-2A | 1.135 (28.83) 1.115 (28.32) | 0.906 (23.01) | 0.096 (2.44) 0.085 (2.16) | 0.823 (20.90) 0.767 (19.48) | M18 X 1.0-6g 0.100R | 1.240 (31.50) 0.519 (13.18) | | 0.136 | 1.512 (38.40) (22.23) | 0.875 (22.23) |
| 15 | 1.0000-.1P-.3L-TS-2A | 1.229 (31.22) 1.209 (30.71) | 0.969 (24.61) | 0.096 (2.44) 0.085 (2.16) | 0.823 (20.90) 0.767 (19.48) | M22 X 1.0-6g 0.100R | 1.240 (31.50) 0.519 (13.18) | | 0.136 (3.45) | 1.637 (41.58) (25.40) | 1.000 (25.40) |
| 17 | 1.1875-.1P-.3L-TS-2A | 1.322 (33.58) 1.302 (33.07) | 1.062 (26.97) | 0.096 (2.44) 0.085 (2.16) | 0.823 (20.90) 0.767 (19.48) | M25 X 1.0-6g 0.100R | 1.240 (31.50) 0.519 (13.18) | | 0.136 (3.12) | 1.762 (44.75) (30.16) | 1.1875 (30.16) |
| 19 | 1.2500-.1P-.3L-TS-2A | 1.448 (36.78) 1.428 (36.27) | 1.156 (29.36) | 0.096 (2.44) 0.085 (2.16) | 0.823 (20.90) 0.767 (19.48) | M28 X 1.0-6g 0.100R | 1.240 (31.50) 0.519 (13.18) | | | 1.887 (47.93) (31.75) | 1.250 (31.75) |
| 21 | 1.3750-.1P-.3L-TS-2A | 1.572 (39.93) 1.552 (39.42) | 1.250 (31.75) | 0.126 (3.20) 0.115 (2.92) | 0.791 (20.09) 0.736 (18.69) | M31 X 1.0-6g 0.100R | 1.240 (31.50) 0.519 (13.18) | | | 2.012 (51.10) (34.92) | 1.375 (34.92) |
| 23 | 1.5000-.1P-.3L-TS-2A | 1.698 (43.13) 1.678 (42.62) | 1.375 (34.92) | 0.126 (3.20) 0.115 (2.92) | 0.791 (20.09) 0.736 (18.69) | M34 X 1.0-6g 0.100R | 1.240 (31.50) 0.519 (13.18) | | 0.162 | 2.200 (55.88) (38.10) | 1.500 (38.10) |
| 25 | 1.6250-.1P-.3L-TS-2A | 1.822 (46.28) 1.802 (45.77) | 1.500 (38.10) | 0.126 (3.20) 0.115 (2.92) | 0.791 (20.09) 0.736 (18.69) | M37 X 1.0-6g 0.100R | 1.240 (31.50) 0.519 (13.18) | | 0.162 (4.11) | 2.387 (60.63) (41.28) | 1.625 (41.28) |
| 25L | 1.6250-.1P-.3L-TS-2A | 1.818 (46.18) 1.807 (45.90) | 1.500 (38.10) | 0.203 (5.16) 0.183 (4.65) | 1.161 (29.49) 1.151 (29.24) | M37 X 1.0-6g 0.100R | 2.600 (66.04) 0.879 (22.33) | | 0.162 (3.78) | 2.453 (62.31) (41.28) | 1.625 (41.28) |
| 33* | 1.875-.1P-.3L-TS-2A | 2.318 (58.88) 2.307 (58.60) | 1.750 (44.45) | 0.203 (5.16) 0.183 (4.65) | 1.161 (29.49) 1.151 (29.24) | M45 X 1.0-6g 0.100R | 2.600 (66.04) 0.879 (22.33) | | 0.217 (5.51) | 3.043 (77.29) (47.63) | 1.875 (47.63) |
| 37* | 2.125-.1P-.3L-TS-2A | 2.490 (63.25) 2.479 (62.97) | 1.922 (48.82) | 0.203 (5.16) 0.183 (4.65) | 1.161 (29.49) 1.151 (29.24) | M50 X 1.0-6g 0.100R | 2.600 (66.04) 0.879 (22.33) | | 0.204 (5.18) | 3.293 (83.64) (53.97) | 2.125 (53.97) |

* Contact factory for availability


Space-grade, environmental connectors

MIL-DTL-38999 Series III Type SSQ Connectors

Plug and Receptacle Connectors IAW SSQ 21635



DO & DDO- WALL MOUNT RECEPTACLE WITH STANDARD HOLES




| DO and DDO PANEL CUT-OUT DIMENSIONS | | | | |
|-------------------------------------|---------------|---------------|------------------------------|---------------|
| SHELL SIZE | Ø M MIN | Ø N MIN | P HOLES | R BSC |
| 9 | 0.656 (16.66) | 0.516 (13.11) | | 0.719 (18.26) |
| 11 | 0.796 (20.22) | 0.625 (15.88) | | 0.812 (20.62) |
| 13 | 0.922 (23.42) | 0.750 (19.05) | | 0.906 (23.01) |
| 15 | 1.047 (26.59) | 0.906 (23.01) | 0.133 (3.38) | 0.969 (24.61) |
| 17 | 1.219 (30.96) | 1.016 (25.81) | 0.123 (3.12) | 1.062 (26.97) |
| 19 | 1.297 (32.94) | 1.141 (28.98) | | 1.156 (29.36) |
| 21 | 1.422 (36.12) | 1.266 (32.16) | | 1.250 (31.75) |
| 23 | 1.547 (39.29) | 1.375 (34.92) | 0.159 (4.04) 0.149 (3.78) | 1.375 (34.92) |
| 25 | 1.672 (42.47) | 1.484 (37.69) | 0.155 (3.94) | 1.500 (38.10) |
| 25L | 1.672 (42.47) | 1.484 (37.69) | 0.145 (3.68) | 1.500 (38.10) |
| 33 | 1.922 (48.82) | 1.798 (45.67) | 0.210 (5.33) | 1.750 (44.45) |
| 37 | 2.172 (55.17) | 1.996 (50.70) | 0.200 (5.08) | 1.922 (48.82) |

Space-grade, environmental connectors

MIL-DTL-38999 Series III Type SSQ Connectors

Plug and Receptacle Connectors IAW SSQ 21635

07 & 007 - JAM NUT MOUNT RECEPTACLE



| Dimensions | | | | | | | | | | | | |
|------------|------------------|---------------------|------------------|--------------------------------|--------------------------------|------------------------|------------------------|-----------------|--------------------------------|--------------------------------|--------------------------------|--|
| SHELL SIZE | A MAX | S THREAD | GG MAX | U | W FLAT | BB THREAD | Y THREAD | B | C MAX | ø AA | BB | |
| 9 | 1.609 (40.87) | .6250-.1P-3L-TS-2A | 1.200 (30.48) | 1.077 (27.36) 1.047 (26.59) | 0.655 (16.64) 0.645 (16.38) | M17 X 1.0-6g 0.100R | M12 X 1.0-6g 0.100R | 0.114 (2.90) | 1.236 (31.39) | 0.703 (17.86) 0.693 (17.60) | 0.661 (16.79) 0.654 (16.61) | |
| 11 | | .7500-.1P-3L-TS-2A | 1.387 (35.23) | 1.265 (32.13) 1.235 (31.37) | 0.755 (19.18) 0.745 (18.92) | M20 X 1.0-6g 0.100R | M15 X 1.0-6g 0.100R | | | 0.835 (21.21) 0.825 (20.96) | 0.771 (19.58) 0.761 (19.33) | |
| 13 | | .8750-.1P-3L-TS-2A | 1.512 (38.40) | 1.390 (35.31) 1.360 (34.54) | 0.942 (23.93) 0.932 (23.67) | M25 X 1.0-6g 0.100R | M18 X 1.0-6g 0.100R | | | 1.020 (25.91) 1.010 (25.65) | 0.955 (24.26) 0.945 (24.00) | |
| 15 | | 1.0000-.1P-3L-TS-2A | 1.637 (41.58) | 1.515 (38.48) 1.485 (37.72) | 1.066 (27.08) 1.056 (26.82) | M28 X 1.0-6g 0.100R | M22 X 1.0-6g 0.100R | | | 1.145 (29.08) 1.135 (28.83) | 1.085 (27.56) 1.075 (27.30) | |
| 17 | | 1.1875-.1P-3L-TS-2A | 1.762 (44.75) | 1.640 (41.66) 1.610 (40.89) | 1.191 (30.25) 1.181 (30.00) | M32 X 1.0-6g 0.100R | M25 X 1.0-6g 0.100R | | | 1.270 (32.26) 1.260 (32.00) | 1.210 (30.73) 1.200 (30.48) | |
| 19 | | 1.2500-.1P-3L-TS-2A | 1.950 (49.53) | 1.827 (46.41) 1.797 (45.64) | 1.316 (33.43) 1.306 (33.17) | M35 X 1.0-6g 0.100R | M28 X 1.0-6g 0.100R | 0.145 (3.68) | 1.395 (35.43) 1.385 (35.18) | 1.335 (33.91) 1.325 (33.65) | | |
| 21 | | 1.3750-.1P-3L-TS-2A | 2.074 (52.68) | 1.953 (49.61) 1.923 (48.84) | 1.441 (36.60) 1.431 (36.35) | M38 X 1.0-6g 0.100R | M31 X 1.0-6g 0.100R | | | 1.520 (38.61) 1.510 (38.35) | 1.460 (37.08) 1.450 (36.83) | |
| 23 | | 1.5000-.1P-3L-TS-2A | 2.200 (55.88) | 2.077 (52.76) 2.047 (51.99) | 1.566 (39.78) 1.556 (39.52) | M41 X 1.0-6g 0.100R | M34 X 1.0-6g 0.100R | | | 1.645 (41.78) 1.635 (41.53) | 1.585 (40.26) 1.575 (40.00) | |
| 25 | | 1.6250-.1P-3L-TS-2A | 2.324 (59.03) | 2.203 (55.96) 2.173 (55.19) | 1.691 (42.95) 1.681 (42.70) | M44 X 1.0-6g 0.100R | M37 X 1.0-6g 0.100R | 0.114 (2.90) | 1.770 (44.96) 1.760 (44.70) | 1.710 (43.43) 1.700 (43.18) | | |
| 25L | | 1.6250-.1P-3L-TS-2A | 2.324 (59.03) | 2.203 (55.96) 2.173 (55.19) | 1.691 (42.95) 1.681 (42.70) | M44 X 1.0-6g 0.100R | M37 X 1.0-6g 0.100R | | | 1.770 (44.96) 1.760 (44.70) | | |
| 33* | | 1.8750-.1P-3L-TS-2A | 2.606 (66.19) | 2.484 (63.09) 2.454 (62.33) | 1.927 (48.95) 1.917 (48.69) | M50 X 1.0-6g 0.100R | M45 X 1.0-6g 0.100R | 0.198 (5.03) | 1.536 (39.01) | 2.006 (50.95) 1.996 (50.70) | | |
| 37* | | 2.1250-.1P-3L-TS-2A | 3.012 (76.50) | 2.843 (72.21) 2.813 (71.45) | 2.276 (57.81) 2.266 (57.56) | M60 X 1.0-6g 0.100R | M50 X 1.0-6g 0.100R | | | 2.400 (60.96) 2.390 (60.71) | | |
| | | | | | | | | | | 2.295 (58.29) 2.285 (58.04) | | |

* Contact factory for availability

Space-grade, hermetic connector

MIL-DTL-38999 Series III Type Connector

Hermetic Bulkhead Feedthru IAW SSQ 21635



| Part Number Development | | | | | | |
|-------------------------|---|--|-----|-----|----|---|
| Sample Part Number | 947-410 | Z16 | 25Q | -08 | PP | N |
| Series / Basic Part No. | 947-410 = Hermetic bulkhead feedthru | | | | | |
| Material/Finish | Z1 = CRES (per SAE-AMS-QQ-S-763), passivated ZL = Nickel plated | Z16 = Nickel plated, space-grade | | | | |
| Shell Size | Add suffix for data-type contacts omit for standard contacts C = CO-AX Q = Quadrax T = Twin-Ax | | | | | |
| Insert Arrangement* | Per MIL-STD-1560 and SSQ 21635 | | | | | |
| Contact Type | P = Pin, jam-nut side S = Socket, jam-nut side | PP = Pin-Pin; See note 5 and 6 SS = Socket-Socket; See note 5 and 6 | | | | |
| Broach Position | Specify N for normal; alternate A, B, C, D, or E | | | | | |

NOTES:


1. Material/ finish:
 - Shell - CRES / finish as specified
 - Jam-nut - aluminum alloy / electroless nickel plate (space grade)
 - Locking pellets - vespel / N.A.
 - Contacts - copper alloy / gold plate (sockets)
 - Nickel alloy / gold plate (pins)
 - Insulator, hermetic - full glass / N.A.
 - Insulator, sockets - high-grade dielectric / N.A.
 - Seals and o-rings - fluorosilicone / N.A.
2. Parts to be 100% tested per Glenair document ATP285. After testing, part to be thermal vacuum outgassed:
 - Pressure: 10^{-6} Torr
 - Temperature: $125^{\circ}\text{C} \pm 1^{\circ}\text{C}$
 - Time at Temperature: 48 hour
3. Hermeticity:
 - Connector: $<5 \times 10^{-9}$ sccHe/sec@ 1 atmosphere delta pressure
 - Sealing surfaces: 1×10^{-6} sccHe/sec @ 1 atmosphere delta pressure (O-rings and flange)
4. Electrical testing:
 - I.R.: 5000 megaOhms @ 500VDC
 - D.W.V: Per MIL-STD-1560/SSQ 21635
5. Pin-pin and socket-socket available only in symmetrical patterns. Consult factory, MIL-STD-1560 or SSQ21635 for available arrangements
6. For pin-pin or socket-socket, contact identification on jam-nut side will be as per MIL-STD-1560 or SSQ21635 and reversed on opposite end

Space-grade, hermetic connector

MIL-DTL-38999 Series III Type Connector

Hermetic Bulkhead Feedthru IAW SSQ 21635

07 - JAM NUT MOUNT RECEPTACLE



| Dimensions | | | | | | | | | | | | | | |
|------------|--------------------------|------------------------------|------------------------------|--------------------------|---------------|---------------|-----------------|-------------|-----------------|----------------|------------------|------------------|---------------|---------------|
| SHELL SIZE | AA THREAD 0.1P-0.3L-TS-2 | A MAX | B | BB THREAD 1.0-6g, 0.100R | C MAX | D +.007 0.000 | ø E +.007 0.000 | ø F | ø H +.001 -.005 | H2 MAX | ø R1 +.011 0.000 | ø R2 +.011 0.000 | S | ø T |
| 11 | 0.7500 | 2.078 (52.78) | 0.114 (2.90) 0.083 (2.11) | M 20 | 1.236 (31.39) | 0.760 (19.30) | 0.816 (20.73) | .694/.682 | 0.697 (17.70) | 0.750 (19.05) | 0.989 (25.12) | 1.239 (31.47) | 1.438 (36.53) | 1.625 (41.28) |
| 13 | 0.8750 | | | M 25 | | 0.947 (24.05) | 1.002 (25.45) | .819/.807 | 0.822 (20.88) | 0.875 (22.23) | 1.114 (28.30) | 1.364 (34.65) | 1.590 (40.39) | 1.752 (44.50) |
| 15 | 1.0000 | | | M 28 | | 1.071 (27.20) | 1.128 (28.65) | .944/.932 | 0.947 (24.05) | 1.000 (25.40) | 1.239 (31.47) | 1.489 (37.82) | 1.727 (43.87) | 1.937 (49.20) |
| 17 | 1.1875 | | | M 32 | | 1.196 (30.38) | 1.261 (32.03) | 1.115/1.101 | 1.124 (28.55) | 1.1875 (30.16) | 1.364 (34.65) | 1.614 (41.00) | 1.850 (46.99) | 2.063 (52.40) |
| 19 | 1.2500 | 0.145 (3.68) 0.114 (2.90) | M 35 M 38 M 41 M 44 | M 35 | 1.243 (31.57) | 1.321 (33.55) | 1.382 (35.10) | 1.178/1.164 | 1.185 (30.10) | 1.250 (31.75) | 1.489 (37.82) | 1.739 (44.17) | 1.970 (50.04) | 2.189 (55.60) |
| 21 | 1.3750 | | | M 38 | | 1.446 (36.73) | 1.500 (38.10) | 1.303/1.289 | 1.310 (33.27) | 1.375 (34.92) | 1.614 (41.00) | 1.864 (47.35) | 2.125 (53.97) | 2.311 (58.70) |
| 23 | 1.5000 | | | M 41 | | 1.571 (39.90) | 1.627 (41.33) | 1.428/1.414 | 1.435 (36.45) | 1.500 (38.10) | 1.739 (44.17) | 1.989 (50.52) | 2.315 (58.80) | 2.500 (63.50) |
| 25 | 1.6250 | | | M 44 | | 1.696 (43.08) | 1.753 (44.53) | 1.553/1.539 | 1.560 (39.62) | 1.625 (41.28) | 1.864 (47.35) | 2.114 (53.70) | 2.450 (62.23) | 2.625 (66.68) |
| 25L | 1.6250 | 2.969 (75.41) | 0.198 (5.03) 0.183 (4.65) | M 44 | 1.536 (39.01) | 1.696 (43.08) | 1.753 (44.53) | 1.553/1.539 | 1.560 (39.62) | 1.625 (41.28) | 1.864 (47.35) | 2.114 (53.70) | 2.450 (62.23) | 2.625 (66.68) |



JAM-FREE LAUNCHING

AS81703 Series 3 Type Lanyard Connectors



In addition to high shock / high vibration environments including military space and defense applications such as missile and space payload deployment, the AS81703 provides jam-free, push-on, pull-off operation. Glenair's AS81703 Series 3 type connector series is intermateable and intermountable with currently available AS81703 mil-spec and commercial connectors, and offers several enhancements to the standard design:

an integrated band porch for shield termination, 360° saw teeth for rear-end accessory clocking, and a red full-mate indicator stripe. The AS81703 Series 3 type connector is ideally suited for droppable stores, umbilical connect, air launch to orbit, and other extreme vibration and shock environments where rugged and reliable lanyard-release and push-pull mating is a must.

Nineteen contact arrangements are available, including hybrid signal/power layouts, and a full complement of backshells and connector accessories is offered—with Glenair's high availability and quick delivery.




- Intermateable and intermountable with available AS81703 connectors
- Signal, power, and high-speed shielded contact arrangements
- Reliable fail-safe axial-pull lanyard equipped coupling
- Instant disconnect for critical quick-release systems
- Available integrated band porch for easy shield termination
- 360° saw teeth for accessory clocking
- Red full-mate indicator stripe
- Blind mate and rack-and-panel versions available
- Available backshells and accessories IAW AS81703
- Polarization keying for mis-mate prevention

LANYARD-RELEASE
AS81703 Series 3 Type Connectors
Table of contents / selection guide




**Connector specifications, How-to-order,
General information and Test report summary**

pages D-2-3




Contact arrangements

pages D-4-5




**253-020-06
Straight plug**

page D-6




**253-020-08
Lanyard-release plug**

page D-7




**253-020-09
Rack-and-panel plug**

page D-8




**253-020-00
Wall-mount receptacle**

page D-9



**253-020-07
Jam-nut receptacle**

page D-10



Backshells and accessories

page D-11


D

SERIES 253-020
AS81703 Series 3 Type Connectors
How to order



| How To Order | | | | | | | |
|---|--|--|--|--|----------|-----------|-----------|
| Sample Part Number | 253-020 | | | | - | 06 | ME |
| Basic Part Number | AS81703 Series 3 type connector | | | | | | |
| Rear Option | - = Accessory threads B = Band porch (consult factory) | | | | | | |
| Connector Style (and AS cross-ref) | 00 = Sq. flange mount receptacle AS34241 type (MS3424) 06 = Straight plug AS34671 type (MS3467) 07 = Jam nut mount receptacle AS34641 type (MS3464) 08 = Lanyard release plug MS3468 type (no SAE equivalent) 09 = Rack & panel plug AS34461 type (MS3446) | | | | | | |
| Material / Finish | See Table I | | | | | | |
| Shell Size / Insert Arrangement | See Table II, diagrams on pgs. 4-5 | | | | | | |
| Contact Styles | P = Pin insert A = Pin insert less contacts (not available for -09 Plug) S = Socket insert B = Socket insert less contacts (not available for -09 Plug) | | | | | | |
| Insert Clocking Positions | N, W, X, Y, B, C (See Table III) | | | | | | |
| Lanyard Ring Mod. Code (-08 Receptacle Only) | Omit = Standard Lanyard Ring 812 = Lanyard Ring Rotated 90° from Master Keyway | | | | | | |

| Table I - Material and Finish | | | |
|-------------------------------|-----------|----------------|--------------------------------------|
| Code | Mil Class | Material | Finish |
| C | - | Aluminum Alloy | Black Anodize |
| ME | E | | Electroless Nickel |
| NF | L | | O.D. Cadmium over Electroless Nickel |
| MT | - | | Nickel-PTFE |
| ZR | - | | Zinc-Nickel/Black (Tri-Valent CR) |



| Table II: Contact Arrangements | | | |
|--------------------------------|-------------------------|-----|-----|
| Contact Arrangement | Contact Size & Quantity | | |
| | #20 | #16 | #12 |
| 3-50 | 3 | | |
| 7-50 | 7 | | |
| 12-6 | 6 | | |
| 12-50 | 12 | | |
| 19-4 | | | 12 |
| 19-7 | | | 7 |
| 19-12 | | 12 | |
| 19-50 | 19 | | |
| 27-2 | | 14 | |
| 27-3 | 14 | 2 | |
| 27-5 | | 19 | |
| 27-8 | | 6 | 4 |
| 27-11 | 12 | | |
| 27-50 | 27 | | |
| 37-2 | | 24 | |
| 37-3 | | | 12 |
| 37-50 | 37 | | |
| 61-42 | 29 | 4 | 8 |
| 61-50 | 61 | | |

| Contact Arrangement | Alternate Insert Clocking Positions | | | | | |
|---------------------|-------------------------------------|-----|---------|----------|---------|------|
| | N | W | X | Y | B | C |
| 3-50 | 0° | | | | 75° | |
| 7-50 | 0° | | | | | 150° |
| 12-6 | 0° | 25° | 45° | 80° | 150° | 220° |
| 12-50 | 0° | 15° | 50° | 75° | 150° | 225° |
| 19-4 | 0° | | | | 22° 30' | 135° |
| 19-7 | 0° | | | | 75° | 150° |
| 19-12 | 0° | 25° | 50° | 75° | 150° | 225° |
| 19-50 | 0° | | | | 75° | 150° |
| 27-2 | 0° | 25° | 50° | 75° | 150° | 225° |
| 27-3 | 0° | 25° | 50° | 75° | 150° | 225° |
| 27-5 | 0° | | | | 75° | 150° |
| 27-8 | 0° | 25° | 50° | 75° | 150° | 225° |
| 27-11 | 0° | 25° | 50° | 75° | 150° | 225° |
| 27-50 | 0° | 25° | 50° | 75° | 150° | 225° |
| 37-2 | 0° | 25° | 145° | 227° 30' | | |
| 37-3 | 0° | 20° | 70° | | | |
| 37-50 | 0° | 25° | 50° | 75° | 150° | 225° |
| 61-42 | 0° | | 67° 30' | | | |
| 61-50 | 0° | | | 75° | 150° | 225° |

SERIES 253-020
AS81703 Series 3 Type Connectors
General information / test report summary



| Validation Test Summary, Tested IAW AS81703 | | | | | | | | | |
|--|---|---------------------------|--------------------------------|------------------------------|------------------------------|-----------------------------------|--|--|--|
| Test | Requirement | | | | | Result | | | |
| Magnetic Permeability | Relative Magnetic Permeability: $\leq 2.0 \text{ Mu}$ | | | | | Pass | | | |
| Maintenance Aging and Contact Forces | Insertion Force: $\leq 15 \text{ lbs.}$ Removal Force: $\leq 10 \text{ lbs.}$ | | | | | Pass | | | |
| Gage Location and Retention | Axial Displacement of the Test Gages: ≤ 0.012 | | | | | Pass | | | |
| Operating Forces | Shell Size | Max Engagement force (lb) | Measured Engagement force (lb) | Min Disengagement force (lb) | Max Disengagement force (lb) | Measured Disengagement force (lb) | | | |
| | 12 | 34 | 15.2 | 2 | 34 | 3.80 | | | |
| | | | 16.8 | | | 4.05 | | | |
| | 19 | 38 | 16.2 | 3 | 38 | 6.75 | | | |
| | | | 15.8 | | | 8.06 | | | |
| | 37 | 44 | 19.7 | 6 | 44 | 7.56 | | | |
| | | | 20.1 | | | 7.72 | | | |
| Insulation Resistance, Room Temperature | Insulation resistance shall be $>10,000 \text{ megohms}$ | | | | | Pass | | | |
| Dielectric Withstanding Voltage | No evidence of breakdown or flashover. Leakage Current $\leq 5 \text{ mA}$ | | | | | Pass | | | |
| | Condition | | Service Rating I | Service Rating II | | | | | |
| | Sea Level | 600 V AC | 1000 V AC | 70,000 ft. | 300 V AC | 450 V AC | | | |
| Thermal Shock | Low Temperature: $-55^{\circ} \pm 3^{\circ}\text{C}$ • High Temperature: Class L $175^{\circ} \pm 3^{\circ}\text{C}$; Class E, $200^{\circ} \pm 3^{\circ}\text{C}$. 5 cycles, 2 hour minimum soak. No damage detrimental to the connector | | | | | Pass | | | |
| Insert Retention | Inserts shall not be dislocated from the specified insert position as shown on the applicable MS drawing when an effective pressure differential of 75 lbs.f/in^2 is applied | | | | | Pass | | | |
| Vibration | 10 to 2,000 Hz and return to 10 Hz in 20 minutes. 12 cycles in 4 hours for X,Y, and Z Axes. Total 12 hrs. Amplitude of 0.06" double amplitude or 20g, whichever is less. Support wires 8" both ends. Electrical load 100 mA max, open circuit $<5\text{V}$. Maximum initial R not to exceed 3 Ohms on individual loops. All samples measured no discontinuity on any axis. | | | | | Pass | | | |
| Shock | 15g peak value, half-sine pulse, 11ms duration. One shock each direction on 3 major axes. Mated connectors shall not be damaged and there shall be no loosening of parts. All samples measured no discontinuity on any axis. | | | | | Pass | | | |
| Insulation Resistance, Elevated Temperature | After an exposure for 1000 hours at 200°C , the insulation resistance shall be greater than 500 megohms, unmated condition | | | | | Pass | | | |
| Moisture Resistance | 10 cycles, low temperature subcycle 5 cycles. Initial and final mated insulation resistance measured $>100\text{Mohms}$ for all samples at $25^{\circ}, 500\text{V}, 12\text{s}$. | | | | | Pass | | | |
| Insulation Resistance | Unmated, 500V, 120x, 10,000 megohms | | | | | Pass | | | |
| Contact Resistance | #24 AWG wires crimped to size 20 contacts. Test current 3A, maximum mV drop 45 mV | | | | | Pass | | | |
| Contact Retention | Axial load: 15 lb. Duration: 5 sec min. Rate: approx. 1lb/sec. Initial load of 2 lb before measuring contact displacement. Force applied in the direction tending to dislodge the contacts toward the rear of the connector. Displacement shall not exceed 0.012" | | | | | Pass | | | |
| Magnetic Permeability | Relative magnetic permeability of connector assemblies $< 2.0 \text{ Mu}$ | | | | | Pass | | | |
| Durability | 500 mating cycles with no mechanical or electrical defects detrimental to operation | | | | | Pass | | | |
| Salt Spray | Unmated, 48 hours, 20% salt concentration. No exposure of basic metal due to corrosion which will affect performance. | | | | | Pass | | | |
| Fluid Immersion, Lubricating Oil | Unmated connectors immersed in MIL-PRF-7808 oil, 20 hours. | | | | | Pass | | | |
| Contact Glenair for complete validation test reports: GT-15-93 (AS81703, series 3, class E) and GT-15-94 (AS81703, series 3, class L). | | | | | | | | | |


MATERIALS/FINISHES

Shells, Jam Nuts, Lockwashers - Aluminum alloy

Insulators - High-grade rigid dielectric


O-Rings, Grommets, Peripheral Seals - Fluorosilicone or equivalent

SERIES 253-020
AS81703 Series 3 Type Connectors
Contact arrangements (pin face shown)




3-50

3X SIZE 20 CONTACT




7-50

7X SIZE 20 CONTACT




12-6

6X SIZE 20 CONTACT




12-50

12X SIZE 20 CONTACT




19-4

4X SIZE 12 CONTACT




19-7

7X SIZE 12 CONTACT




19-12

12 SIZE 16 CONTACT




19-50

19X SIZE 20 CONTACT




27-2

14X SIZE 16 CONTACT




27-3

2X SIZE 16 CONTACT
14X SIZE 20 CONTACT




27-5

19X SIZE 16 CONTACT




27-8

6X SIZE 16 CONTACT
4X SIZE 12 CONTACT



27-11

12X SIZE 20 CONTACT



27-50


27X SIZE 20 CONTACT

D

SERIES 253-020


AS81703 Series 3 Type Connectors

Contact arrangements (pin face shown)




37-2

24X SIZE 16 CONTACT




37-3

12X SIZE 12 CONTACT




37-50

37X SIZE 20 CONTACT



61-42

4X SIZE 16 CONTACT
29X SIZE 20 CONTACT
8X SIZE 12 CONTACTS




61-50

61X SIZE 20 CONTACT


D

AS81703 SERIES 3 TYPE CONNECTORS
Plug
253-020-06



| -06 Plug Dimensions | | | | | | | | | |
|---------------------|-----------|---------|----------|------|----------|------|------------------------------|------------|---------|
| Shell Size | Ø A | | Ø C Max. | | Ø E Max. | | F Thd. | H | |
| | In. ± .02 | mm ± .5 | In. | mm | In. | mm | | In. ± .025 | mm ± .6 |
| 3 | .657 | 16.7 | .351 | 8.9 | .509 | 12.9 | % ₁₆ -24 UNEF-2A | .925 | 23.5 |
| 7 | .795 | 20.2 | .531 | 13.5 | .687 | 17.4 | % ₄ -20 UNEF-2A | 1.062 | 27.0 |
| 12 | .945 | 24.0 | .665 | 16.9 | .812 | 20.6 | % ₈ -20 UNEF-2A | 1.172 | 29.8 |
| 19 | 1.090 | 27.7 | .790 | 20.1 | .937 | 23.8 | 1-20 UNEF-2A | 1.328 | 33.7 |
| 27 | 1.230 | 31.2 | .869 | 22.1 | .992 | 25.2 | 1% ₁₆ -18 UNEF-2A | 1.475 | 37.5 |
| 37 | 1.350 | 34.3 | .994 | 25.2 | 1.117 | 28.4 | 1% ₃₆ -18 UNEF-2A | 1.610 | 40.9 |
| 61 | 1.620 | 41.1 | 1.280 | 32.5 | 1.427 | 36.2 | 1½-18 UNEF-2A | 1.890 | 48.0 |

AS81703 SERIES 3 TYPE CONNECTORS
Lanyard-release plug
253-020-08




-08 Lanyard-Release Plug Dimensions

| Shell Size | Ø A | | Ø C Max. | | Ø E Max. | | F Thd. | G Max. | | H Max. | |
|------------|----------------|--------------|----------|------|----------|------|-------------------|--------|------|--------|------|
| | In. | mm | In. | mm | In. | mm | | In. | mm | In. | mm |
| 3 | .657 .648 | 16.7 16.5 | .351 | 8.9 | .509 | 12.9 | %16-24 UNEF-2A | 1.261 | 32.0 | .925 | 23.5 |
| 7 | .793 .782 | 20.1 19.9 | .531 | 13.5 | .687 | 17.4 | ¾-20 UNEF-2A | 1.411 | 35.8 | 1.062 | 27.0 |
| 12 | .942 .932 | 23.9 23.7 | .665 | 16.9 | .812 | 20.6 | ⁷/₈-20 UNEF-2A | 1.531 | 38.9 | 1.172 | 29.8 |
| 19 | 1.073 1.063 | 27.3 27.0 | .790 | 20.1 | .937 | 23.8 | 1-20 UNEF-2A | 1.681 | 42.7 | 1.328 | 33.7 |
| 27 | 1.226 1.216 | 31.1 30.9 | .869 | 22.1 | .992 | 25.2 | 1½-18 UNEF-2A | 1.826 | 46.4 | 1.475 | 37.5 |
| 37 | 1.348 1.338 | 34.2 34.0 | .994 | 25.2 | 1.117 | 28.4 | 1 ³/₁₆-18 UNEF-2A | 1.915 | 48.6 | 1.610 | 40.9 |
| 61 | 1.614 1.604 | 41.0 40.7 | 1.280 | 32.5 | 1.427 | 36.2 | 1 ½-18 UNEF-2A | 2.235 | 56.8 | 1.890 | 48.0 |

AS81703 SERIES 3 TYPE CONNECTORS
Rack-and-panel plug
253-020-09



| How To Order | | | | | | | |
|---------------------------------|--|--|--|--|---|----|----|
| Sample Part Number | 253-020 | | | | - | 09 | ME |
| Basic Part Number | AS81703 Series 3 type connector | | | | | | |
| Rear Option | - = Accessory threads B = Band porch (consult factory) | | | | | | |
| Connector Style | 09 = Rack & panel plug AS34461 type (MS3446) | | | | | | |
| Material / Finish | C = Al Alloy/Black Anodize ME = Al Alloy/Electroless Nickel MT = Al Alloy/Nickel-PTFE NF = Al Alloy/Cad O.D. Over Electroless Nickel ZR = Al Alloy/Zinc-Nickel Black | | | | | | |
| Shell Size / Insert Arrangement | See Table II pg. 2, diagrams on pgs. 4-5 | | | | | | |
| Contact Styles | P = Pin insert S = Socket insert A = Pin insert less contacts B = Socket insert less contacts | | | | | | |
| Insert Clocking Positions | N, W, X, Y, B, C (See Table III pg. 2) | | | | | | |




| Shell Size | -09 Rack-and-Panel Plug Dimensions | | | | | | | | | | J Thd. | Spring force when mated (lbs-in.) |
|------------|------------------------------------|--------------|----------|------|----------|------|----------|------|----------|------|-------------------|-----------------------------------|
| | Ø A | | Ø B Max. | | Ø D Max. | | Ø F Max. | | Ø G Max. | | | |
| In. | mm | In. | mm | In. | mm | In. | mm | In. | mm | | | |
| 3 | .891 .869 | 22.6 22.1 | .800 | 20.3 | .351 | 8.9 | .509 | 12.9 | 1.225 | 31.1 | 1/16-24 UNEF-2A | 16 – 20 |
| 7 | 1.172 1.150 | 29.8 29.2 | .990 | 25.1 | .531 | 13.5 | .687 | 17.4 | 1.356 | 34.4 | 3/16-20 UNEF-2A | 16 – 20 |
| 12 | 1.263 1.241 | 32.1 31.5 | 1.190 | 30.2 | .665 | 16.9 | .812 | 20.6 | 1.575 | 40.0 | 5/16-20 UNEF-2A | 30 – 35 |
| 19 | 1.391 1.369 | 35.3 34.8 | 1.320 | 33.5 | .790 | 20.1 | .937 | 23.8 | 1.715 | 43.6 | 1-20 UNEF-2A | 40 – 50 |
| 27 | 1.529 1.507 | 38.8 38.3 | 1.475 | 37.5 | .869 | 22.1 | .992 | 25.2 | 1.860 | 47.2 | 1 1/16-18 UNEF-2A | 43 – 50 |
| 37 | 1.816 1.794 | 46.1 45.6 | 1.655 | 42.0 | .994 | 25.2 | 1.117 | 28.4 | 2.120 | 53.8 | 1 3/16-18 UNEF-2A | 45 – 53 |
| 61 | 2.150 2.118 | 54.6 53.8 | 2.025 | 51.4 | 1.280 | 32.5 | 1.427 | 36.2 | 2.850 | 72.4 | 1 1/2-18 UNEF-2A | 75 – 80 |

AS81703 SERIES 3 TYPE CONNECTORS
Wall-mount receptacle
253-020-00



| How To Order | | | | | | | | |
|---------------------------------|--|--|---|----|----|------|---|---|
| Sample Part Number | 253-020 | | - | 00 | ME | 19-7 | P | N |
| Basic Part Number | AS81703 Series 3 type connector | | | | | | | |
| Rear Option | - = Accessory threads B = Band porch (consult factory) | | | | | | | |
| Connector Style | 00 = Sq. flange mount receptacle AS34241 type (MS3424) | | | | | | | |
| Material / Finish | C = Al Alloy/Black Anodize ME = Al Alloy/Electroless Nickel NF = Al Alloy/Cad O.D. Over Electroless Nickel MT = Al Alloy/Nickel-PTFE ZR = Al Alloy/Zinc-Nickel Black | | | | | | | |
| Shell Size / Insert Arrangement | See Table II pg. 2, diagrams on pgs. 4-5 | | | | | | | |
| Contact Styles | P = Pin insert A = Pin insert less contacts S = Socket insert B = Socket insert less contacts | | | | | | | |
| Insert Clocking Positions | N, W, X, Y, B, C (See Table III pg. 2) | | | | | | | |



| Shell Size | -00 Wall Mount Receptacle Dimensions | | | | | | | | | | | | |
|------------|--------------------------------------|--------------|-----------|---------|----------|------|----------|------|-------------------|-------|------|--------|------|
| | Ø A | | Ø B | | Ø D Max. | | Ø F Max. | | G Thd. | K | | L Max. | |
| | In. | mm | In. ±.003 | mm ± .1 | In. | mm | In. | mm | | In. | mm | In. | mm |
| 3 | .441 .431 | 11.2 10.9 | .573 | 14.6 | .351 | 8.9 | .509 | 12.9 | %16-24 UNEF-2A | .625 | 15.9 | .896 | 22.8 |
| 7 | .576 .566 | 14.6 14.4 | .686 | 17.4 | .531 | 13.5 | .687 | 17.4 | 3/4-20 UNEF-2A | .719 | 18.3 | 1.021 | 25.9 |
| 12 | .710 .700 | 18.0 17.8 | .823 | 20.9 | .665 | 16.9 | .812 | 20.6 | 7/8-20 UNEF-2A | .812 | 20.6 | 1.114 | 28.3 |
| 19 | .849 .839 | 21.6 21.3 | .948 | 24.1 | .790 | 20.1 | .937 | 23.8 | 1-20 UNEF-2A | .906 | 23.0 | 1.208 | 30.7 |
| 27 | 1.004 .994 | 25.5 25.2 | 1.132 | 28.8 | .869 | 22.1 | .992 | 25.2 | 1 1/16-18 UNEF-2A | .968 | 24.6 | 1.302 | 33.1 |
| 37 | 1.126 1.116 | 28.6 28.3 | 1.261 | 32.0 | .994 | 25.2 | 1.117 | 28.4 | 1 3/16-18 UNEF-2A | 1.187 | 30.1 | 1.458 | 37.0 |
| 61 | 1.414 1.404 | 35.9 35.7 | 1.573 | 40.0 | 1.280 | 32.5 | 1.427 | 36.2 | 1 1/2-18 UNEF-2A | 1.438 | 36.5 | 1.797 | 45.6 |


AS81703 SERIES 3 TYPE CONNECTORS

Jam nut receptacle


Glenair®

253-020-07

| How To Order | | | | | | |
|---------------------------------|--|-----------------------|----|----|------|----------|
| Sample Part Number | 253-020 | - | 09 | ME | 19-7 | P N |
| Basic Part Number | AS81703 Series 3 type connector | | | | | |
| Rear Option | - = Accessory threads B = Band porch (consult factory) | | | | | |
| Connector Style | 07 = Jam nut receptacle | AS34461 type (MS3446) | | | | |
| Material / Finish | C = Al Alloy/Black Anodize ME = Al Alloy/Electroless Nickel MT = Al Alloy/Nickel-PTFE NF = Al Alloy/Cad O.D. Over Electroless Nickel ZR = Al Alloy/Zinc-Nickel Black | | | | | |
| Shell Size / Insert Arrangement | See Table II pg. 2, diagrams on pgs. 4-5 | | | | | |
| Contact Styles | P = Pin insert S = Socket insert A = Pin insert less contacts B = Socket insert less contacts | | | | | |
| Insert Clocking Positions | N, W, X, Y, B, C (See Table III pg. 2) | | | | | |




| -07 Jam Nut Receptacle Dimensions | | | | | | | | | |
|-----------------------------------|--------------------------------|---------------|---------------|------------------|------------------|--------------------------------|--------------------------------|---------------|----------------|
| Shell Size | Ø A | Ø D Max. | Ø F Max. | G Thd. | H Thd. | K | L | R | N Mounting Nut |
| 3 | .441 (11.20) .431 (10.95) | .351 (8.92) | .509 (12.93) | ¾-16-24 UNEF-2A | ¾-16-24 UNEF-2A | .765 (19.43) .735 (18.67) | .765 (19.43) .735 (18.67) | .523 (13.28) | .625 (15.88) |
| 7 | .576 (14.63) .566 (14.38) | .531 (13.49) | .687 (17.45) | ¾-20 UNEF-2A | 1⅓-16-24 UNEF-2A | .890 (22.61) .860 (21.84) | .890 (22.61) .860 (21.84) | .655 (16.64) | .812 (20.62) |
| 12 | .710 (18.03) .700 (17.78) | .665 (16.89) | .812 (20.62) | 7/8-20 UNEF-2A | 1⅓-16-20 UNEF-2A | 1.077 (27.36) 1.047 (26.59) | 1.077 (27.36) 1.047 (26.59) | .778 (19.76) | .937 (23.80) |
| 19 | .849 (21.56) .839 (21.31) | .790 (20.07) | .937 (23.80) | 1-20 UNEF-2A | 1-20 UNEF-2A | 1.171 (29.74) 1.141 (28.98) | 1.202 (30.53) 1.172 (29.77) | .963 (24.46) | 1.062 (26.97) |
| 27 | 1.004 (25.50) .994 (25.25) | .869 (22.07) | .992 (25.20) | 1⅓-18 UNEF-2A | 1⅓-18 UNEF-2A | 1.327 (33.71) 1.297 (32.94) | 1.327 (33.71) 1.297 (32.94) | 1.089 (27.66) | 1.250 (31.75) |
| 37 | 1.126 (28.60) 1.116 (28.35) | .994 (25.25) | 1.117 (28.37) | 1⅓-16-18 UNEF-2A | 1⅓-18 UNEF-2A | 1.450 (36.83) 1.445 (36.70) | 1.515 (38.48) 1.485 (37.72) | 1.214 (30.84) | 1.375 (34.92) |
| 61 | 1.414 (35.92) 1.404 (35.66) | 1.280 (32.51) | 1.427 (36.25) | 1⅓-18 UNEF-2A | 1⅓-18 UNEF-2A | 1.864 (47.35) 1.834 (46.58) | 1.890 (48.01) 1.860 (47.24) | 1.463 (37.16) | 1.688 ±.015 |




| Panel Cutout | | | | | | | | |
|--------------|--------------|--------------|------------|---------------|---------------|------------|---------------|---------------|
| Shell Size | U | V | Shell Size | U | V | Shell Size | U | V |
| 3 | .538 (13.67) | .577 (14.66) | 19 | .973 (24.71) | 1.013 (25.73) | 61 | 1.471 (37.36) | 1.514 (38.46) |
| | .534 (13.56) | .567 (14.40) | | .969 (24.61) | 1.003 (25.48) | | 1.467 (37.26) | 1.504 (38.20) |
| 7 | .665 (16.89) | .701 (17.81) | 27 | 1.099 (27.91) | 1.138 (28.91) | 37 | 1.224 (31.09) | 1.263 (32.08) |
| | .661 (16.79) | .961 (24.41) | | 1.095 (27.81) | 1.128 (28.65) | | 1.220 (30.99) | 1.253 (31.83) |
| 12 | .788 (20.02) | .826 (20.98) | 37 | 1.224 (31.09) | 1.263 (32.08) | | 1.220 (30.99) | 1.253 (31.83) |
| | .784 (19.91) | .816 (20.73) | | 1.220 (30.99) | 1.253 (31.83) | | | |

AS81703 SERIES 3 TYPE CONNECTORS
Backshells and Accessories
Selection guide




Straight strain relief
AS85049/118

page D-12




90° strain relief
AS85049/120

page D-13




Straight strain relief
AS85049/52

page D-14




90° strain relief
AS85049/51

page D-15




Straight shrink boot adapter
AS85049/60-1

page D-16



Straight shrink boot adapter
AS85049/60-2G

page D-17




Straight crimp ring backshell and crimp ring
AS85049/26-1 and MS3419

page D-18




Backshell Crimp Ring
AS85049/26-2

page D-19




E-Nut (Self-Locking and Non-Self-Locking)
AS85049/31, MS3416 and MIL-DTL-85723/15N

page D-20




90° Environmental Backshell
AS85049/9 and MS3188B

page D-21



Straight EMI/RFI Environmental Backshell
AS85049/10 and MS3437A

page D-22




Straight Environmental Backshell
AS85049/11 and MS3437B

page D-23

**BACKSHELLS AND ACCESSORIES
FOR AS81703 SERIES 3 TYPE CONNECTORS
Straight Strain Relief**



AS85049/118



| TABLE I: Dash Number, Shell Size, Thread and Dimensions | | | | | | | | | | |
|---|------------|------------|-------------------|-------------|--------------------|------------|--------------|----------------------------|-------------|--------------|
| Dash No. | Screw Size | Shell Size | A Thread Class 2B | B Dia Max | C Dim ± .031 (0.8) | D Min | E Max Length | F Dim | G Dim Max | H Dim Max |
| 03 | 4-40 | 3 | 9/16-24 UNEF | .95 (24.1) | .219 (5.6) | .22 (5.6) | 1.14 (29.0) | .77 (19.6) .51 (13.0) | .88 (22.4) | .710 (18.00) |
| 12 | 4-40 | 7 | 3/4-20 UNEF | 1.14 (29.0) | .344 (8.7) | .35 (8.9) | 1.38 (35.1) | 1.01 (25.7) .76 (19.3) | 1.12 (28.4) | .710 (18.00) |
| 14 | 4-40 | 12 | 7/8-20 UNEF | 1.26 (32.0) | .460 (11.7) | .47 (11.9) | 1.38 (35.1) | 1.01 (25.7) .76 (19.3) | 1.19 (30.3) | .710 (18.00) |
| 16 | 4-40 | 19 | 1-20 UNEF | 1.39 (35.3) | .545 (13.8) | .55 (14.0) | 1.50 (38.1) | 1.13 (28.7) .88 (22.4) | 1.44 (36.6) | .710 (18.00) |
| 18 | 6-32 | 27 | 11/16-18 UNEF | 1.51 (38.4) | .615 (15.6) | .62 (15.7) | 1.75 (44.5) | 1.38 (35.1) 1.13 (28.7) | 1.56 (39.6) | .710 (18.00) |
| 20 | 6-32 | 37 | 13/16-18 UNEF | 1.64 (41.7) | .698 (17.7) | .70 (17.8) | 1.88 (47.8) | 1.51 (38.4) 1.25 (31.8) | 1.69 (42.9) | .710 (18.00) |
| 61 | 8-32 | 61 | 11/2-18 UNEF | 1.95 (49.5) | .850 (21.6) | .85 (21.6) | 2.13 (54.1) | 1.76 (44.7) 1.51 (38.5) | 1.88 (47.8) | .710 (18.0) |

TABLE II: Material and Finish

| Sym. | Material | Finish |
|------|----------------|-----------------------------|
| A | | Black Anodize |
| N | | Electroless Nickel |
| W | Aluminum Alloy | Cadmium, Olive Drab |
| X | | Nickel Fluorocarbon Polymer |
| Z | | Zinc Nickel |


NOTES

1. Glenair Series 600 Backshell Assembly Tools are recommended for assembly/installation.
2. Cable entry is measured with saddle bars closed and bottomed on clamp ears.
3. Material/Finish:
Clamp body, coupling nut, saddles - Al alloy or 300 Series SST/See Table II.
Clamp screws and lock nuts - CRES/Passivated, Silver plate optional.
Anti-rotation device - Corrosion resistant material

**BACKSHELLS AND ACCESSORIES
FOR AS81703 SERIES 3 TYPE CONNECTORS
90° Strain Relief**



AS85049/120



| TABLE I: Dash Number, Shell Size, Thread and Dimensions | | | | | | | | | | | |
|---|------------|------------|-------------------|-------------|-------------------|-------------|--------------|-------------|-------------|-------------|-------------|
| Dash No. | Screw Size | Shell Size | A Thread Class 2B | B Dia Max | C Dim ±.031 (0.8) | D Max | E Max Length | F Dim Max | G Dim Max | H Dim Max | J Dim Max |
| 03 | 4-40 | 3 | 9/16-24 UNEF | .95 (24.1) | .219 (5.6) | .93 (23.6) | 1.29 (32.8) | .84 (21.3) | 1.32 (33.5) | .88 (22.4) | .710 (18.0) |
| 12 | 4-40 | 7 | 3/4-20 UNEF | 1.14 (29.0) | .344 (8.7) | 1.21 (30.7) | 1.57 (39.9) | .93 (23.6) | 1.50 (38.1) | 1.12 (28.4) | .710 (18.0) |
| 14 | 4-40 | 12 | 7/8-20 UNEF | 1.26 (32.0) | .460 (11.7) | 1.27 (32.3) | 1.63 (41.4) | 1.00 (25.4) | 1.62 (41.4) | 1.19 (30.2) | .710 (18.0) |
| 16 | 4-40 | 19 | 1-20 UNEF | 1.39 (35.3) | .545 (13.8) | 1.42 (36.1) | 1.78 (45.2) | 1.06 (26.9) | 1.75 (44.5) | 1.44 (36.6) | .710 (18.0) |
| 18 | 6-32 | 27 | 11/16-18 UNEF | 1.51 (38.4) | .615 (15.6) | 1.53 (38.9) | 1.89 (48.0) | 1.23 (31.2) | 1.99 (50.5) | 1.56 (39.6) | .710 (18.0) |
| 20 | 6-32 | 37 | 13/16-18 UNEF | 1.64 (41.7) | .698 (17.7) | 1.65 (41.9) | 2.01 (51.1) | 1.30 (33.0) | 2.07 (52.6) | 1.69 (42.9) | .710 (18.0) |
| 61 | 8-32 | 61 | 11/2-18 UNEF | 1.95 (49.5) | .850 (21.6) | 1.90 (48.3) | 2.26 (57.4) | 1.45 (36.8) | 2.43 (61.7) | 1.88 (47.8) | .710 (18.0) |

| TABLE II: Material and Finish | | |
|-------------------------------|----------------|-----------------------------|
| Sym. | Material | Finish |
| A | Aluminum Alloy | Black Anodize |
| N | | Electroless Nickel |
| W | | Cadmium, Olive Drab |
| X | | Nickel Fluorocarbon Polymer |
| Z | | Zinc Nickel |



NOTES

1. Glenair Series 600 Backshell Assembly Tools are recommended for assembly and installation.
2. Cable entry is measured with saddle bars closed and bottomed on clamp ears.
3. Material/Finish:
Clamp body, coupling nut, saddles - Al alloy or 300 Series SST/See Table II.
Clamp screws and lock nuts - CRES/Passivated, Silver plate optional.
Anti-rotation device - Corrosion resistant material

**BACKSHELLS AND ACCESSORIES
FOR AS81703 SERIES 3 TYPE CONNECTORS
Straight Strain Relief**



AS85049/52



| TABLE I: Shell Size, Cable Entry and Backshell Dimensions | | | | | | | | | | | | |
|---|------------|-------------------|----------------------|--------|--------------------|--------|-------|--------|-------------|--------|-------|--------|
| Dash No. | Shell Size | A Thread Class 2B | Ø E Max Self-Locking | | F Max Self-Locking | | G Max | | Cable Entry | | | |
| | | | Min | Max | Min | Max | Min | Max | Min | Max | | |
| 03* | 3 | .562 - 24 UNEF | - | - | - | - | .782 | (19.9) | .125 | (3.2) | .204 | (5.2) |
| 12 | 7 | .750 - 20 UNEF | 1.135 | (28.8) | .98 | (24.9) | 1.003 | (24.6) | .291 | (7.4) | .416 | (10.6) |
| 14 | 12 | .875 - 20 UNEF | 1.260 | (32.0) | .98 | (24.9) | 1.061 | (25.5) | .351 | (8.9) | .476 | (12.1) |
| 16 | 19 | 1.000 - 20 UNEF | 1.385 | (35.2) | 1.10 | (27.9) | 1.234 | (26.9) | .501 | (12.7) | .626 | (15.9) |
| 18 | 27 | 1.062 - 18 UNEF | 1.510 | (38.4) | 1.35 | (34.3) | 1.466 | (35.4) | .518 | (13.2) | .706 | (17.9) |
| 20 | 37 | 1.188 - 18 UNEF | 1.635 | (41.5) | 1.98 | (50.3) | 1.572 | (37.2) | .581 | (14.8) | .831 | (21.1) |
| 61* | 61 | 1.500 - 18 UNEF | - | - | - | - | 1.775 | (45.1) | .706 | (17.9) | 1.081 | (27.5) |

* Not Available in Self Locking


NOTES

1. Cable Entry is defined as the accommodation entry for the wire bundle or cable.
2. Dimensions are not intended for inspection criteria.
3. For complete dimensions, see the applicable Military Specification.

**BACKSHELLS AND ACCESSORIES
FOR AS81703 SERIES 3 TYPE CONNECTORS
90° Strain Relief**



AS85049/51



| TABLE I: Shell Size, Cable Entry and Backshell Dimensions | | | | | | | | | | | |
|---|------------|-------------------|----------------------|--------------|--------------------|--------------|---------------------|-----------------|----------------|-----------------|--|
| Dash No. | Shell Size | A Thread Class 2B | Ø E Max Self-Locking | | F Max Self-Locking | | G ±.062 (1.6) | H Max | | Cable Entry | |
| | | | Ø E Max | Self-Locking | F Max | Self-Locking | | H Max | Min | Max | |
| 3* | 3 | .562 - 24 UNEF | - | - | - | - | .777 (19.7) | .782 (19.9) | .125 (3.2) | .204 (5.2) | |
| 12 | 7 | .750 - 20 UNEF | 1.135 (28.8) | | 1.532 (38.9) | | .867 (22.0) | .968 (24.6) | .291 (7.4) | .416 (10.6) | |
| 14 | 12 | .875 - 20 UNEF | 1.260 (32.0) | | 1.592 (40.4) | | .930 (23.6) | 1.003 (25.5) | .351 (8.9) | .476 (12.1) | |
| 16 | 19 | 1.000 - 20 UNEF | 1.385 (35.2) | | 1.741 (44.2) | | .994 (25.2) | 1.061 (26.9) | .501 (12.7) | .626 (15.9) | |
| 18 | 27 | 1.062 - 18 UNEF | 1.510 (38.4) | | 1.853 (47.1) | | 1.171 (29.7) | 1.394 (35.4) | .518 (13.2) | .706 (17.9) | |
| 20 | 37 | 1.188 - 18 UNEF | 1.635 (41.5) | | 1.978 (50.2) | | 1.234 (31.2) | 1.466 (37.2) | .581 (14.8) | .831 (21.1) | |
| 61* | 61 | 1.500 - 18 UNEF | - | - | - | - | 1.388 (35.3) | 1.775 (45.1) | .706 (17.9) | 1.081 (27.5) | |

* Not Available in Self Locking



NOTES

1. Cable Entry is defined as the accommodation entry for the wire bundle or cable.
2. Dimensions are not intended for inspection criteria.
3. For complete dimensions, see the applicable Military Specification.

**BACKSHELLS AND ACCESSORIES
FOR AS81703 SERIES 3 TYPE CONNECTORS**
Straight Shrink Boot Adapter



AS85049/60-1



D

| TABLE I: Shell Size, Thread and Dimensions | | | | | | |
|--|------------|----------------------|--|-----------------|-------------------------------------|-------------|
| Dash No. | Shell Size | A Thread Class 2B | C Dia Max +.000 (0.0) -.045 (1.14) | E Min Dia | F Dia +.000 (0.0) -.020 (0.5) | G Max |
| 3 | 3 | .562 - 24 UNEF | .670 (17.0) | .250 (6.4) | .533 (13.5) | .832 (21.1) |
| 12 | 7 | .750 - 20 UNEF | .860 (21.8) | .491 (12.5) | .774 (19.7) | .832 (21.1) |
| 14 | 12 | .875 - 20 UNEF | .980 (24.9) | .565 (14.4) | .838 (21.3) | .832 (21.1) |
| 16 | 19 | 1.000 - 20 UNEF | 1.110 (28.2) | .690 (17.5) | .963 (24.5) | .832 (21.1) |
| 18 | 27 | 1.062 - 18 UNEF | 1.220 (31.0) | .769 (19.5) | 1.042 (26.5) | .832 (21.1) |
| 20 | 37 | 1.188 - 18 UNEF | 1.350 (34.3) | .894 (22.7) | 1.217 (30.9) | .832 (21.1) |
| 61 | 61 | 1.500 - 18 UNEF | 1.650 (41.9) | 1.174 (29.8) | 1.529 (38.8) | .832 (21.1) |



NOTE

1. For complete dimensions see the applicable Military Specification.

**BACKSHELLS AND ACCESSORIES
FOR AS81703 SERIES 3 TYPE CONNECTORS
Straight Shrink Boot Adapter**



AS85049/60-2G



| TABLE I: Shell Size, Thread and Dimensions | | | | | |
|--|------------|-------------------|-------------------------------------|-------------------------------------|-------------|
| Dash No. | Shell Size | A Thread Class 2B | D Dia +.000 (0.0) -.020 (0.5) | F Dia +.000 (0.0) -.045 (1.1) | G Max |
| 3 | 3 | .562 - 24 UNEF | .709 (18.0) | .750 (19.1) | .540 (13.7) |
| 12 | 7 | .750 - 20 UNEF | .898 (22.8) | .938 (23.8) | .540 (13.7) |
| 14 | 12 | .875 - 20 UNEF | 1.024 (26.0) | 1.063 (27.0) | .540 (13.7) |
| 16 | 19 | 1.000 - 20 UNEF | 1.152 (29.3) | 1.238 (31.4) | .540 (13.7) |
| 18 | 27 | 1.062 - 18 UNEF | 1.243 (31.6) | 1.310 (33.3) | .540 (13.7) |
| 20 | 37 | 1.188 - 18 UNEF | 1.370 (34.8) | 1.436 (36.5) | .540 (13.7) |
| 61 | 61 | 1.500 - 18 UNEF | 1.653 (42.0) | 1.748 (44.4) | .540 (13.7) |



NOTE

1. For complete dimensions see the applicable Military Specification.

**BACKSHELLS AND ACCESSORIES
FOR AS81703 SERIES 3 TYPE CONNECTORS**
Straight Crimp Ring Backshell and Crimp Ring



AS85049/26-1 and MS3419



| TABLE I: Adapter Shell Size, Thread, and Dimensions | | | | | |
|---|------------|-------------------|--------------|--------------|--------------|
| Dash No. | Shell Size | A Thread Class 2B | C Dia Max | E Dia | F Dia |
| 3 | 3 | .562 - 24 UNEF | .670 (17.0) | .250 (6.4) | .337 (8.6) |
| 12 | 7 | .750 - 20 UNEF | .860 (21.8) | .420 (10.7) | .500 (12.7) |
| 14 | 12 | .875 - 20 UNEF | .980 (24.9) | .540 (13.7) | .620 (15.7) |
| 16 | 19 | 1.000 - 20 UNEF | 1.110 (28.2) | .670 (17.0) | .750 (19.1) |
| 18 | 27 | 1.062 - 18 UNEF | 1.220 (31.0) | .789 (20.0) | .880 (22.4) |
| 20 | 37 | 1.188 - 18 UNEF | 1.350 (34.3) | .914 (23.2) | 1.000 (25.4) |
| 61 | 61 | 1.500 - 18 UNEF | 1.650 (41.9) | 1.210 (30.7) | 1.359 (34.5) |

D

NOTES

1. For complete dimensions see the applicable Military Specification.
2. Metric dimensions (mm) are in parentheses.

**BACKSHELLS AND ACCESSORIES
FOR AS81703 SERIES 3 TYPE CONNECTORS**
Backshell Crimp Ring



AS85049/26-2





TABLE I: Shell Size, Thread, Cable Entry and Dimensions

| Dash No. | Shell Size | Color Code | A Dia | | B Dia | | L Dim $\pm .020$ (0.5) | Installing Die Cat. No. (See Note 2) |
|----------|------------|------------|--------------|--------------|--------------|--------------|------------------------------|---|
| | | | Min | Max | Min | Max | | |
| 8 | 3 | GREEN | .400 (10.2) | .410 (10.4) | .448 (11.4) | .458 (11.6) | .250 (6.4) | GS405 |
| 12 | 7 | RED | .585 (14.9) | .595 (15.1) | .660 (16.8) | .680 (17.3) | .440 (11.2) | GS590 |
| 14 | 12 | BLUE | .705 (17.9) | .715 (18.2) | .780 (19.8) | .800 (20.3) | .440 (11.2) | GS710 |
| 16 | 19 | GREY | .835 (21.2) | .845 (21.5) | .910 (23.1) | .930 (23.6) | .440 (11.2) | GS840 |
| 18 | 27 | BROWN | 1.005 (25.5) | 1.015 (25.8) | 1.080 (27.4) | 1.100 (27.9) | .440 (11.2) | GS1010 |
| 20 | 37 | GREEN | 1.125 (28.6) | 1.135 (28.8) | 1.200 (30.5) | 1.220 (31.0) | .440 (11.2) | GS1130 |
| 61 | 61 | PURPLE | 1.435 (36.4) | 1.445 (36.7) | 1.510 (38.4) | 1.530 (38.9) | .440 (11.2) | GS1440 |

D



NOTES

1. Assembly identified with manufacturer's name and part number, space permitting.
2. Crimp tool shall be the Thomas and Betts Installing Head catalog number 13640 or equivalent (see Table I).
3. The installing dies (Thomas and Betts Cat. No.--See Table I) shall be used with the Thomas and Betts Installing head Catalog Number 13640 or an equivalent tool.
4. Material/Finish: Copper/Tin Plate.
5. Metric dimensions (mm) are in parentheses.

**BACKSHELLS AND ACCESSORIES
FOR AS81703 SERIES 3 TYPE CONNECTORS
E-Nut (Self-Locking and Non-Self-Locking)**



AS85049/31, MS3416 and MIL-DTL-85723/15N



| Superseded Part Number | | |
|---|----------|--|
| M83723/15N-10 A | | |
| Basic Part No. (Non-Self-Locking Only) | Dash No. | Finish Designator A = Non-Conductive, Black Anodize R = Conductive, Electroless Nickel |
| | | |

| Superseded Part Number | | |
|---|-------|---|
| MS3416 -10-E A | | |
| Dash No. | Style | Metal and Finish Designator A = Aluminum 500 Hour Cad. Olive Drab Over Electroless Nickel C = Aluminum, Cadmium Olive Drab G = Aluminum, Black Anodize N = Aluminum, Electroless Nickel |
| Basic Part No. (Non-Self-Locking Only) | | |

| TABLE I: Shell Size, Thread and Dimensions | | | | | | |
|--|-------------------|---------|--------|-------|--------|--------------|
| Shell Size | A Thread Class 2B | Ø E Max | | F Max | | Ø G Max |
| 3 | .562 - 24 UNEF | .270 | (6.9) | -- | -- | -- |
| 7 | .750 - 20 UNEF | .511 | (13.0) | .710 | (18.0) | 1.135 (28.8) |
| 12 | .875 - 20 UNEF | .585 | (14.9) | .710 | (18.0) | 1.260 (32.0) |
| 19 | 1.000 - 20 UNEF | .710 | (18.0) | .710 | (18.0) | 1.385 (35.2) |
| 27 | 1.062 - 18 UNEF | .789 | (20.0) | .710 | (18.0) | 1.510 (38.4) |
| 37 | 1.188 - 18 UNEF | .914 | (23.2) | .710 | (18.0) | 1.635 (41.5) |
| 61 | 1.500 - 18 UNEF | 1.194 | (30.3) | -- | -- | -- |



NOTES

- For complete dimensions see the applicable Military Specification.
- Metric dimensions (mm) are in parentheses.


**BACKSHELLS AND ACCESSORIES
FOR AS81703 SERIES 3 TYPE CONNECTORS
90° Environmental Backshell**



AS85049/9 and MS3188B



STYLE 2



D

TABLE II: Dash Number and Cable Range

| Dash No. | Shell Size | A Thread Ref | C Dia Max | H Max | J Max | K Ref. | L Max | Cable Range Min | Cable Range Max |
|----------|------------|---------------|-------------|--------------|--------------|--------------|--------------|-----------------|-----------------|
| 1 | 03 | 9/16-24 UNEF | .98 (24.9) | .761 (19.3) | 1.862 (47.3) | 1.027 (26.1) | .957 (24.3) | .125 (3.2) | .250 (6.4) |
| 2 | 03 | | | 1.511 (38.4) | 1.382 (35.1) | 1.027 (26.1) | 1.145 (29.1) | .250 (6.4) | .437 (11.1) |
| 6 | 12 | 7/8-20 UNEF | 1.28 (32.5) | .766 (19.5) | 2.002 (50.9) | 1.027 (26.1) | .957 (24.3) | .125 (3.2) | .312 (7.9) |
| 7 | 12 | | | .766 (19.5) | 2.002 (50.9) | 1.027 (26.1) | 1.145 (29.1) | .250 (6.4) | .437 (11.1) |
| 8 | 12 | | | .766 (19.5) | 1.397 (35.5) | 1.027 (26.1) | 1.332 (33.8) | .350 (8.9) | .500 (12.7) |
| 38 | 61 | 1-1/2-18 UNEF | 1.89 (48.0) | 1.291 (32.8) | 2.442 (62.0) | 1.059 (26.9) | 1.551 (39.4) | .500 (12.7) | .750 (19.1) |
| 39 | 61 | | | 1.291 (32.8) | 2.087 (53.0) | 1.375 (34.9) | 2.113 (53.7) | .875 (22.2) | 1.184 (30.1) |
| 53 | 61 | | | 1.291 (32.8) | 2.087 (53.0) | 1.156 (29.4) | 1.770 (45.0) | .625 (15.9) | .937 (23.8) |



NOTES

1. For complete dimensions see the applicable Military Specification.
2. Metric dimensions (mm) are in parentheses.
3. When maximum cable entry is exceeded, Style 2 will be supplied.
4. Cable Range is defined as the accommodation range for the wire bundle or cable. Dimensions shown are not intended for inspection criteria.
5. Approximate chain lengths: Dash No. 01-12 = 5.0 (127.0); Dash No. 13-29 = 6.0 (152.4).

**BACKSHELLS AND ACCESSORIES
FOR AS81703 SERIES 3 TYPE CONNECTORS
Straight EMI/RFI Environmental Backshell**



AS85049/10 and MS3437A



STYLE 2

STYLE 1

TABLE I: Shell Size and Dimensions

| Dash No. | Shell Size | A Thread Class 2B | C Dia Max |
|----------|------------|-------------------|-------------|
| 3 | 3 | .562 - 24 UNEF | .67 (17.0) |
| 12 | 7 | .750 - 20 UNEF | .86 (21.8) |
| 14 | 12 | .875 - 20 UNEF | .98 (24.9) |
| 16 | 19 | 1.000 - 20 UNEF | 1.11 (28.2) |
| 18 | 27 | 1.062 - 18 UNEF | 1.22 (31.0) |
| 20 | 37 | 1.188 - 18 UNEF | 1.34 (34.0) |
| 61 | 61 | 1.500 - 18 UNEF | 1.65 (41.9) |

TABLE II: Dash No., Style, Shell Size, Dimensions and Cable Range

| Dash No. | Shell Size | Style | E Max | K Ref | L Max | Cable Range Min | Cable Range Max |
|----------|------------|-------|---------------|--------------|--------------|-----------------|-----------------|
| 01 | 3 | 1 | 2.125 (54.0) | 1.544 (39.2) | .957 (24.3) | .125(3.2) | .250(6.4) |
| 02 | 3 | 1 | 3.125 (79.4) | 1.544 (39.2) | .957 (24.3) | .125(3.2) | .250(6.4) |
| 03 | 3 | 2 | 2.875 (73.0) | 1.544 (39.2) | 1.145 (29.1) | .250(6.4) | .437 (11.1) |
| 04 | 3 | 2 | 3.875 (98.4) | 1.544 (39.2) | 1.145 (29.1) | .250(6.4) | .437 (11.1) |
| 13 | 12 | 1 | 2.125 (54.0) | 1.544 (39.2) | 1.145 (29.1) | .250(6.4) | .437 (11.1) |
| 14 | 12 | 1 | 3.125 (79.4) | 1.544 (39.2) | 1.145 (29.1) | .250(6.4) | .437 (11.1) |
| 15 | 12 | 2 | 2.875 (73.0) | 1.844 (46.8) | 1.332 (33.8) | .350(8.9) | .625 (15.9) |
| 16 | 12 | 2 | 3.875 (98.4) | 1.844 (46.8) | 1.332 (33.8) | .350(8.9) | .625 (15.9) |
| 103 | 61 | 1 | 3.125 (79.4) | 1.916 (48.7) | 1.551 (39.4) | .500 (12.7) | .750 (19.1) |
| 104 | 61 | 1 | 4.125 (104.8) | 1.916 (48.7) | 1.551 (39.4) | .500 (12.7) | .750 (19.1) |
| 105 | 61 | 1 | 3.125 (79.4) | 2.000 (50.8) | 1.770 (45.0) | .625 (15.9) | .937 (23.8) |
| 106 | 61 | 1 | 4.125 (104.8) | 2.000 (50.8) | 1.770 (45.0) | .625 (15.9) | .937 (23.8) |
| 107 | 61 | 2 | 3.875 (98.4) | 2.230 (56.6) | 2.113 (53.7) | .875 (22.2) | 1.250 (31.8) |
| 108 | 61 | 2 | 4.875 (123.8) | 2.230 (56.6) | 2.113 (53.7) | .875 (22.2) | 1.250 (31.8) |
| 109 | 61 | 2 | 3.875 (98.4) | 2.024 (51.4) | 2.363 (60.0) | 1.000 (25.4) | 1.375 (34.9) |
| 110 | 61 | 2 | 4.875 (123.8) | 2.024 (51.4) | 2.363 (60.0) | 1.000 (25.4) | 1.375 (34.9) |
| 111 | 12 | 1 | 2.125 (54.0) | 1.844 (46.8) | 1.332 (33.8) | .350 (8.9) | .500 (12.7) |
| 114 | 12 | 1 | 2.125 (54.0) | 1.544 (39.2) | .957 (24.3) | .125 (3.2) | .312 (7.9) |
| 115 | 12 | 1 | 3.125 (79.4) | 1.544 (39.2) | .957 (24.3) | .125 (3.2) | .312 (7.9) |
| 138 | 12 | 1 | 2.125 (54.0) | 1.844 (46.8) | 1.332 (33.8) | .350 (8.9) | .500 (12.7) |
| 139 | 12 | 1 | 3.125 (79.4) | 1.844 (46.8) | 1.332 (33.8) | .350 (8.9) | .500 (12.7) |

D

NOTES



- For complete dimensions see the applicable Military Specification.
- Metric dimensions (mm) are in parentheses.
- Cable Range is defined as the accommodation range for the wire bundle or cable. Dimensions shown are not intended for inspection criteria.

BACKSHELLS AND ACCESSORIES FOR AS81703 SERIES 3 TYPE CONNECTORS


Straight Environmental Backshell




AS85049/11 and MS3437B



STYLE 2



| Finish / Material | |
|-------------------|---|
| B | = Black Cadmium / Stainless Steel |
| N | = Electroless Nickel / Aluminum |
| S | = Passivated / Stainless Steel |
| W | = 1,000 Hr. Cadmium Olive Drab over Electroless Nickel / Aluminum |
| X | = Aluminum, Nickel Fluorocarbon Polymer |
| Z | = Aluminum, Zinc-Nickel, Black |
| XS | = Stainless Steel, Nickel Fluorocarbon Polymer |
| ZS | = Stainless Steel, Zinc-Nickel, Black |



STYLE 1

| TABLE I: Shell Size and Dimensions | | | |
|------------------------------------|------------|-------------------|-------------|
| Dash No. | Shell Size | A Thread Class 2B | C Dia Max |
| 3 | 3 | .562 - 24 UNEF | .67 (17.0) |
| 12 | 7 | .750 - 20 UNEF | .86 (21.8) |
| 14 | 12 | .875 - 20 UNEF | .98 (24.9) |
| 16 | 19 | 1.000 - 20 UNEF | 1.11 (28.2) |
| 18 | 27 | 1.062 - 18 UNEF | 1.22 (31.0) |
| 20 | 37 | 1.188 - 18 UNEF | 1.34 (34.0) |
| 61 | 61 | 1.500 - 18 UNEF | 1.65 (41.9) |

| Dash No. | Shell Size | Style | E Max | K Ref | L Max | Cable Range Min | Cable Range Max |
|----------|------------|-------|---------------|--------------|--------------|-----------------|-----------------|
| Dash No. | Shell Size | Style | E Max | K Ref | L Max | Cable Range Min | Cable Range Max |
| 01 | 3 | 1 | 2.125 (54.0) | 1.027 (26.1) | .957 (24.3) | .125 (3.2) | .250 (6.4) |
| 02 | 3 | 1 | 3.125 (79.4) | 1.027 (26.1) | .957 (24.3) | .125 (3.2) | .250 (6.4) |
| 03 | 3 | 2 | 2.875 (73.0) | 1.027 (26.1) | 1.145 (29.1) | .250 (6.4) | .437 (11.1) |
| 04 | 3 | 2 | 3.875 (98.4) | 1.027 (26.1) | 1.145 (29.1) | .250 (6.4) | .437 (11.1) |
| 13 | 12 | 1 | 2.125 (54.0) | 1.027 (26.1) | 1.145 (29.1) | .250 (6.4) | .437 (11.1) |
| 14 | 12 | 1 | 3.125 (79.4) | 1.027 (26.1) | 1.145 (29.1) | .250 (6.4) | .437 (11.1) |
| 15 | 12 | 2 | 2.875 (73.0) | 1.027 (26.1) | 1.332 (33.8) | .350 (8.9) | .625 (15.9) |
| 16 | 12 | 2 | 3.875 (98.4) | 1.027 (26.1) | 1.332 (33.8) | .350 (8.9) | .625 (15.9) |
| 103 | 61 | 1 | 3.125 (79.4) | 1.059 (26.9) | 1.551 (39.4) | .500 (12.7) | .750 (19.1) |
| 104 | 61 | 1 | 4.125 (104.8) | 1.059 (26.1) | 1.551 (39.4) | .500 (12.7) | .750 (19.1) |
| 105 | 61 | 1 | 3.125 (79.4) | 1.156 (29.4) | 1.770 (45.0) | .625 (15.9) | .937 (23.8) |
| 106 | 61 | 1 | 4.125 (104.8) | 1.156 (29.4) | 1.770 (45.0) | .625 (15.9) | .937 (23.8) |
| 107 | 61 | 2 | 3.875 (98.4) | 1.375 (34.9) | 2.113 (53.7) | .875 (22.2) | 1.250 (31.8) |
| 108 | 61 | 2 | 4.875 (123.8) | 1.375 (34.9) | 2.113 (53.7) | .875 (22.2) | 1.250 (31.8) |
| 109 | 61 | 2 | 3.875 (98.4) | 1.500 (38.1) | 2.363 (60.0) | 1.000 (25.4) | 1.375 (34.9) |
| 110 | 61 | 2 | 4.875 (123.8) | 1.500 (38.1) | 2.363 (60.0) | 1.000 (25.4) | 1.375 (34.9) |
| 111 | 12 | 1 | 2.125 (54.0) | 1.027 (26.1) | 1.332 (33.8) | .350 (8.9) | .500 (12.7) |
| 114 | 12 | 1 | 2.125 (54.0) | 1.027 (26.1) | .957 (24.3) | .125 (3.2) | .312 (7.9) |
| 115 | 12 | 1 | 3.125 (79.4) | 1.027 (26.1) | .957 (24.3) | .125 (3.2) | .312 (7.9) |
| 138 | 12 | 1 | 2.125 (54.0) | 1.027 (26.1) | 1.332 (33.8) | .350 (8.9) | .500 (12.7) |
| 139 | 12 | 1 | 3.125 (79.4) | 1.027 (26.1) | 1.332 (33.8) | .350 (8.9) | .500 (12.7) |

NOTES

- For complete dimensions see the applicable Military Specification.
- Metric dimensions (mm) are in parentheses.
- Cable Range is defined as the accommodation range for the wire bundle or cable. Dimensions shown are not intended for inspection criteria.

D

Specification information

Space-grade interconnect manufacturing and test capability

Outgassing and Inspection Modification Codes

Glenair space mechanisms and related interconnect solutions are ideally designed for deployment of CubeSat and NanoSat equipment. All HDRMs, and connectors feature materials, finishes, and performance specifications that perform to NASA EEE-INST-002

Outgassing

Space flight equipment requires low-outgassing components in order to prevent degradation to optics and other sensitive instruments. Various Glenair connectors contain nonmetallic materials such as rubber, plastic, adhesives and potting compounds which can give off gasses when subjected to a vacuum or high heat. Unless the connector is specially processed, the TML and CVCM can exceed allowable limits. The space industry has adopted a standardized test procedure, ASTM E595, to evaluate outgassing properties. The MIL-DTL-38999 specification Class G also details specific TVM and CVCM values. In Glenair's 186T process, for example, connectors and connector materials are heated to 175° C at a vacuum of 5×10^{-6} Torr for 48 hours. Items under test are then weighed to calculate the Total Mass Loss (TML), which may not exceed 1.0% of the total initial mass. A collector plate is used to determine the Collected Volatile Condensable Material (CVCM), which may not exceed 0.1% of the total original specimen mass. Glenair is able to offer outgas processing which assures all materials comply with their respective standards.

Note on Connector Material and Finish Options

Some types of metals are prohibited for space flight. "Pure Tin, Cadmium, Zinc shall not be used as a final finish on EEE part (NASA EEE-INST-002 Instructions for EEE Parts Selection, Screening, Qualification, and Derating). NASA recommends electroless nickel or gold finish on connector shells and gold finish for contacts.

Specifying Appropriate NASA Screening

- 1** Choose a NASA EEE-INST-002 Table 2A screening level. This table contains three screening levels: **Level 1** for missions requiring the highest reliability and lowest level of risk, **Level 2** for low to moderate risk missions, and **Level 3** missions where enhanced screening and inspection is not invoked.
- 2** Choose outgassing process and/or NASA inspection requirements. 9 options are available for NASA outgassing, see Table I for details. Cross reference Table II for inspections completed by screening level as required by NASA standards.
- 3** Select the modification code from the table and add it to the part number.
Example: 253-01600ME21-35PNMSA-**429**.

Table I: Outgassing per NASA Screening Levels and D38999, Class G


| Screening Level | No Outgas Processing | 48 Hour Oven Bake 175° C 100% | Thermal Vacuum* Outgassing 24 Hour 125° C 100% | Thermal Vacuum* Outgassing 48 Hour 175° C 100% | Mod Code |
|-----------------|----------------------|-------------------------------|--|--|--|
| No Screening | | | ● | | 186M (ASTM E595) 186T (Class G) |
| 3 | | | ● | | 429L |
| 2 | ● | | | | 429 |
| | | ● | ● | | 429A 429K |
| 1 | ● | | | ● | 429B 429C 429J |
| | | ● | | | |

*Thermal vacuum of 10^{-6} Torr.

Table II: NASA EEE-INST-02, Table 2A Screening Levels

| Inspection | Level 1 | Level 2 | Level 3 |
|---------------------------------------|---------|---------|---------|
| Visual | 100% | 100% | 100% |
| Mechanical | 2 | 2 | |
| Dielectric Withstanding Voltage | 2 | 2 | |
| Insulation Resistance | 2 | 2 | |
| Contact Engagement & Separation Force | 2 | | |
| Hermeticity (Sealed Receptacles Only) | 100% | 100% | 100% |
| Coupling Force | 2 | | |

Note: required inspection quantity shown. Zero acceptance of failures allowed for all quantities inspected. Inspection is not performed/required for MIL-DTL-38999, Class G



Glenair's family of space mechanisms are manufactured in certified cleanrooms. Full qualification test reports are available for every device type. NASA/ESA outgas processing and screening completed on-site. All operations are managed under a single certified quality system with unprecedented levels of performance.



But don't take it from us... take it from NASA

December 5, 2016

Good afternoon Mr. Christopher J. Toomey...and to the Glenair Family


On behalf of the NASA Launch Services Program (LSP) and the Safety and Mission Assurance Division (SMA), I would like to express sincere appreciation for the hospitality afforded our NASA team... last week. It is obvious that your company takes pride and recognizes the value in meeting and even exceeding the intents of the Aerospace Standard AS9100. We came away with a positive sense in the partnership.... You have a remarkable campus facility and a remarkable employee team there in Glendale, and I am sure, throughout your vast network of offices and facilities around the world as well. The Quality leadership has done an outstanding job implementing a working Quality Management System around your successful business model. Thank you for recognizing the importance of this particular supplier audit to NASA... as we seek crucial information relative to the NASA Certification....

...I would like to express some of the other very positive comments that our team came away with regarding this audit. All of your employee team should take pride in the quality of your finished product line for your customers. To that end, here is a listing of but a few of our team's observations during the audit process:

| | |
|---|---|
| 1. Welcoming hospitality to customers 2. Informative Corporate Overview Presentation 3. Positive Employee Attitudes about the workplace 4. Informative and thorough process walk-downs 5. Informative and thorough production facility walk-downs 6. Processing area cleanliness and 5S organization | 7. Timely Corrective Action and effective Preventive Action plans 8. Top Management involvement and participation in the QMS – AS9100 processes 9. Expertise of the employee team members 10. ...and the ability of a randomly selected employee to express the Quality Policy and what it means to him in his position with the company |
|---|---|

A formal compilation report is in work, and should reflect the over arching positive note, which recognizes that the audit at Glenair had no Major and no Minor findings whatsoever. Please forward to any appropriate team members who have contributed to this successful audit.

Respectfully,
 Paul Cloues, NASA Quality Engineer
 NASA Launch Services Program
 Safety and Mission Assurance, SA-D
 Analysis Planning and Test (APT) Research



PROVEN FLIGHT HERITAGE


SPACE-GRADE SOLUTIONS

NASA · ESA · JAXA · Commercial




Complex space-grade cable assemblies (shown: Glenair-made "Golden Umbilical")

TURNKEY, SPACE-GRADE EMI/RFI WIRE HARNESS AND CABLE ASSEMBLIES



HOLD-DOWN RELEASE MECHANISMS, PIN PULLERS AND PIN PUSHERS



SPACEWIRE CERTIFIED CABLES



Laboratory and flight variants

SPACE-QUALIFIED HERMETIC RECEPTACLES



Glass-to-metal and CODE RED encapsulant hermetic solutions for high-pressure / low-leakage space applications


EMI/RFI FILTER CONNECTORS



MIL-DTL-38999 type, Series 80 Mighty Mouse, and other circulars


HiPer-D and Micro-Crimp filtered rectangualrs

SPACE-GRADE 83513 MICRO-D AND 32139 NANO



ESA and NASA screened connectors and backshells available as discrete components or wired pigtail assemblies

SERIES 28 HIPER-D M24308 INTERMATEABLE



Qualified MIL-DTL-24308 Class K Space-Grade Hermetic, environmental, filter, Sav-Con's and cordsets

LIGHTWEIGHT MIGHTY MOUSE AND SERIES 79



Small, lightweight, high-density ideally suited for space programs

A proven product, ideal for guidepin and rack-and-panel applications

SAV-CON® CONNECTOR SAVERS



Available for every military and commercial circular and rectangular connector series


ULTRA-LIGHTWEIGHT CONDUIT AND BRAID



Factory-terminated and user-installable conduit systems

Weight-saving microfilament EMI braided shielding solutions

ASSISTED-RELEASE, AND LANYARD QUICK-DISCONNECTS



Blind mate D38999 type feedthrough with kick-off assist

Lanyard-release quick-disconnects

FIBER OPTIC CONNECTORS, CABLES, AND PHOTONIC MEDIA CONVERSION



High-speed, high-bandwidth space-grade solutions



MISSION-CRITICAL INTERCONNECT SOLUTIONS

Glenair, Inc.

1211 Air Way • Glendale, California • 91201-2497

Telephone: 818-247-6000 • Fax: 818-500-9912 • sales@glenair.com

www.glenair.com

Glenair Power

Products Group

860 N. Main Street Extension
Wallingford, CT
06492

Telephone:

203-741-1115

Facsimile:

203-741-0053

sales@glenair.com

Glenair UK Ltd

40 Lower Oakham Way
Oakham Business Park
Mansfield, Notts
NG18 5BY England

Telephone:

+44-1623-638100

Facsimile:

+44-1623-638111

sales@glenair.co.uk

Glenair Microway Systems

7000 North Lawndale Avenue
Lincolnwood, IL
60712

Telephone:

847-679-8833

Facsimile:

847-679-8849

Glenair Nordic AB

Gustav III : S Boulevard 46
SE-169 27 Solna
Sweden

Telephone:

+46-8-50550000

sales@glenair.se

Glenair Electric GmbH

Schaberweg 28
61348 Bad Homburg
Germany

Telephone:

06172 / 68 16 0

Facsimile:

06172 / 68 16 90

info@glenair.de

Telephone:

+34-925-89-29-88

Facsimile:

+34-925-89-29-87

sales@glenair.es

Glenair Italia S.p.A.

Via Del Lavoro, 7
40057 Quarto Inferiore –
Granarolo dell'Emilia
Bologna, Italy

Telephone:

+39-051-782811

Facsimile:

+39-051-782259

info@glenair.it

Telephone:

+33-5-34-40-97-40

Facsimile:

+33-5-61-47-86-10

sales@glenair.fr

Glenair Korea

B-1304 Gunpo IT Valley
148 Gosan-Ro, Gunpo-Si
Kyunggi-Do, Korea
435-733

Telephone:

+82-31-8068-1090

Facsimile:

+82-31-8068-1092

sales@glenair.kr
